
SANITARY ACCESSORIES


Micro-DC Cable Assemblies For Probes, Sensors and Transmitters

M12C Series


- ✓ Extension Cables with M12 Female Connector
- ✓ Gold Plated Contacts
- ✓ PVC and Polyurethane Jacket/Insulation
- Available in Various Lengths
- Straight or Right Angle Connection
- Cable Configurations Include Connector and Stripped Lead Ends or Connectors at Both Ends











Color Codes						
Pin 1	Pin 2	Pin 3	Pin 4			
Brown	White	Blue	Black			

To Order Visit omega.com/m12c for Pricing and Details						
Model Number	Connector #1	Connector #2	Cable Length	Insulation Jacket		
M12C-PUR-4-S-F-2	Straight M12 plug	Stripped leads	2 m (6.5')	PUR		
M12C-PUR-4-R-F-2	Angled M12 plug	Stripped leads	2 m (6.5')	PUR		
M12C-PUR-4-S-F-5	Straight M12 plug	Stripped leads	5 m (16.4')	PUR		
M12C-PUR-4-R-F-5	Angled M12 plug	Stripped leads	5 m (16.4')	PUR		
M12C-PUR-4-S-F-10	Straight M12 plug	Stripped leads	10 m (32.6')	PUR		
M12C-PUR-4-R-F-10	Angled M12 plug	Stripped leads	10 m (32.6')	PUR		
M12C-PVC-4-S-F-5	Straight M12 plug	Stripped leads	5 m (16.4')	PVC		
M12C-PVC-4-R-F-5	Angled M12 plug	Stripped leads	5 m (16.4')	PVC		
M12C-PVC-4-S-F-10	Straight M12 plug	Stripped leads	10 m (32.6')	PVC		
M12C-PVC-4-R-F-10	Angled M12 plug	Stripped leads	10 m (32.6')	PVC		
M12C-PVC-4-S-M-R-F-2	Straight M12 plug	Angled M12 socket	2 m (6.5')	PVC		
M12C-PVC-4-S-M-R-F-5	Straight M12 plug	Angled M12 socket	5 m (16.4')	PVC		
M12C-PVC-4-S-M-S-F-2	Straight M12 plug	Straight M12 socket	2 m (6.5')	PVC		
M12C-PVC-4-S-M-S-F-5	Straight M12 plug	Straight M12 socket	5 m (16.4')	PVC		
M12-S-F-FM	Straight M12 socket - field mountable†		N/A	N/A		
M12-S-M-FM	Straight M12 plug - field mountable†		N/A	N/A		
M12-R-F-FM	Angled M12 socket - field mountable [†]		N/A	N/A		
M12-R-M-FM	Angled M12 plug - field mountable†		N/A	N/A		

[†] Field installable 4-pin M12 connector with screw type terminals.

Ordering Examples: M12C-PVC-4-R-F-5, M12C series cable assembly, right angle connection, PVC cable, 5 m (16.4') L. M12C-PUR-4-S-F-2, M12C series cable assembly, straight connection, polyurethane cable, 2 m (6.5') L.