

NON-METALLIC PUSHBUTTON ENCLOSURES

NEMA 4X (IP66) FOR 22 AND 30 mm PUSHBUTTONS

OM-AMPB Series



- Suited for Higher Temperatures or Corrosive Environments
- Protect Controls and Components Indoors or Outdoors
- 30 or 22 mm Hole Sizes
- UL 94 Flammability Rating
- UV Stabilized for Outdoor Use
- 304 SS Hardware and Continuous Hinge
- Optional Sub-Panels Available

OM-AMPB Series non-metallic fiberglass pushbutton enclosures are designed to insulate and protect electrical controls and components in both indoor and outdoor applications and are especially well suited for higher temperatures and corrosive environments. These NEMA 4X (IP66) fiberglass pushbutton enclosures feature stainless steel continuous hinge.

CONSTRUCTION

- Fiberglass Reinforced Polyester Formulation
- Closed Cell Neoprene Seal Designed for NEMA 4X (IP66) Rating
- 304 SS Continuous Hinge and Mounting Feet Included with SS Screws

SPECIFICATIONS

Service Temperature Rating:

-35 to 130°C (-31 to 266°F)

Standards: UL Types 1, 2, 3, 4, 4X, 12 and 13; CSA Types 1, 2, 3, 3R, 4 4X, 12 and 13; NEMA Types 1, 2, 3, 3R, 4, 4X, 12 and 13; IEC Type IP66

OM-AM1084HP9, 9 hole pushbutton enclosure.

All models shown smaller than actual size.



OM-AM1PB, 1 hole pushbutton enclosure.



OM-AM2PB, 2 hole pushbutton enclosure.

OM-AM3PB, 3 hole pushbutton enclosure.

To Order

FLAT COVER SCREW CLOSURE MODELS

MODEL NO.	NO. OF PUSHBUTTONS	HEIGHT	INCHES WIDTH	DEPTH
OM-AM1PB	1	6.75	4	3.63
OM-AM2PB	2	6.75	4	3.63
OM-AM3PB	3	9	4	3.63
OM-AM664HP4	4	6	6	4
OM-AM864HP6	6	8	6	4
OM-AM1084HP9	9	10	8	4
OM-AM1086HP9	9	10	8	6
OM-AM1086HP12	12	10	8	6
OM-AM1206HP16	16	12	10	6
OM-AM1206HP20	20	12	10	6
OM-AM1426HP25	25	14	12	6
OM-AM1648HP30	30	16	14	8
OM-AM1868HP42	42	18	16	8

Accessories

STEEL SUB-PANELS	DESCRIPTION
SCE-6P6	Sub-panel for 6 x 6" enclosure
SCE-8P6	Sub-panel for 8 x 6" enclosure
SCE-10P8	Sub-panel for 10 x 8" enclosure
SCE-12P10	Sub-panel for 12 x 10" enclosure
SCE-14P12	Sub-panel for 14 x 12" enclosure
SCE-16P14	Sub-panel for 16 x 14" enclosure
OM-P186	Sub-panel for 18 x 16" enclosure

Note: For 22 mm button holes add "22" to the end of the model number, no additional cost. Mounting feet included on 4 button or larger models.

Ordering Examples: OM-AM3PB22, fiberglass pushbutton enclosure for 3, 22 mm pushbuttons, 9 H x 4 W x 3.63" D.

OM-AM1086HP9, fiberglass pushbutton enclosure for 9, 30 mm pushbuttons, mounting feet included, 10 H x 8 W x 6" D.