

3/4" to 1" OD TUBING, 75 Shore A Durometer							
Model No.	Price	OD (Nom) (in)	ID (in)	Wall (in)	ID (±) (in)	Wall Tol (±) (in)	Std. Length (ft)
TYVT7-3438-100	\$3025	3/4	3/8	3/16	0.018	0.012	100
TYVT7-7838-100	4487	7/8	3/8	1/4	0.018	0.012	100
TYVT7-34716-100	2525	3/4	7/16	5/32	0.018	0.012	100
TYVT7-5812-100	950	5/8	1/2	1/16	0.02	08	100
TYVT7-111612-100	776	11/16	1/2	3/32	0.02	0.01	100
TYVT7-3412-100	2452	3/4	1/2	1/8	0.02	0.012	100
TYVT7-7812-100	4484	7/8	1/2	3/16	0.02	0.012	100
TYVT7-112-100	6553	1	1/2	1/4	0.02	0.014	100
TYVT7-151658-100	2762	15/16	5/8	3/32	0.022	0.01	100
TYVT7-7858-25	495	7/8	5/8	1/8	0.022	0.012	25
TYVT7-7858-100	1950	7/8	5/8	1/8	0.022	0.012	100
TYVT7-158-100	5052	1	5/8	3/16	0.022	0.012	100
TYVT7-134-100	2275	1	3/4	1/8	0.022	0.012	100
TYVT7-178-100	2084	1	7/8	1/16	0.025	0.01	100
5/32 "to 1" OD TUBING, 90 Shore A Durometer							
TYVT9-532132-250	\$770	5/32	1/32	1/16	08	08	250
TYVT9-18116-250	440	1/8	1/16	1/32	0.01	05	250
TYVT9-316116-100	260	3/16	1/16	1/16	0.01	08	100
TYVT9-14116-100	452	1/4	1/16	3/32	0.01	08	100
TYVT9-516116-100	735	5/16	1/16	1/4	0.01	0.01	100
TYVT9-38116-100	995	3/8	1/16	5/32	0.01	0.012	100
TYVT9-31618-100	595	3/16	1/8	1/32	0.01	08	100
TYVT9-1418-100	368	1/4	1/8	1/16	0.01	08	100
TYVT9-51618-100	690	5/16	1/8	3/32	0.01	08	100
TYVT9-3818-100	980	3/8	1/8	1/8	0.01	0.01	100
TYVT9-14316-100	288	1/4	3/16	1/32	0.015	08	100
TYVT9-516316-100	595	5/16	3/16	1/16	0.015	08	100
TYVT9-38316-100	925	3/8	3/16	3/32	0.015	08	100
TYVT9-716316-100	1192	7/16	3/16	1/8	0.015	0.01	100
TYVT9-12316-100	1744	1/2	3/16	5/32	0.015	0.012	100
TYVT9-916316-100	2632	9/16	3/16	3/16	0.015	0.012	100
TYVT9-58316-100	2425	5/8	3/16	7/32	0.015	0.012	100
TYVT9-51614-100	595	5/16	1/4	1/32	0.017	05	100
TYVT9-3814-100	640	3/8	1/4	1/16	0.017	08	100
TYVT9-71614-100	1012	7/16	1/4	3/32	0.017	08	100
TYVT9-1214-100	1544	1/2	1/4	1/8	0.017	0.01	100
TYVT9-91614-100	2148	9/16	1/4	5/32	0.017	0.012	100
TYVT9-5814-100	2762	5/8	1/4	3/16	0.017	0.012	100
TYVT9-71638-100	635	7/16	3/8	1/32	0.018	08	100
TYVT9-1238-100	916	1/2	3/8	1/16	0.018	08	100
TYVT9-91638-100	1348	9/16	3/8	3/32	0.018	0.01	100
TYVT9-5838-100	1995	5/8	3/8	1/8	0.018	0.012	100
TYVT9-3438-100	985	3/4	3/8	3/16	0.018	0.012	100
TYVT9-7838-100	4550	7/8	3/8	1/4	0.018	0.012	100
TYVT9-34716-100	2448	3/4	7/16	5/32	0.018	0.012	100
TYVT9-5812-100	1152	5/8	1/2	1/16	0.02	08	100
TYVT9-111612-100	1704	11/16	1/2	3/32	0.02	0.01	100
TYVT9-3412-100	2352	3/4	1/2	1/8	0.02	0.012	100
TYVT9-7812-100	4304	7/8	1/2	3/16	0.02	0.012	100
TYVT9-112-100	6434	1	1/2	1/4	0.02	0.014	100
TYVT9-151658-100	2600	15/16	5/8	3/32	0.022	0.01	100
TYVT9-7858-100	3140	7/8	5/8	1/8	0.022	0.012	100
TYVT9-158-100	4848	1	5/8	3/16	0.022	0.012	100
TYVT9-134-100	3592	1	3/4	1/8	0.022	0.012	100
TYVT9532132-100	310	5/32	1/32	1/16	08	08	250

Ordering Example: TYVT9-7858-100, 100 feet of tubing, 7/8" OD, 5/8" ID, 1/8" wall, 90A Shore durometer, \$3140

Quick tubing changes are a snap with the OMEGAFLEX® FPU500 peristaltic pump, shown below. See Page L-25 for details





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters