


RUGGED PROCESS WATER IMMERSION HEATER WITH 2½ NPT FITTING

MTS-3 Series
Starts at
\$725




MTS-330E2/480V/3P, \$975, shown smaller than actual size.




MTS-360A/480V/3P, \$875, shown smaller than actual size.

- ✓ Stainless Steel Wetted Construction
- ✓ 120, 208, 240, 480V; 1 and 3-Phase Power
- ✓ Reliable Heater Design
- ✓ General Purpose Enclosure, NEMA 1 (IP00) Rated and UL Listed



Dimensions: cm (in)



Please Note: This immersion heater should be used with an approved temperature control device to ensure safe operation. See Section P for our selection of process controllers.

CAUTION AND WARNING!
Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel.

 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)				E1 Gen. Purpose Enclosure ¹			E2 Moist-/Explos-Res. Enc. ²		
kW	W/in ²	No. Htg. Elem.	Dim. B cm (in)	Model No.	Price	Wt. kg (lb)	Model No.	Price	Wt. lb (kg)
3	51	3	17 (6 ⁷ / ₈)	MTS-330A/**/***	\$725	2 (5)	MTS-330E2/**/***	\$975	4 (8)
4.5	48	3	28 (10 ⁷ / ₈)	MTS-345A/**/***	800	3 (6)	MTS-345E2/**/***	1050	4 (9)
6	48	3	43 (16 ⁷ / ₈)	MTS-360A/**/***	875	3 (6)	MTS-360E2/**/***	1100	4 (9)
7.5	53	3	49 (18 ¹ / ₁₆)	MTS-375A/**/***	925	3 (6)	MTS-375E2/**/***	1159	4 (9)
9	47	3	61 (24)	MTS-390A/208V/**/***	1010	3 (7)	MTS-390E2/**/***	1250	5 (10)
12	46	3	81 (31 ⁷ / ₈)	†MTS-3120A/208V/**/***	1150	4 (9)	†MTS-3120E2/**/***	1400	5 (12)
15	46	3	101 (39 ³ / ₈)	†MTS-3150A/208V/**/***	1300	5 (10)	†MTS-3150E2/**/***	1550	6 (13)
18	51	3	118 (46 ⁷ / ₈)	†MTS-3180A/208V/**/***	1400	5 (12)	†MTS-3180E2/**/***	1650	7 (15)

¹ Designate voltage: insert "120" for 120 Vac, "208" for 208 Vac, "240" for 240 Vac or "480" for 480 Vac.

² Designate voltage: insert "208" for 208 Vac, "240" for 240 Vac or "480" for 480 Vac.

³ Add suffix "3P" to the model number for 3-phase power, no extra charge (not available for 120 V models).

¹ Heaters with general purpose enclosures are UL listed and CSA certified except models with † (exceed 48 amps).

² Heaters with moisture-resistant/explosion-resistant enclosures are CSA NRTL/C certified and are not intended for use in hazardous areas, except models with † (exceed 48 amps).

Ordering Example: MTS-330A/480V, 3 kW heater powered by 1-phase 480 Vac, \$725.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters