



Economical pH, ORP, Conductivity and TDS Testers

CDH-5021 Series

- ✓ Economical
- ✓ Easy-to-Use
- ✓ Electrode Extends to 80 mm (3.1")

The CDH-5021, CDH-5022, PHH-5012, ORP-5041 and TDH-5031 are easy to use. These units feature a telescoping electrode which extends to 80 mm (3.1"). These kits are supplied with a carrying case, battery, calibration solution, and complete instructions.



All products shown smaller than actual size. Carrying case, battery, screw driver, calibration solution and operation instructions included.

To Order

Model No.	CDH-5021	CDH-5022	TDH-5031	PHH-5012	ORP-5041
Range	10 to 9990 μ S/cm	0 to 999 μ S/cm	10 to 9990 ppm	0 to 14.0 pH	\pm 999 mV
Resolution	10 μ S/m	1 μ S/m	10 ppm	0.02 pH	1 mV
Accuracy	\pm 1%FS	\pm 1%FS	\pm 1%FS	\pm 0.01 pH @ 25°C	\pm 5%FS
ATC	Yes (0 to 50°C)	Yes (0 to 50°C)	Yes (0 to 50°C)	Yes (0 to 50°C)	No
Power (Battery, included)	9V	9V	9V	1.55V 3 required	9V
Size	Meter: 152 x 40 x 34 mm (6 x 1.6 x 1.3"); carrying case: 165 x 100 x 40 mm (6.5 x 3.9 x 1.6")				
Weight	120 g (4.2 oz) with battery (avg)				

Accessories

Model No.	Description
PH-BATT-3	1.55V replacement battery for PHH-5012, requires 3
MN1604	9V replacement battery for CDH-5021, CDH-5022, TDH-5031, ORP-5041, requires 1

Comes complete with carrying case, battery, screwdriver, calibration solution and operator's manual. ORP-5041 supplied with carrying case, battery, and operator's manual

Ordering Examples: PHH-5012, pH tester. ORP-5041, ORP tester.

Order Online

omega.com

Over 100,000 Products Available!

To download information and to order pH Field and Lab Instrument products online, visit omega.com