

LOW-RANGE REMOTE PLATFORM SCALES

HIGH ACCURACY FOR PARTS COUNTING

LSC7000 Series
Capacities from 2 to 220 lb
(1 to 91 kgf)

All Ranges
\$495



- ✓ 1 Part in 5000 Accuracy
- ✓ Heavy-Duty Construction
- ✓ In-Line Weighing and Checkweighing
- ✓ Parts Counting or Weighing
- ✓ Sample or Bulk Scale for Counting Systems
- ✓ General Purpose Weighing Applications

Sustained accuracy and long life are built into every LSC7000 Series remote platform scale. Their clean, durable design makes these scales ideal for weighing or counting applications. The 2 and 5 lb ranges have a 203 x 203 mm (8 x 8") aluminum cover and a rugged fabricated construction. Ranges 10 lb and up have 305 x 356 mm (12 x 14") stainless steel covers and a rugged cast structure. Both structures are designed to give years of accurate, trouble-free service.



LSC7000-2, \$495, shown much smaller than actual size.

LSC7000-100, \$495, shown much smaller than actual size.

See Section Y for a Selection of Scientific, Technical, and Reference Books Available from omega.com

SPECIFICATIONS

Output: 1 mV/V 10 lb ranges, 2 mV/V all other ranges

Excitation: 15 V max

Linearity: 0.01%

Hysteresis: 0.02%

Connection: 3 m (10') cable

Dimensions:

203 x 203 mm (8 x 8")

305 x 356 mm (12 x 14")

Shipping Weight:

8 x 8": 3.7 kgf (8 lb)

12 x 14": 8 kgf (18 lb)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

ALUMINUM PLATFORM—FABRICATED CONSTRUCTION

MODEL NO.	PRICE	CAPACITY		PLATFORM SIZE	COMPATIBLE METERS*
LSC7000-2	\$495	2 x 0.0002 lb	1 x 0.0001 kgf	8 x 8" AL	DP41-S, WM7400 and WM7600
LSC7000-5	495	5 x 0.0005 lb	2.3 x 0.0002 kgf	8 x 8" AL	DP41-S, WM7400 and WM7600

STAINLESS STEEL PLATFORM—CAST CONSTRUCTION

LSC7000-10	\$495	10 x 0.001 lb	4.5 x 0.0005 kgf	12 x 14" SS	DP41-S, WM7400 and WM7600
LSC7000-20	495	20 x 0.002 lb	9.1 x 0.001 kgf	12 x 14" SS	DP41-S, WM7400 and WM7600
LSC7000-50	495	50 x 0.005 lb	22.7 x 0.002 kgf	12 x 14" SS	DP41-S, WM7400 and WM7600
LSC7000-100	495	100 x 0.01 lb	45 x 0.005 kgf	12 x 14" SS	DP41-S, WM7400 and WM7600
LSC7000-200	495	200 x 0.02 lb	91 x .01 kgf	12 x 14" SS	DP41-S, WM7400 and WM7600

Comes complete with operator's manual.

* See section D for compatible meters.

Ordering Examples: LSC7000-5, 8 x 8" aluminum remote platform scale with 5 lb range, \$495.

LSC7000-100, 12 x 14" stainless steel remote platform scale with 7100 lb range, \$495.

LOAD CELLS



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters