

BOLT SENSORS WITH MOUNTING WASHERS

STANDARD AND METRIC MODELS

To Order					
S Z			M D L	M D L	M B L M R S**
	LB		S R D ENDS	R D	
S D RD M D LS					
1/4"	2000	8897	/901-1/4-2K	-	DP41-S, DP25B-S, DPiS
1/4"	5000	22,242	L 901-1/4-5K	-	DP41-S, DP25B-S, DPiS
3/8"	10,000	44,484	L 901-3/8-10K	-	DP41-S, DP25B-S, DPiS*
1/2"	30,000	133,452	L 901-1/2-30K	L 911-1/2-30K	DP41-S, DP25B-S, DPiS*
5/8"	50,000	222,420	L 901-5/8-50K	L 911-5/8-50K	DP41-S, DP25B-S, DPiS*
3/4"	65,000	289,146	L 901-3/4-65K	L 911-3/4-65K	DP41-S, DP25B-S, DPiS*
1 1/2"	100,000	444,840	L 901-1.5-100K	-	DP41-S, DP25B-S, DPiS*
M R M D LS					
6 mm	2248	10,000	L M901-6-10Kn	-	DPiS, DP41-S, DP25B-S
6 mm	4496	20,000	L M901-6-20Kn	-	DPiS, DP41-S, DP25B-S
10 mm	11,240	50,000	L M901-10-50Kn	-	DPiS, DP41-S, DP25B-S
13 mm	29,225	130,000	L M901-13-130Kn	L M911-13-130K	DPiS, DP41-S, DP25B-S
16 mm	44,962	200,000	L M901-16-200Kn	L M911-16-200K	DPiS, DP41-S, DP25B-S
19 mm	67,443	300,000	L M901-19-300Kn	L M911-19-300K	DPiS, DP41-S, DP25B-S*
38 mm	112,405	500,000	L M901-38-500Kn	-	DPiS, DP41-S, DP25B-S*

(6625

02(12.	D S R
01F10-6	Mating connector for LC911/LCM911 series load cells

Comes complete with 2-point NIST-traceable calibration and 59 kΩ shunt data. * 4-digit meter. ** Visit us online for compatible meters.

Ordering Examples: LC901-3/8-10K, 10,000 lb capacity bolt sensor for a 3/8" diameter bolt, with stripped ends on the leads.

LCM901-10-50KN, 50 kN capacity bolt sensor for 10 mm bolt, with stripped ends on the leads.

LC911-1/2-30K, 30,000 lb capacity bolt sensor for a 1/2" diameter bolt with a connector installed on the cable. PT01F10-6P, mating connector (sold separately).

LCM911-13-130KN, 130 kN capacity bolt sensor for 13 mm bolt with a connector installed on the cable. PT01F10-6P, mating connector (sold separately).