


Flexible Molded RTD Surface Sensors

- ✓ Flexible Sensors Mount to Any Shape
- ✓ Temperature Range: -50 to 200°C
- ✓ Precision 100 Ω, Class “A” DIN Platinum Element
- ✓ Sensors Have Adhesive Back for Easy Mounting

- ✓ Available in Two Configurations
- ✓ Stripped Leads Standard, Connector Options Available
- ✓ PFA Insulated Cables
- ✓ 4-Wire Configuration Standard

SA2C-RTD Series



To Order			
Model Number	Resistance	Number of Wires	Wire Length
SA2C-RTD-3-100-A-40	100 Ω, Class “A” DIN Platinum	4	1 m (40")
SA2C-RTD-3-100-A-80	100 Ω, Class “A” DIN Platinum	4	2 m (80")
SA2C-RTD-3-100-A-120	100 Ω, Class “A” DIN Platinum	4	3 m (120")
SA2F-RTD-3-100-A-40	100 Ω, Class “A” DIN Platinum	4	1 m (40")
SA2F-RTD-3-100-A-120	100 Ω, Class “A” DIN Platinum	4	3 m (120")

Options: For longer cable lengths, change “-120” in model number to length needed, per foot, for additional cost. For miniature connectors add “-MTP” to model number for an additional cost. For a TA3F audio connector, add “-TA3F” to model number for an additional cost.

Ordering Examples: SA2C-RTD-3-100-A-80, 4-wire 100 Ω, Class “A” element and 80" of lead wire.
SA2F-RTD-3-100-A-120, 4-wire, 100 Ω, Class “A” element with 120" of lead wire.