

Single J/K/T Input Thermocouple Thermometer



HH-25U



HH-25U shown smaller than actual size.

The HH-25U handheld thermocouple thermometers feature Type K, J, T thermocouple inputs and are available in single input models. The HH-25U is a single-input model that has an auto range resolution of 0.1 or 1°. are °C/°F switchable, and maximum/Minimum reading/display hold functions and low battery indicator. Offered at an economical price.

- ✓ Auto Power-Off with Disable Feature (15 Minutes)
- ✓ Single Thermocouple Input
- ✓ Large LCD Screen
- ✓ Data Hold Function Freeze Readings on Display.
- ✓ Maximum/Minimum Record for Each Power on Cycle
- ✓ °C or °F Select Function
- ✓ Low Battery Indicator

Specifications

Input: Single K/J/T
Temperature Range K: -200 to 1370°C (-328 to 2498°F)
Resolution (K): 0.1°C (0.1°F), over 1000°C 1°C/1°F
Accuracy (K): ±(0.1% rdg + 0.5°C) for -50 to 1370°C; others ±(0.1% rdg + 2°C)
Temperature Range J: -80 to 760°C (-112 to 1400°F)
Accuracy (J): ±1% of rdg + 1°C/2°F
Temperature Range T: -80 to 400°C (-112 to 752°F)

Accuracy (T): ±1% of rdg + 1% 200 to 400°C, others ±0.4% rdg + 0.6 °C/1.2°F

Temperature Coefficient: 0.1 times the applicable accuracy specification per °C from 0 to 18°C and 28 to 50°C (32 to 64°F and 82 to 122°F)

Function: Max/Min. hold

Power: 9V battery

Dimensions: 159 L x 55 W x 38 D mm (6.25 x 2.16 x 1.49")

Weight: 170 g (6 oz)

Operating Temperature: -10 to 50°C (14 to 122°F)

To Order

Model No.	Description
HH-25U	Single J/K/T input thermocouple thermometer
Accessory	
SC-25U	Carrying case

Comes complete with thermometer, 9V Battery, and operator's manual.

Thermocouples Sold Separately – See Omega Thermocouple Selection for Type J, K, or T thermocouples.