NON-METALLIC FIBERGLASS FREE STANDING ENCLOSURES

NEMA 4X (IP66) SINGLE AND DOUBLE DOOR ELECTRICAL CABINETS

OM-AMFS Series









- Insulates and Houses Electrical and Electronic Controls. **Instruments and Components Indoors or Outdoors**
- Suited for Higher Temperatures or Corrosive Environments
- Protect from Dirt. Dust. Oil and Water
- UL 94 Flammability Rating and **UV Stabilized for Outdoor Use**
- Optional Sub-Panels

CONSTRUCTION

- Fiberalass Reinforced Polvester Formulation
- One-Piece Body Construction for Dimensional Stability
- Soft, Self-Gripping Gasket **Compressed Over the Flange for** NEMA 4X (IP66) Rating
- Continuous 304 SS Hinge and 3 Point Latching Handle with Padlocking Handle
- Heavy Duty Stainless Steel Lifting Evebolts
- Molded-In Drip Shield

OM-AM722525FS single door free standing electrical cabinet.





Both models shown much smaller than actual size.

OM-AM724925FS double

door free standing electrical cabinet.

OM-AM FS Series non-metallic fiberglass electrical cabinets are designed to insulate and protect electrical and electronic controls, instruments and components in both indoor and outdoor applications and are especially well suited for higher temperatures and corrosive environments. These NEMA 4X (IP66) fiberglass electrical cabinets have a 3 point handle with padlocking provisions and a continuous 304 SS hinge.

SPECIFCATIONS


Service Temperature Rating: -370 to 130°C (-350 to 266°F)


STANDARDS:

UL Types: 1,4, and 4x CSA Types: 1,4, and 4x **NEMA Types:** 1,4, and 4x

IEC Type: IP66







Dimensions: mm (inch)

Model Number	D	Е	F	Н	J	K	L	М	N	Р	Q	R
OM-AM722525FS	1829	635	622	552	1597	524	1403	489	702	311	1676	584
	(72)	(25)	(24.50)	(21.75)	(62.88)	(20.63)	(55.25)	(19.25)	(27.63)	(12.25)	(66)	(23)
OM-AM724925FSDD	1829	1245	622	1149	1597	542	1403	489	702	127	1676	584
	(72)	(49)	(24.50)	(45.25)	(62.88)	(20.63)	(55.25)	(19.25)	(27.63)	(5)	(66)	(23)

To Order							
ENCLOSURES MODEL NO.	HEIGHT	WIDTH	DEPTH	CA MODEL NO.	RBON STEI HEIGHT	EL SUB-P WIDTH	ANELS DESCRIPTION
OM-AM722525FS	72"	25"	26"	OM-P7225CS	57"	21"	For free standing single door enclosure
OM-AM724925FSDD	72"	49"	26"	OM-P7249CS	57"	21"	For free standing double door enclosure (2) included

ACCESSORY

MODEL NO.	DESCRIPTION
OM-AMPRINTPOCKET	Print pocket with adhesive tape 238 H x 264 W x 27 mm D (9.375 x 10.375 x 1.045")

Ordering Example: OM-AM724925FSDD, free standing fiberglass electrical cabinet, 72 x 49 x 26", and **OM-P7249CS,** carbon steel sub-panels (2 pcs.).