



4 pt. 110VAC In , 4 pt. 110VAC Out Module

EZIO-4ACI4ACO



Re-Order from
Omegamation™
 1-888-55-66342
 1-888-55-OMEGA
 omegamation.com

Terminal Block
 300 Volt/10 Amp/
 14AWG UL Rating

Module Specifications			
AC Power Supply Specs	Voltage Range		
AC Input Specs	Number of Inputs	4	
	Input Voltage Range	70-132 VAC	
	AC Frequency	47-63 Hz	
	Peak Voltage	180 Volt	
	Input Current	0.5mA @ 110 VAC	
	Maximum Input Current	0.6mA @ 132 VAC	
	Input Impedance	200K	
	ON Voltage Level	70 VAC	
	OFF Voltage Level	40 VAC	
	OFF to ON Response	< 10ms	
	ON to OFF Response	< 10ms	
	Status Indicators	Red LED for each input	
	Commons	1 Common	
	Fuse	No fuse	
	Base Power Required (3.3V)	10mA for all 4 on	
	Optical Isolation	2500 Volt	
	Wires	1 of 14 AWG, 2 of 18 AWG, 4 of 22 AWG	
	AC Output Specs	Number of Output Points	4
		Number of Commons	1
Output Voltage Range		20-132 VAC	
Peak Voltage		180 Volt	
ON Voltage Drop		1.2 V @ 1A	
Maximum Current		1.2 A @ 25°C, 0.8A @ 50°C for each output	
Maximum Leakage Current		1mA @ 132 VAC	
Maximum Inrush Current		38Amps for 16.6ms	
Minimum Load		15mA	
OFF to ON Response		max 1/2 cycle	
ON to OFF Response		max 1/2 cycle	
Fuse		No fuse	
Base Power Required (3.3V)		35mA for all 4 on	
Optical Isolation		2500 Volt	
Wires		1 of 14 AWG, 2 of 18 AWG, 4 of 22 AWG	

Pinout Information	
Pin No.	EZIO-4ACI4ACO
1	Input(1)
2	Input(2)
3	Input(3)
4	Input(4)
5	AC_Common
6	Output(1)
7	Output(2)
8	Output(3)
9	Output(4)
10	AC_Common
11	Not Connected

