

OS-310-501 QUICK Start Guide

Battery Installation



1. Locate the notches on the side of the unit's handle and pull the front of the handle forwards as shown above.



2. Attach a 9V battery (provided) to the black connector inside. The battery should snap into place. Swing the front of the handle back upwards to close the unit.

Note: Positive side of the battery has a "+" mark and negative side has a "-" mark on the battery label.

How to turn on the unit

- Press the trigger of device to power on

Quick Measurement

- Point thermometer at a surface
- Pull and hold the trigger to begin scanning
- Release the trigger to stop scanning
- The data will be held for 20 seconds, and then the unit will power off

Switch between Celsius and Fahrenheit


The default setting for the temperature unit is in Celsius. Please follow the below steps to change the temperature units to Fahrenheit.

- Press the °C °F Button
- You should now see the temperature displayed in °F (Fahrenheit)



Field of View

- This unit has a distance ratio of 50:1
- When measuring a surface 50 cm away, a 1 cm area will be measured.



Contact Information

If you need technical support, please call 1-888-826-6342.