


Heavy Duty Probes

- ✓ Each Probe Comes Standard with SMPW Miniature Connector
- ✓ Six Rugged Probe Styles Available in J, K and E Calibrations
- ✓ 1.8 m (6') PFA Coated 22 AWG Stranded Lead Wires
- ✓ Beaded Wire Probe Has Glass-on-Glass Insulation with Stainless Steel Overbraid [1.8 m (6')]
- ✓ Optional Extension Handle with 100, 300, 600 mm (4, 12 or 24") L
- ✓ Black Anodized Aluminum Handle on Handle Probes



Discount Schedule		
1-10 Units.....	Net 100 -499.....	30%
11-24 Units.....	10% 500 and up.....	25%
25-99 Units.....		20%

Also Available

Probes trimmed to 3.85 Ω
 For use with analog pyrometers that require 3.85 Ω lead resistance, the SP series heavy duty probes are available with lead lengths trimmed to 3.85 Ω . To order, change the **6** in the model number to **3.85**. No additional cost.

To Order		
Code	Model No.	Description
A	SP-RL-(*)-6	Curved surface probe
B	SP-GP(*)-6	General purpose probe
C	SP-BW-(*)-6	Beaded wire probe
D	SP-EH-4	100 mm (4") extension handle
	SP-EH-12	300 mm (12") extension handle
	SP-EH-24	600 mm (24") extension handle
E	SP-RA-(*)-6	Right angle probe
F	SP-SP-(*)-6	Surface probe
G	SP-NP-(*)-6	Needle probe

* Specify calibration: J, K, or E.
Ordering Example: SP-SP-J-6, Type J surface probe, with SMP connector.