

OMEGAMARKER® Custom Temperature Test Kit SELECT-A-KIT™

To Order Specify
OMEGAMARKER-Custom-
(List Ranges)

Kit includes 10 crayons,
holder, sharpener and case

- ✓ Mix and Match User Selected Temperatures
- ✓ From 38 to 399°C (100 to 750°F) Range
- ✓ Kit of 10 Crayons Includes Sharpener and Case
- ✓ Individual Holders for Each Crayon
- ✓ 63 mm (2½") Long Crayons



An Invaluable Tool
for the Person Who Has
to Measure Many Different
Temperatures.

The OMEGAMARKER® crayon is easy to use, but certain conditions must be considered. OMEGAMARKERS will not make any mark on smooth or rough surfaces in cold conditions. When rubbed hard on a rough surface, the OMEGAMARKER® gets ground and the powder is deposited on the surface which appears like a mark,

but will not adhere. The correct way of using OMEGAMARKERS would be to strike it across a pre-heated surface during the heating process, using proper safety precautions. While the temperature is below the rated temperature there will not be a visible mark, but as soon as the surface reaches the rated temperature of the marker, at

the point of contact the marker will melt and make a visible mark on the surface. This is an indication that the surface has reached the rated temperature of the OMEGAMARKER®.

The crayons are suitable for testing most surfaces. The crayons indicate temperatures from 38 to 399°C (100 to 750°F) and are accurate to within ±1%. Each crayon is 63 mm (2½") long.

Choose 1 or More of These Temperatures—Total of 10 Crayons—Any Combination of °C and °F

Deg. F	Deg. C	Deg. F	Deg. C	Deg. F	Deg. C
100	38	263	128	450	232
109	43	269	132	463	239
119	48	275	135	475	246
125	52	288	142	488	253
150	66	294	146	500	260
163	73	300	149	525	274
169	76	306	152	550	288
175	79	313	156	575	302
182	83	325	163	600	316
188	87	344	173	650	343
200	93	350	177	700	371
213	101	363	184	750	399
219	104	375	191		
225	107	388	198		
250	121	400	204		
256	124	413	212		

For Pricing and Details
Visit us Online

