

SSDH and SHDH Series Heavy Duty Drum Heater Installation Instructions

SSDH and SHDH Series Heavy Duty Drum Heater Installation Instructions outline the steps necessary to install a 55 gallon or 30 gallon heavy duty drum heater.

Step 1

The drum heater should be positioned in the center of the drum if it is on its side in a cradle; on the lower third if it's sitting upright. This surface should be free of any weld splatter, rust flakes, dirt or oil. Clean the surface area with acetone or a solvent to insure tight contact and eliminate the chance of damage to the silicone heater.


Step 2

Place the heater around the drum and fasten with the spring included.

Step 3

Turn the temperature adjustment dial counter-clockwise to the off position. Connect the heater to a 3-prong electric receptacle. DO NOT use a standard 2-prong receptacle due to the self-grounding requirements of the heater. Using a certified 3-prong plug will alleviate static charges from building up and causing potential fire hazards. Set the temperature adjustment dial to the appropriate setting.

NOTE: SSDH & SHDH Series Drum Heaters are not approved for and should not be used in any hazardous classified area.



(Cradle not included)

OMEGALUX™

An OMEGA Technologies Company

One Omega Drive, Box 4047
Stamford, Connecticut 06907-0047

Call OMEGALUX Toll Free*

1-800-872-4328
1-800-USA-HEAT

*In CT: (203) 359-1660
And International

CABLE: OMEGA
TELEX: 996404

EASYLINK: 62968934
FAX: (203) 359-7700

WARRANTY

OMEGALUX warrants this unit to be free of defects in materials and workmanship and to give satisfactory service for a period of 13 months from date of purchase. OMEGALUX Warranty adds an additional one (1) month grace period to the normal one (1) year product warranty to cover handling and shipping time. This ensures that our customers receive maximum coverage on each product. If the unit should malfunction, it must be returned to the factory for evaluation. Our Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGALUX, if the unit is found to be defective it will be repaired or replaced at no charge. However, this WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of being damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGALUX's control. Components which wear or which are damaged by misuse are not warranted. These include contact points, fuses, and triacs.

THESE UNITS ARE INHERENTLY DANGEROUS AND ARE INTENDED TO BE INSTALLED AND USED ONLY BY QUALIFIED PERSONNEL. NO WARRANTY EXTENDED HEREIN WILL APPLY IF SUCH UNIT IS INSTALLED OR USED BY UNQUALIFIED PERSONNEL. THERE ARE NO WARRANTIES EXCEPT AS STATED HEREIN. THERE ARE NO OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND OF FITNESS FOR A PARTICULAR PURPOSE. OMEGALUX IS NOT RESPONSIBLE FOR ANY DAMAGES OR LOSSES CAUSED TO OTHER EQUIPMENT, WHETHER DIRECT, INDIRECT, INCIDENTAL, SPECIAL OR CONSEQUENTIAL, WHICH THE PURCHASER MAY EXPERIENCE AS A RESULT OF THE INSTALLATION OR USE OF THE PRODUCT. THE BUYER'S SOLE REMEDY FOR ANY BREACH OF THIS AGREEMENT BY OMEGALUX OR ANY BREACH OF ANY WARRANTY BY OMEGALUX SHALL NOT EXCEED THE PURCHASE PRICE PAID BY THE PURCHASER TO OMEGALUX FOR THE UNIT OR UNITS OR EQUIPMENT DIRECTLY AFFECTED BY SUCH BREACH.

EVERY PRECAUTION FOR ACCURACY HAS BEEN TAKEN IN THE PREPARATION OF THIS MANUAL. HOWEVER, OMEGALUX NEITHER ASSUMES RESPONSIBILITY FOR ANY OMISSIONS OR ERRORS THAT MAY APPEAR NOR ASSUMES LIABILITY FOR ANY DAMAGES THAT RESULT FROM THE USE OF THE PRODUCTS IN ACCORDANCE WITH THE INFORMATION CONTAINED IN THE MANUAL.

OMEGALUX™

An OMEGA Technologies Company

One Omega Drive, Box 4047
Stamford, Connecticut 06907-0047

Call OMEGALUX Toll Free*

1-800-872-4328

1-800-USA-HEAT

*In CT: (203) 359-1660 CABLE: OMEGA EASYLINK: 62968934
And International TELEX: 996404 FAX: (203) 359-7700

Return Requests/Inquiries

Direct all warranty and repair requests/inquiries to OMEGA Customer Service Department, telephone number (203) 359-1660. BEFORE RETURNING ANY INSTRUMENT, PLEASE CONTACT THE OMEGA CUSTOMER SERVICE DEPARTMENT TO OBTAIN AN AUTHORIZED RETURN (AR) NUMBER. The designated AR number should then be marked on the outside of the return package.

To avoid processing delays, also please be sure to include:

- 1. Returnee's name, address, and phone number.**
- 2. Model and Serial numbers.**
- 3. Repair instructions.**

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. That way our customers get the latest in technology and engineering.

OMEGA® is a registered trademark of OMEGA ENGINEERING, INC.

OMEGALUX™ is a trademark of OMEGA ENGINEERING, INC.

© Copyright 1989 OMEGA ENGINEERING, INC. All rights reserved including illustrations. Nothing in this manual may be reproduced in any manner, either wholly or in part for any purpose whatsoever without written permission from OMEGA ENGINEERING, INC.