



# NORGREN EXCELON® MODULAR SYSTEM ACCESSORIES

## SYSTEM ACCESSORIES




- For use with Excelon 72, 73 and 74 Series Filters, Regulators and Lubricators



SERIES mm (in)	A	B	C	D	E	F	G	H
72	60 (2.36)	42 (1.65)	39 (1.54)	19 (0.73)	4 (0.16)	38 (1.50)	6 (0.24)	51 (2.01)
73	67 (2.64)	60 (2.36)	48 (1.89)	19 (0.75)	7 (0.28)	38 (1.50)	6 (0.24)	61 (2.40)
74	79 (3.11)	69 (2.72)	50 (1.97)	20 (0.79)	5 (0.20)	51 (2.01)	6 (0.24)	61 (2.40)

### Neck mounting brackets



SERIES mm (in)	J	K	L	M	N	P	R	S	T	V
72	8 (0.31)	49 (1.93)	38 (1.50)	64 (2.50)	30 (1.18)	24 (0.94)	-	6 (0.24)	8 (0.31)	15 (0.59)
73	17 (0.67)	64 (2.52)	38 (1.50)	70 (2.76)	38 (1.50)	38 (1.50)	25 (0.98)	7 (0.28)	-	-
74	24 (0.94)	89 (3.50)	52 (2.05)	86 (3.39)	56 (2.20)	35 (1.38)	23 (0.91)	7 (0.28)	-	-

# To Order

MODEL NO.	FILTERS							REGULATORS, FILTER/REGULATORS							LUBRICATORS					
	F72		F73			F74		B72, R72		B73, R73			B74, R74		L72		L73		L74	
	PORT							PORT							PORT					
	1/4"	3/8"	1/4"	3/8"	1/2"	3/8"	1/2"	1/4"	3/8"	1/4"	3/8"	1/2"	3/8"	1/2"	1/4"	3/8"	1/4"	3/8"	1/2"	3/8"
<b>WALL BRACKETS</b>																				
OM-AIR-4224-50	•							•							•					
OM-AIR-4424-50				•							•						•			
OM-AIR-4324-50						•							•							•
OM-AIR-4323-51																				•
<b>QUICKMOUNT PIPE ADAPTORS</b>																				
OM-AIR-4215-02	•							•							•					
OM-AIR-4215-03		•							•							•				
OM-AIR-4315-01			•							•							•			
OM-AIR-4315-02				•		•					•		•				•		•	
OM-AIR-4315-03					•		•					•		•				•		•
<b>QUICKMOUNT PIPE ADAPTORS METRIC G THREADS</b>																				
OM-AIR-4215-05	•							•							•					
OM-AIR-4215-06		•							•							•				
OM-AIR-4315-09			•							•							•			
OM-AIR-4315-10				•		•					•		•				•		•	
OM-AIR-4315-11					•		•					•		•				•		•
<b>QUICKCLAMP</b>																				
OM-AIR-4214-51	•							•							•					•
OM-AIR-4314-51				•		•					•		•				•		•	
<b>QUICKCLAMP WITH WALL BRACKET</b>																				
OM-AIR-4214-52	•							•							•					
OM-AIR-4213-89		•							•							•				
OM-AIR-4313-50			•			•					•		•				•		•	
OM-AIR-4314-52				•		•				•			•				•		•	
<b>REPLACEMENT ELEMENTS</b>																				
OM-AIR-5925-09																				
OM-AIR-4444-01																				
OM-AIR-4344-01																				
<b>NECK MOUNTING BRACKETS</b>																				
OM-AIR-74316-50								•												
OM-AIR-4461-50											•									
OM-AIR-4368-51																				
<b>PANEL NUT</b>																				
OM-AIR-4248-89								•												
OM-AIR-5191-88											•									
OM-AIR-4348-89																				
<b>GAGES</b>																				
OM-AIR-18-013-212								•												
OM-AIR-18-013-209											•		•							
<b>GAGES METRIC ISO R THREAD</b>																				
OM-AIR-18-013-989								•												
OM-AIR-18-013-269											•		•							
<b>REMOTE FILL KIT</b>																				
OM-AIR-5335-50																				•
<b>QUICK FILL NIPPLE</b>																				
OM-AIR-18-011-024																			•	•
<b>TAMPER RESISTANT SNAP-ON CAP FOR LUBRICATOR SIGHT FEED DOME#</b>																				
OM-AIR-4050-89															•		•		•	
<b>LEVEL SWITCH</b>																				
OM-AIR-18-023-610																				•

Ordering Example: OM-AIR-4224-50, Wall bracket.