



REVISIONS						
LTR	ECN	DESCRIPTION	DATE	DR	CHK	ENG
-	XXXX	INITIAL RELEASE	1/16/2013	SV	RM	SV
A	6749	REMOVED NONCONDUIT WIRING & PARAMETERS, DELETED NOTES 1 & 4	7/18/13	SV	RM	SV
B	6904	CHANGED APPROVAL TO GASES ONLY; TA WAS 85	10/15/2014	SV	KM	SV
C	7140	UPDATED TO OMEGA TITLE BLOCK WAS "C" SIZE CHANGED SERVICE TEMPERATURE TO 75 WAS 80	3/4/2015	RM	KM	SV





Hazardous (Classified) Location
 Rated Non-Incendive
 Class I Division 2 Groups A, B, C, D (US & CANADA) 
 T4, Ta = -40 TO 75 ° C



- NOTES:**
1. Rigid Conduit, Associated Apparatus (Barrier) is not required.
 2. Class I, DIV 2 wiring practices permitted by the NEC (NFPA 70) and CEC Part 1 (C22.1).

THIS IS A CONTROLLED DRAWING AND MAY NOT BE CHANGED WITHOUT FACTORY MUTUAL'S AUTHORIZATION.

SIMILAR P/N: *CONFIDENTIAL- THIS DRAWING IS PROPRIETARY PROPERTY OF OMEGA ENGINEERING, INC. IT IS SUPPLIED IN CONFIDENCE FOR A PARTICULAR LIMITED PURPOSE ONLY AND RECIPIENT HEREOF IS NOT AUTHORIZED TO REPRODUCE THIS DRAWING NOR MAKE THE STRUCTURE DISCLOSED THEREIN NOR DISCLOSE ITS CONTENTS TO OTHERS NOR USE IT IN ANY OTHER WAY WHETHER IN WHOLE OR PART UNLESS PRIOR WRITTEN APPROVAL THEREFORE IS OBTAINED FROM OMEGA*	TOLERANCES	63/ MAX.	USED ON			 NI INSTALLATION DWG FOR FM APPROVED PRESSURE/LOAD TRANSMITTERS
	DEC.XX±.01	FRAC±1/64	DR	S VICARS	1/16/13	
	.XXX±.005	ANG ±1°	CHK	R MILLER	2/27/13	
	REMOVE BURRS, BREAK EDGES		APPD	S VICARS	05/1/16/13	
ALL DIMENSIONS IN INCHES	CAGE CODE:			09AL6		
MATERIAL:	PROJECTION					
HEAT TREAT:	A012841 REV. C			ITEM NO.	DOC NO.	
				A031432	REV C	
SCALE: NONE				SHEET 2 OF 2		