Process Measurement and Control **OMEGA...** Your Source for

TEMPERATURE

- Probes, Connectors, Panels & Assemblies Ly Thermocouple, RTD & Thermistor
- 国 Wire: Thermocouple, RTD & Thermistor 国 Calibrators & Ice Point References 国 Recorders, Controllers & Process Monitors 国 Infrared Pyrometers

PRESSURE/STRAIN FORCE

- 臣 Transducers & Strain Gages 臣 Load Cells & Pressure Gauges 臣 Displacement Transducers 臣 Instrumentation & Accessories

- FLOW/LEVEL

 B Rotameters, Gas Mass Flowmeters & Flow Computers
 - 译 Air Velocity Indicators 译 Turbine/Paddlewheel Systems 译 Totalizers & Batch Controllers

- pH/CONDUCTIVITY 译 pH Electrodes, Testers & Accessories 译 Benchtop/Laboratory Meters 译 Controllers, Calibrators, Simulators &
- B Industrial pH & Conductivity Equipment

DATA ACQUISITION

P Data Acquisition and Engineering Software

Ç

- [四 Communications-Based Acquisition [] Plug-in Cards for Apple, IBM & Systems
 - Compatibles
- L Datalogging Systems
 Recorders, Printers & Plotters

Ç

Ç

Ç

- Cartridge & Strip Heaters HEATERS

 E' Heating Cable

 E' Cartridge & Strip Heat

 E' Immersion & Band He

 E' Flexible Heaters

 E' Laboratory Heaters
- Immersion & Band Heaters

ENVIRONMENTAL MONITOR-

Ç

G

Ç

- Metering & Control Instrumentation
- Industrial Water & Wastewater ING AND CONTROL

 E Metering & Control Instrumen

 E Refractometers

 F Pumps & Tubing

 E Air, Soil & Water Monitors

 I Industrial Water & Wastewater
- [] pH, Conductivity & Dissolved Oxygen Instruments

83.N3 **PHCN-410** DE pH Controller

OF OMEGA" | Operator's Manual

M1811/0694



Servicing USA and Canada: Call OMEGA Toll Free

Canada

Stamford, CT 06907-0047 USA One Omega Drive, Box 4047 Telephone: (203) 359-1660 FAX: (203) 359-7700

Telephone: (514) 856-6928 Laval (Quebec) H7L 5A1 FAX: (514) 856-6886 976 Bergar

Customer Service: 1-800-622-2378 / 1-800-622-BEST**
Engineering Service: 1-806-872-9436 / 1-800-USA-WHEN**
TELEX: 996404 EASYLINK: 62968934 CABLE OMEGA Sales Service: 1-800-826-6342 / 1-800-TC-OMEGA^{5M}

Servicing Europe: United Kingdom Sales and Distribution Center 25 Swaruington Road, Broughton Astley, Leicestershire LE9 6TU, England Telephone: 44 (0455) 285520 FAX: 44 (0455) 283912

Direct all warranty and repair requests/finquiries to the OMEGA ENGINEERING Customer Service Department.

Call toll free in the USA and Canada: 1-800-622-2378, FAX: 203-359-7811; International: 203-359-1660, FAX: 203-359-7807.

BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, YOU MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OUR CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

FOR WARRANTY. RETURNS, please have the fol- lowing information available BEFORE contacting OMEGA.

OMEGA.

I. P.O. number under which the product was PURCHASED.

- P.O. number under which the product was PURCHASED.
 Model and serial number of the product under
- warranty, and
 3. Repair instructions and/or specific problems you are having with the product.

repair/calibration,
2. Model and serial number of product, and
3. Repair instructions and/or specific problems you are having with the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering.

OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 1994 OMEGA ENGINEERING, INC. All rights reserved. This documentation may not be copied, photo-opied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without prior written consent of OMEGA ENGINEERING, INC.

pH Controller Operator's Manual PHCN-410

Section 1 1.1 1.2 1.3 1.4 1.4 1.5 Section 2 2.1 2.1	Section 1 Getting Started 1.1 Unpacking the Controller 1.1 1.2 Controller Description 1.3 1.3 Keypad Description 1.4 1.4 Front Panel Displays 1.4 1.5 General Information 1.4 2.1 Mounting the Controller 2.1 2.2 Wiring the Controller 2.3 2.3 Wiring the Controller 2.3 2.4 Connect at Power 2.3
Section 3	at at

Section 4	Section 4 Operating the Controller
4.1	4.1 Entering PHCN-410 Hi/Lo Setpoints 4-1
	4.1.1 To Enter the Hi Setpoint Value4-1
	4.1.2 To Enter the Lo Setpoint Value4-1
4.2	4.2 Error Messages 4-2
Section 5	Section 5 Specifications

Section 5.1 Specifications......5-1

Getting Started

1.1 Unpacking the Controller

•

Remove the Packing List and verify that you have received all equipment. If you have questions about the shipment, please call the OMEGA Customer Service Department at 1-800-622-2378 or (203) 359-1660. Upon receipt of shipment, inspect the container and equipment for any signs of damage. Note any evidence of rough handling in transit. Immediately report any damage to the shipping agent.



shipping material is saved for their examination. After examining and removing contents, save packing material in the event reshipment is necessary. The carrier will not honor any claims unless all

Ξ

Getting Started

1.2 Controller Description

The OMEGA® PHCN-410 pH controller is a microprocessor-based pH controller with automatic temperature compensation, a 4-digit LED display, two SPDT mechanical relays, and a fixed 4-20 mA output.




Figure 1-1. Front Panel Display



1.3 Keypad Description

The PHCN-410 features four keys for entering all set-up parameters and performing calibration. (Refer to Figure 1-1).

Use This Key:	To:
SET/TEMP	Select setpoint relay modes (Lo and Hi)
CAL/ENTER	Initiate calibration procedure using standard pH buffers 7.00, 4.01 or 10.01 to enter selected setpoint values
•	Select numerical position from right to left
•	Select number from 0-9

<u>-</u>3

1.4 Front Panel Displays

This Display: PH CAL

1.5 General Information

We recommend that you bench-test all equipment prior to installation. This requires wiring the equipment and checking relay and output functions as well as pH input (see section 2.2). This is also a good time to initially calibrate the pH electrode to the meter (see section 3).

Installing the Controller

2.1 Mounting the Controller

Refer to Figures 2-1 and 2-2 for panel cutout and meter dimensions.




Figure 2-1. Panel Cutout Dimensions




Figure 2-2. Meter Dimensions

2.2 Wiring the Controller

2.2.1 Connect ac Power

Connect ac power to the proper terminals (refer to Figure 2-3). "D3" is hot, "D2" is neutral, and "D1" is ground.For 220 Vac operation, "D4" is hot, "D2" is neutral, and "D1" is ground.




Figure 2-3. Rear Panel Connections

2

2.2.2 Making Input Connections

- . Connect the pH combination electrode to the BNC connector on the back of the unit.
- If using Automatic Temperature Compensation (ATC), connect the 100 ohm Pt RTD leads of the temperature probe to Terminals 1 and 2 (no polarity - see Figure 2-3).

The 100 ohm Pt RTD temperature probe can be separate from the pH electrode, built into the body of the pH electrode or (in selected models) built into the mounting assembly of the pH electrode.

If an ATC input is not provided to the meter, the temperature reading will default to 25°C. If the process temperature is constant, but not 25°C, a precision resistor can be used to simulate the appropriate temperature value to the unit. For example, if the control process runs at 0°C, a resistor with a value of 100 ohms can be wired to Terminals 1 and 2. The temperature display will show approximately 0°C. For a complete temperature versus resistance table, consult the OMEGA Temperature Measurement Handbook and Encyclopedia®.



The PHCN-410 features Automatic Temperature Compensation; however, the temperature value is not displayed.

2.2.3 Making Output Connections

For Hi and Lo Setpoint Relays:

Connect the proper load to the NO and COM terminals or the NC and COM terminals.

When the load is connected to the NO and COM, the relay is open until the setpoint is reached. When the load is connected to the NC and COM, the relay is closed until the setpoint is reached. The wiring configuration is application dependent.

The PHCN-410 has a fixed 4-20 mA output.

<u>e</u>
豆
S
‡
ing
stall
2

S
Ü
÷
0
7
_

Calibrating the pH Electrode

Calibrating the pH Electrode

Calibration of the electrode to the pH meter is essential for accurate periodically. The frequency of recalibration is system dependent. pH measurement. It is also necessary to recalibrate the electrode

The pH calibration procedure is as follows:

- 1. Connect the combination pH electrode and temperature compensation probe (if using ATC) to the meter (refer to Figure 2-3).
- Apply power to the instrument. ۲
- rinse the electrode with distilled water, and place it in standard pH Remove the electrode protector from the end of the pH electrode; buffer 7.00 solution. Press the CAL key. က

At this time the "CAL" annunciator light will appear. When the light goes off, the first point is calibrated. If "7-E" appears in the display, this means the pH buffer 7.00 was not used or the pH electrode has failed. ا

7

3

4. Remove the pH electrode from the pH buffer 7.00. Rinse the electrode with distilled water and place the electrode in standard pH buffer 4.01 or 10.01. Press the CAL Key.

At this time the "CAL" annunciator light will appear. When the light goes off, the slope is calibrated.

Operating the Controller

.

4.1 Entering PHCN-410 Hi/Lo Setpoints

4.1.1 To Enter the Hi Setpoint Value:

- Press the SET/TEMP keypad, until the Hi annunciator is lit on the front panel.
- ... Use the \blacktriangleleft and \blacktriangle keys to change the displayed value to the desired value.
 - 3. When the desired value is showing in the display, press the CAL/ENTER keypad to store this value into memory.

4.1.2 To Enter the Lo Setpoint Value:

- Press the SET/TEMP keypad, until the Lo annunciator is lit on the front panel.
- When the desired value is showing in the display, press the CAL/ENTER keypad to store this value into memory.

Operating the Controller

4.2 Error Messages

- 7-E The calibration standard 7.00 pH was not used or the pH electrode has failed.
- -- E The pH/mV value is over range.

Specifications

Two 12 Amp 120 Vac SPDT Mechanical Relays for High and Lo Setpoints 0.0 to 100.0°C, Automatic or Manual 100 Ohm Pt RTD for ATC or Manual pH 0.80" LED 4 Digit Display 110/220 Vac, 50/60 Hz Two Mechanical Relays 41 to 122°F (5 to 50°C) 0.00 to 14.00 pH 1.98 lbs. (0.9 Kg) ±0.01 pH 0.01 pH Temperature Compensation: Operating Temperature: pH Resolution: **Temperature:** Dimensions: Accuracy: Display: Weight Contact: **Control:** Power: Range:

,