



CDH-4X

CONDUCTIVITYSTIK™

INSTRUCTION
SHEET

M1358/1215


Shop online at omega.comSM e-mail: info@omega.com
For latest product manuals: omegamanual.info

GENERAL DESCRIPTION

The OMEGA CDH-4X Conductivitystik™ conductivity tester is an economical, portable handheld unit. The CDH-4X features large display numerics for easy reading, automatic temperature compensation, and a calibration trimmer. All readings are referenced to 25°C using a 2% per °C temperature coefficient. The CDH-4X reads out in microsiemens (μS) directly.

OPERATING PROCEDURE

1. Remove black protective cap.
2. Turn the CDH-4X on by the On/Off switch on top of the unit.
3. Dip the CDH-4X in solution up to the immersion level. Under no circumstances immerse the unit above the immersion level. Refer to Figure 1.
4. Stir gently and allow a few seconds for reading to stabilize.
NOTE: If this is the first time the unit is being used, it may require extra time for reading to stabilize.
5. Units are shipped factory calibrated; however, should calibration be required, immerse the unit in a standard solution of known value. The value of this solution should be close to that of the solution to be measured.* To calibrate the CDH-4X, adjust the calibration trimmer located on the reverse side with a small screwdriver until the LCD display matches the value of the standard solution.
6. To improve performance, clean the stainless steel electrodes periodically with a mild detergent or solution (i.e. alcohol) because particulates can build up. Rinse with distilled or de-ionized water.
7. To change batteries, pull out the battery case and replace batteries. Refer to Figure 2.
8. When not in use, switch off the instrument. Rinse electrode with distilled or de-ionized water and shake off excess water. Replace protective cap.



SPECIFICATIONS

RANGE:	1 to 199 μ S
RESOLUTION:	1 μ S
ACCURACY:	\pm 2% Full scale
ELECTRODES:	Stainless steel
OPERATING TEMPERATURE:	5 to 55°C, 41 to 131°F, Automatic temperature compensation using a precision thermistor with a 2% per °C temperature coefficient; readings referenced to 25°C.
BATTERY:	Four 1.5 V
BATTERY LIFE:	200 Hours
DIMENSIONS:	5.9" H X 1.26" W X 0.59" D (15 X 3.2 X 1.5 cm)
WEIGHT:	2.1 oz. (60 g.)

NOTE: OMEGA Engineering offers Conductivity Standard traceable to NIST. CDS-45 (45 μ S/cm); CDS-450 (450 μ S/cm); cds-1500 (1500 mS/cm); CDS-4500 (4500 μ S/cm).

Ω OMEGA® omega.com info@omega.com

Servicing North America:

U.S.A.: Omega Engineering, Inc., One Omega Drive, P.O. Box 4047, Stamford, CT 06907-0047 USA
Toll-Free: 1-800-826-6342 (USA & Canada only) Customer Service: 1-800-622-2378 (USA & Canada only)
Engineering Service: 1-800-872-9436 (USA & Canada only) Tel: (203) 359-1660 Fax: (203) 359-7700 e-mail: info@omega.com

For Other Locations Visit omega.com/worldwide

The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. **BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS).** The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

1. Purchase Order number under which the product was PURCHASED,
2. Model and serial number of the product under warranty, and
3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

1. Purchase Order number to cover the COST of the repair,
2. Model and serial number of the product, and
3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering. OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2015 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.