

1 YEAR  
WARRANTY

CE



# User's Guide



*Shop online at*

**omega.com<sup>®</sup>**

Ω OMEGA<sup>®</sup>

*omega.com*

*e-mail: info@omega.com*

*For latest product manuals:  
omegamanual.info*

ISO 9001  
CERTIFIED  
CORPORATE QUALITY  
STAMFORD, CT

ISO 9002  
CERTIFIED  
CORPORATE QUALITY  
MANCHESTER, UK

MADE IN TAIWAN

## HHG191 Magnetic Field Meter



**OMEGAnet® Online Service**  
**omega.com**

**Internet e-mail**  
**info@omega.com**

### **Servicing North America:**

**U.S.A.:** One Omega Drive, Box 4047  
ISO 9001 Certified Stamford, CT 06907-0047  
Tel: (203) 359-1660  
FAX: (203) 359-7700  
e-mail: info@omega.com

**Canada:** 976 Bergar  
Laval (Quebec) H7L 5A1, Canada  
Tel: (514) 856-6928  
FAX: (514) 856-6886  
e-mail: info@omega.ca

### **For immediate technical or application assistance:**

**U.S.A. and Canada:** Sales Service: 1-800-826-6342/1-800-TC-OMEGA®  
Customer Service: 1-800-622-2378/1-800-622-BEST®  
Engineering Service: 1-800-872-9436 1-800-USA-WHEN®

**Mexico:** En Español: (001) 203-359-7803  
FAX: (001) 203-359-7807  
e-mail: espanol@omega.com  
info@omega.com.mx

### **Servicing Europe:**

**Czech Republic:** Frystatska 184, 733 01 Karviná, Czech Republic  
Tel: +420 (0)59 6311899  
FAX: +420 (0)59 6311114  
Toll Free: 0800-1-66342  
e-mail: info@omegashop.cz

**Germany/Austria:** Daimlerstrasse 26, D-75392 Deckenpfronn, Germany  
Tel: +49 (0)7056 9398-0  
FAX: +49 (0)7056 9398-29  
Toll Free in Germany: 0800 639 7678  
e-mail: info@omega.de

**United Kingdom:** One Omega Drive, River Bend Technology Centre  
ISO 9002 Certified Northbank, Irlam, Manchester  
M44 5BD United Kingdom  
Tel: +44 (0)161 777 6611  
FAX: +44 (0)161 777 6622  
Toll Free in United Kingdom: 0800-488-488  
e-mail: sales@omega.co.uk

---

It is the policy of OMEGA Engineering, Inc. to comply with all worldwide safety and EMC/EMI regulations that apply. OMEGA is constantly pursuing certification of its products to the European New Approach Directives. OMEGA will add the CE mark to every appropriate device upon certification.

The information contained in this document is believed to be correct, but OMEGA Engineering, Inc. accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

**WARNING:** These products are not designed for use in, and should not be used for, human applications.

## Table of Contents

<u>1</u>	<a href="#">Introduction</a> .....	1
<u>2</u>	<a href="#">Application</a> .....	1
<u>3</u>	<a href="#">Features</a> .....	1
<u>4</u>	<a href="#">Identifying Parts</a> .....	2
<u>5</u>	<a href="#">Measurement Procedures</a> .....	2
<u>6</u>	<a href="#">Specifications</a> .....	4
<u>7</u>	<a href="#">Battery replacement</a> .....	4
<u>8</u>	<a href="#">Safety Precaution</a> .....	5
<u>9</u>	<a href="#">End of life</a> .....	5

# 1 Introduction

Safety precautions should be taken against electric appliances in places including medical institutions, schools and residential districts, where people usually stay for a long time, to prevent patients, babies and senior citizens from exposure to high electromagnetic waves.

An electromagnetic wave simply means the wave motion of the electromagnetic field (**EMF**).


The change in electric fields produces magnetic fields, and the change in magnetic fields can also generate electric fields. The fluctuation of correlation between each other is known as "electromagnetic waves", which is a form of energy similar to light and heat that can be transmitted either by radiation in the air or by an electric conductor.

It is suggested that rearrangements should be made in families and work locations where electromagnetic fields are detected the strongest in order to avoid prolonged exposure to excessive electromagnetic fields.

## 2 Application

- This meter is applied to measuring electromagnetic fields of extremely low frequency (**ELF**) of 30 to 300Hz.
- It is capable of measuring the electromagnetic field radiation intensity that is produced from electric transmission equipment, power line, microwave oven, air conditioner, refrigerator, computer monitor, video/audio device and so forth.
- The magnetic field unit is Tesla (T), Gauss (G), milli-Gauss (mG) or micro-Tesla ( $\mu$ T).
  - 1 T\_10,000 G
  - 1 G\_1,000 mG
  - 1  $\mu$ T\_10 mG

## 3 Features

- Switch between the display of micro-Tesla and milli-Gauss is available.
- Data hold (HOLD)\_maximum (MAX) Hold function.
- Range display(20, 200, 2000).
- Low battery detector "".
- Over load display "OL".

## 4 Identifying Parts



1. Sensor position.
2. LCD
3. Power on/off.
4. maximum hold button
5. Data hole button
6. mG unit select button
7.  $\mu$ T unit select button
8. Range select button
9. Battery cover.

## 5 Measurement Procedures

- Press **Power** power on.
- Select **Gauss** mG unit or **Tesla** T unit.
- Position the front (refer to Figure 1) of the meter to measure the electromagnetic waves. Try to change the measurement angle or position for obtaining the highest reading value (please refer to Figure 2 to 6).
- Read the measured value. The display of "OL" on the left highest position indicates there is an overload on the reading. Please press **Range** select a higher range for measurement again.
- Due to the environmental magnetic field factors, this magnetic field meter could display a reading value that is lower than 0.5mG prior to measuring. This is not a malfunction of the device.
- To permanently lock and keep the reading displayed on the LCD, press **Hold** press **Hold** to unlock.
- To retain the maximum value, press **Max** and the reading value displayed on the LCD will keep updating to the maximum value.



Figure 1



Figure 2



Figure 3



Figure 4



Figure 5



Figure 6

(\*1) Arrow pointing direction indicates the direction of the electromagnetic

- Figure 1 indicate the correct measurement direction of the electromagnetic wave.
- Figure 2,3, 4, 5 and 6 indicate the incorrect measurement direction of the electromagnetic wave.

## 6 Specifications

- **Display:** 3-1/2 digits LCD, maximum reading 1999.
- **Range:** 200/2000 mG, 20/200  $\mu$ T.
- **Resolution:** 0.1/1 mG or 0.01/0.1  $\mu$ T.
- **Frequency response:** 30Hz to 300Hz.
- **Sensor:** Single Axis
- **Accuracy:**  $\pm(2.5\%+6\text{dgt})$  at 50Hz/60Hz.
- **Over load:** LCD display "OL".
- **Sample rate:** 2.5 times per second.
- **Battery:** 9V NEDA 1604, IEC 6F22 or JIS 006P.
- **Battery life:** Approximate 100 hours.
- **Operating temperature & humidity:** 5\_ to 40\_, below 80% RH.
- **Storage temperature & humidity:** -10\_ to 60\_, below 70%.
- **Weight:** About 170g.
- **Dimensions:** 130(L)\*56(W)\*38(H)mm.
- **Accessories:** User's manual, 9V battery, Carrying case.

## 7 Battery replacement



### WARNING

If the symbol "  " appears on the LCD, please replace the battery immediately

- Turn off the instrument.
- Remove the battery cover
- Replace the battery.
- Install the battery cover.

## 8 Safety Precaution

- For cleaning the instrument use a soft dry cloth. Never use a wet cloth, solvents or water, etc..
- Operation Altitude: Up to 2000M.
- Operating Environment: Indoors use. This instrument has been designed for being used in an environment of pollution degree 2.

## 9 End of life



Caution: this symbol indicates that equipment and its accessories shall be subject to a separate collection and correct disposal





## WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

**OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.**

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

## RETURN REQUESTS/INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

1. Purchase Order number under which the product was PURCHASED,
2. Model and serial number of the product under warranty, and
3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

1. Purchase Order number to cover the COST of the repair,
2. Model and serial number of the product, and
3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering.

OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2007 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.

# Where Do I Find Everything I Need for Process Measurement and Control? **OMEGA...Of Course!** *Shop online at [omega.com](http://omega.com)*

## **TEMPERATURE**

- Thermocouple, RTD & Thermistor Probes, Connectors, Panels & Assemblies
- Wire: Thermocouple, RTD & Thermistor
- Calibrators & Ice Point References
- Recorders, Controllers & Process Monitors
- Infrared Pyrometers

## **PRESSURE, STRAIN AND FORCE**

- Transducers & Strain Gages
- Load Cells & Pressure Gages
- Displacement Transducers
- Instrumentation & Accessories

## **FLOW/LEVEL**

- Rotameters, Gas Mass Flowmeters & Flow Computers
- Air Velocity Indicators
- Turbine/Paddlewheel Systems
- Totalizers & Batch Controllers

## **pH/CONDUCTIVITY**

- pH Electrodes, Testers & Accessories
- Benchtop/Laboratory Meters
- Controllers, Calibrators, Simulators & Pumps
- Industrial pH & Conductivity Equipment

## **DATA ACQUISITION**

- Data Acquisition & Engineering Software
- Communications-Based Acquisition Systems
- Plug-in Cards for Apple, IBM & Compatibles
- Datalogging Systems
- Recorders, Printers & Plotters

## **HEATERS**

- Heating Cable
- Cartridge & Strip Heaters
- Immersion & Band Heaters
- Flexible Heaters
- Laboratory Heaters

## **ENVIRONMENTAL MONITORING AND CONTROL**

- Metering & Control Instrumentation
- Refractometers
- Pumps & Tubing
- Air, Soil & Water Monitors
- Industrial Water & Wastewater Treatment
- pH, Conductivity & Dissolved Oxygen Instruments