
# LDM80 Signal-Powered, Fiber-Optic Modem









## OMEGAnet<sup>™</sup> On-Line Service http://www.omega.com

Internet e-mail info@omega.com

#### **Servicing North America:**

USA:

One Omega Drive, Box 4047

ISO 9001 Certified

Stamford, CT 06907-0047

Tel: (203) 359-1660

FAX: (203) 359-7700

Canada:

976 Bergar

Laval (Quebec) H7L 5A1

Tel: (514) 856-6928

FAX: (514) 856-6886

#### For immediate technical or application assistance:

USA and Canada:

Sales Service: 1-800-826-6342 / 1-800-TC-OMEGA<sup>SM</sup>

Customer Service: 1-800-622-2378 / 1-800-622-BEST<sup>SM</sup>
Engineering Service: 1-800-872-9436 / 1-800-USA-WHEN<sup>SM</sup>
TELEX: 996404 EASYLINK: 62968934 CABLE: OMEGA

Mexico:

Tel: (95) 800-TC-OMEGA<sup>SM</sup> FAX: (95) 203-359-7807

### **Servicing Europe:**

Benelux:

Postbus 8034, 1180 LA Amstelveen, The Netherlands

Tel: (31) 20 6418405

FAX: (31) 20 6434643

Toll Free in Benelux: 06 0993344

Czech Republic:

Ostravska 767, 733 01 Karvina

Tel: 42 (69) 6311899

FAX: 42 (69) 6311114

France:

9, rue Denis Papin, 78190 Trappes

Tel: 33 (1) 30.62.14.00

FAX: 33 (1) 30.69.91.20

Toll Free in France: 05-4-OMEGA

Germany/Austria:

Daimlerstrasse 26, D-75392 Deckenpfronn, Germany

Tel: 49 (07056) 3017

FAX: 49 (07056) 8540

Toll Free in Germany: 0130 11 21 66

United Kingdom:

25 Swannington Road, Broughton Astley, Leicestershire,

ISO 9002 Certified

LE9 6TU, England

Tel: 44 (1455) 285520

FAX: 44 (1455) 283912

Toll Free in England: 0800-488-488

It is the policy of OMEGA to comply with all worldwide safety and EMC/EMI regulations that apply. OMEGA is constantly pursuing certification of its products to the European New Approach Directives. OMEGA will add the CE mark to every appropriate device upon certification.

#### **Unpacking Instructions**



Remove the Packing List and verify that you have received all equipment, including the following (quantities in parentheses):

- LDM80 Modem
- Operator's Manual.

If you have any questions about the shipment, please call the OMEGA Customer Service Department. When you receive the shipment, inspect the container and equipment for signs of damage. Note any evidence of rough handling in transit. Immediately report any damage to the shipping agent.

NOTE

The carrier will not honor damage claims unless all shipping material is saved for inspection. After examining and removing contents, save packing material and carton in the event reshipment is necessary.

From the Technical Library of \_\_\_\_\_

# LDM80

# Signal-Powered, Fiber-Optic Modem

# **Description**


The LDM80 is a small, inexpensive fiber optic transmitter/receiver completely powered by the host RS-232 port. The enclosure for the LDM80 is a conductive shell that greatly reduces RF radiation and susceptibility. The rugged metal enclosure is small enough to mount on the back panel of typical computer equipment saving valuable desk and floor space. A pair of these units allows most RS-232C cable links to be replaced and extended with a duplex fiber optic cable. The normal 50-foot RS-232 limit may be extended to 2.2 miles (3.5 km). Fiber optic data communications provide complete EMI/RFI rejection, isolation, elimination of ground loops, and reduced error rates. Data security is enhanced by almost nonexistent electromagnetic emissions. The RS-232 connection is through male or female EIA 25-pin connectors. The fiber optic connection is either through SMA (905) or ST connectors.

The LDM80 is equivalent to a 3-wire, full duplex, RS-232 circuit. Handshake signals are locally connected as in Figure 1. Indicating LEDs come on during a "SPACE" on transmit or receive data. A TD/RD reversing DIP switch is provided for connection to DTE (Data Terminal Equipment) or DCE (Data Communication Equipment) ports.

# **Specifications**


Model		LDM80			
Baud Rate Range	0 19.	2K			
Distance: Over Baud Rate Range					
Fiber Core Diameter (µm) 100 (glass) 50 (glass) 62.5 (glass) 85 (glass) 200 (glass)		ax. Cable Length (km) 3.5 2.5 2.0 3.5 3.5 3.0 meters	Loss Budget (dB) 17 9 11 16 23		
1000 (plastic) Channel Lines(1)	TD, RD		32		
Control Lines(1)	RTS, CTS, DSR, DTR, RLSD				
Modes	Asynchronous 2-fiber full duplex, 1-fiber simplex				
Optical Transmitter	850 nm wavelength				
Output from 1 m cable	-26 dB typ, -27dB min, -18 dB max				
Optical Receiver Power Input for 4µs Pulse Distortion	-44 dB min				
Optical Connectors	ST, SMA (905) Compatible				

Notes: (1) TD = Transmit Data, RD = Receive Data, RTS = Request To Send, CTS = Clear To Send. DTR = Data Terminal Ready, DSR = Data Set Ready, RLSD = Received Line Signal Detect.



Model	LDM80	
RS-232 Output Voltage with 3kΩ Load	+5V logic 0, -5V logic 1	
DCE/DTE Switch	One	
Diagnostic LEDs	Two	
Power: Port Power and/or DC operation	+5.0 to +8.5 VDC, no current limit, 5 mA >+8.5 VDC, 10 mA current limit	
Operating Environment non-condensing	-20°C to +70°C, 0 to 95% relative humidity,	
Dimensions	3.51 in x 1.88 in x 0.729 in (89.2 mm x 47.8 mm x 18.5 mm)	
Weight	8.1 oz (230 g) max	
MTBF <sup>(2)</sup>	>100,000 hrs	


<sup>(2)</sup> Ground-benign environmental conditions (no salt atmosphere, <50°C ambient temperature).



#### **Recommended Cables**

The LDM80 optical transmitter may be used with a wide range of fiber sizes. Specifications are for 100/140  $\mu m$ . Other fiber sizes may be used with a resulting different cable loss budget.

Pin Descriptions		S	Fiber Optic	
Pin 1 Pin 2 Pin 3 Pin 4 Pin 5 Pin 6 Pin 7	Case TD RD RTS CTS DSR SIG GND	Case Ground Transmit Data Receive Data Request To Send Clear To Send Data Set Ready Signal Ground	T	
Pin 8 Pin 20	rlsd Dtr	Receive Line Signal Detect Data Terminal Ready		




#### Installation

Power is supplied through a high RS-232 signal, normally current limited, applied to any of pins 4, 5, 6, 8 or 20. If the LDM80 is powered by a voltage source, V > +8.5 VDC, the current must be limited to 10 mA. Voltage sources, V < = +8.5 VDC, will need no current limit. Voltage sources, V < +8.0 VDC, will lower transmission distances. The minimum operating supply voltage for the LDM80 is +5.0 VDC and correct operation below this voltage is not guaranteed.

**WARNING!** Voltage sources greater than +8.5 VDC without current limit will damage the LDM80!

For installation check-out, it is recommended that a short fiber-optic cable be connected from transmit to receive on a locally connected device. See Figure 2 for a typical installation.



	Models
Model	Description
LDM80-P	Pinned RS-232 connector, SMA (905) fiber optic connector
LDM80-S	Socketed RS-232 connector, SMA (905) fiber optic connector
LDM80-P-025	Pinned RS-232 connector, ST fiber optic connector
LDM80-S-025	Socketed RS-232 connector, ST fiber optic connector

Note: (1) Specify length to the nearest meter. Example: LDM85CA2-0550 for 550 meters dual cable.



### WARRANTY/DISCLAIMER

OMEGA warrants this unit to be free of defects in materials and workmanship and to give satisfactory service for a period of 13 months from date of purchase. OMEGA Warranty adds an additional one (1) month grace period to the normal one (1) year product warranty to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product. If the unit should malfunction, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective it will be repaired or replaced at no charge. However, this WARRANTY is VOID, if the unit shows evidence of having been tampered with or shows evidence of being damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components which wear or which are damaged by misuse are not warranted. These include contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. Nevertheless, OMEGA only warrants that the parts manufactured by it will be as specified and free of defects.

OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED.

LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY / DISCLAIMER language, and additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

## RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA ENGINEERING Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

- 1. P.O. number under which the product was PURCHASED.
- 2. Model and serial number of the product under warranty, and
- 3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS OR **CALIBRA- TION,** consult OMEGA for current repair/calibration charges. Have the following information
available BEFORE contacting OMEGA:

- 1. P.O. number to cover the COST of the repair/calibration,
- 2. Model and serial number of the product, and
- 3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering.

OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 1996 OMEGA ENGINEERING, INC. All rights reserved. This documentation may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without prior written consent of OMEGA ENGINEERING, INC.

# Where Do I Find Everything I Need for **Process Measurement and Control? OMEGA...Of Course!**



#### **TEMPERATURE**

- Thermocouple, RTD & Thermistor Probes, Connectors, Panels & Assemblies
- Wire: Thermocouple, RTD & Thermistor
- ☑ Calibrators & Ice Point References
- Recorders, Controllers & Process Monitors
- Infrared Pyrometers



## PRESSURE, STRAIN AND FORCE

- Transducers & Strain Gages
- Load Cells & Pressure Gauges
- Displacement Transducers
- ☑ Instrumentation & Accessories



- Rotameters, Gas Mass Flowmeters & Flow Computers
- Air Velocity Indicators
- Turbine/Paddlewheel Systems
- ☑ Totalizers & Batch Controllers



- Benchtop/Laboratory Meters
- Controllers, Calibrators, Simulators & Pumps
- ☑ Industrial pH & Conductivity Equipment



#### DATA ACQUISITION

- ☑ Data Acquisition and Engineering Software
- Communications-Based Acquisition Systems
- Plug-in Cards for Apple, IBM & Compatibles
- Datalogging Systems
- Recorders, Printers & Plotters

#### **HEATERS**

- Heating Cable
- ☑ Cartridge & Strip Heaters
- ☑ Immersion & Band Heaters
- Flexible Heaters
- Laboratory Heaters



#### **ENVIRONMENTAL** MONITORING AND CONTROL

- ☑ Metering & Control Instrumentation
- ☑ Refractometers
- Pumps & Tubing
- Air, Soil & Water Monitors
- Industrial Water & Wastewater Treatment
- pH, Conductivity & Dissolved Oxygen Instruments



