

# FLSC-62A Wire Loop Powered 4-20mA Transmitter

## SPECIFICATIONS

<b>Temperature:</b>	Operating -40 to 85°C Storage -65 to 125°C
<b>Input Voltage:</b>	Minimum = $7\text{ V} + (20\text{mA} \times \text{RL})$ Maximum = $28\text{ V} + (4\text{mA} \times \text{RL})$ Protected against polarity reversal
<b>Signal Input:</b>	Frequency 0-10 KHz Amplitude 50 mV – 35 V sine or square wave Sensitivity field adjustable Impedance 50K
<b>Analog Output</b>	4mA @ 0 Hz, 20mA @ desired full scale frequency Full scale range -- 100 Hz-10 KHz selectable Response time -- 95% of change in 1 second Linearity -- .3% F/S Tempco -- < 2% of reading over entire temperature range
<b>Features:</b>	Mounts directly on flowmeter
<b>Enclosure:</b>	FM Approved, CSA Certified Class I Groups B, C, D Class II Groups E, F, G Weight 1.7 lbs.

The FLSC-62A is a 2-wire loop powered analog transmitter designed to linearly convert a frequency input to an equivalent 4-20mA current output. When it incorporates with a turbine flowmeter a current representation proportional to flow is obtainable. Data transmission in a current format exhibits excellent noise immunity and the capability of long distance transmission.


A full-scale frequency range of 100 Hz-10 KHz is selectable, via S1. The span adjustment establishes the frequency point at which a 20mA output is achieved. The sensitivity adjustment permits the FLSC-62A to discriminate between a signal input and noise by increasing (CCW) or decreasing (CW) the input signal amplitude necessary to process a valid signal. 'Test' S2 when depressed, illuminates D1 if loop voltage and input signal both are present.

Installation of the FLSC-62A requires only 2 wires because it is a true 2-wire transmitter: input power and signal output utilizes the same wires.

# BENCH TEST CALIBRATION PROCEDURE

**Required Equipment:** Power Supply 12-28v, Digital Multimeter (DMM), Frequency Generator, & Frequency Counter

**Test Procedure:**



- A) Connect DMM positive lead to power supply positive, connect DMM negative lead to J1-3, set DMM function to mA DC
- B) Connect power supply negative lead to 250 Ω resistor, connect other resistor leg to J1-5
- C) Connect frequency generator positive & negative leads to J1-1,2; respectively. Set output to sinewave & amplitude to zero
- D) Set S1 for desired frequency range
- E) Turn power supply & frequency generator 'ON', DMM should indicate approximately 4.00mA
- F) Adjust 'ZERO' (R25) for 4.00mA DMM indication (record data)
- G) Set 'Sensitivity' adjust (R1) fully clockwise
- H) Adjust signal amplitude of frequency generator to 50mv & frequency to maximum desired point (full scale frequency) (record data)
- I) Adjust 'SPAN' (R19) for 20.00mA DMM indication (record data)
- J) Reduce signal amplitude of frequency generator to zero, adjust 'ZERO' (R25) for 4.00mA DMM indication if necessary
- K) Adjust signal amplitude of frequency generator to 50mv, adjust 'SPAN' (R19) for 20.00mA DMM indication if necessary
- L) Adjust frequency of frequency generator to exactly 50% of maximum frequency point in step H, DMM should indicate 12.00mA ± .06. Repeat for 25% & 75% full scale frequencies(record data)

To check linearity @ any frequency point, incorporate the following formula:

$$(F/F_{\max} \times 16) + 4 = \text{mA}$$

(Where F = Flowrate frequency in Hz)

(F<sub>max</sub> = Frequency in Hz at which 20mA is set)





Ex. Assume maximum frequency point = 2000 Hz (20.00mA) Check for linearity @ 750 Hz point

$$750/2000 = .375$$

$$16 \times .375 = 6$$


$$6 + 4 = 10; \text{ DMM should indicate } 10.00\text{mA @ } 750 \text{ Hz input}$$

# TYPICAL LOOP CONFIGURATIONS





DATE	REV	REVISION RECORD	AUTH	DR	CK
2/02	C	Updated to REV. C	KN	TN	



TERMINAL LOCATION

- 1 SIGNAL IN +
- 2 SIGNAL IN -
- 3 LOOP IN +
- 4 N/C
- 5 LOOP IN -

BOARD SET REPLACEMENT PART#:

PCB-712-2-REV-C

NOTE: DIMENSIONS ARE IN INCHES

		SCALE	DRAWN BY
File:Elect\FLSC-62A.dwg		NONE	TN
DESCRIPTION		DATE	5-5-97
FLSC-62A 4-20mA Transmitter		REVIEWED BY	
		DATE	
CODE	DRAWING NUMBER	REV. #	APPR. BY
EM	FLSC-62A-01		
		DATE	