C OMEGA[™] HH11C DIGITAL THERMOMETER





Servicing North America:

U.S.A. Omega Engineering, Inc.

Headquarters: Toll-Free: 1-800-826-6342 (USA & Canada only)

Customer Service: 1-800-622-2378 (USA & Canada only)

Engineering Service: 1-800-872-9436 (USA & Canada only)

Tel: (203) 359-1660 Fax: (203) 359-7700

e-mail: info@omega.com

For Other Locations Visit omega.com/worldwide

INTRODUCTION

This instrument is a portable $4\frac{1}{2}$ digit, compact-sized digital thermometer designed to use external K-type thermocouples as temperature sensor. Temperature indication follows National Bureau of Standards and IEC 584 tem-perature/voltage tables for K-type thermocouples. One K-type thermocouple is supplied with the thermometer.

SAFETY INFORMATION

It is recommended that you read the safety and operation instructions before using this thermometer.

WARNING To avoid electrical shock, do not use this instrument when working voltages at the measurement surface over 24V AC or 60V DC.

WARNING

To avoid damage or burns, do not make temperature measurement in microwave ovens.

CAUTION

Repeated sharp flexing can break the thermocouple leads. To prolong lead life, avoid sharp bends in the leads, especially near the connector.

The \triangle symbol on the instrument indicates that the operator must refer to an explanation in this manual.

SPECIFICATIONS

ELECTRICAL

Temperature Scale: Celsius or Fahrenheit user-selectable Measurement Range:

-200°C to 1372°C, -328°F to 2501°F **Auto range:** 0.1°C/1°C, 0.1°F/1°F **Accuracy:** Accuracy is specified for operating temperatures over the range of 18°C to 28°C (64°F to 82°F), for 1 year, not including thermocouple error. $\pm (0.1\% rdg+0.5°C)$ on -60°C to 1372°C $\pm (0.1\% rdg+2°C)$ on -60°C to -200°C $\pm (0.1\% rdg+1°F)$ on -76°F to 2501°F $\pm (0.1\% rdg+4°F)$ on -76°F to -328°F

Temperature Coefficient:

 $0.\bar{1}$ times the applicable accuracy specification per °C from 0°C to 18°C and 28°C to 50°C (32°F to 64°F and 82°F to122°F).

Input Protection:

60V dc or 24V ac rms maximum input voltage on any combination of input pins.

Input Connector:

Accepts standard miniature thermocouple connectors (flat blades spaced 7.9mm, center to center).

ENVIRONMENTAL

Ambient Operating Ranges: 0°C to 50°C (32°F to 122°F)

Storage Temperature:

-20°C to 60°C (-4°F to 140°F)

GENERAL

- **Display:** 4¹/₂ digit liquid crystal display (LCD) with maximum reading of 19999.
- Low battery indication: The "----" is displayed when the battery voltage drops below the operating level.
- Measurement rate: 1 time/second.
- **Operating environment:** 0°C to 50°C at<70% R.H. **Storage temperature:** -20°C to 60°C, 0 to 80% R.H. with battery removed from meter.

Accuracy: Stated accuracy at 23°C±5°C, <75% R.H. Battery: Standard 9V battery (NEDA 1604, IEC 6F22). Battery Life: 100 hours typical with carbon zinc battery. Dimensions: 210mm(H) x 65mm(W) x 35mm(D). Weight: approx. 282g including battery.

Supplied Wire: 4 feet type "K" thermocouple bead wire (PTFE tape insulated). Maximum insulation temperature 260° C (500° F). Wire accuracy $\pm 2.2^{\circ}$ C or $\pm 0.75\%$ of reading (whichever is greater) from 0° C to 800° C.

OPERATING INSTRUCTIONS

1. "°C/°F" Button: Selecting the Temperature Scale Readings are displayed in either degrees Celsius(°C) or degrees Fahrenheit(°F). When the thermometer is turned on, it is set to the temperature scale that was in use when the thermometer was last turned off. To change the temperature scale, hold down for 2 seconds "APO >2S°C/°F" key.

2. "HOLD" Button

Press the "HOLD" key to enter the Data Hold mode, the "HOLD" annunciator is displayed. When HOLD mode is selected, the thermometer held the present readings and stops all further measurements. Press the "HOLD" key again cancels HOLD mode, causing the thermometer to resume taking measurements.

3. "REL" Button

Press "REL" key to enter Relative mode, zero the display, and store the displayed reading as a reference value and annunciator REL is displayed. Pressing "REL" key over 2 seconds to exit the relative mode.

4. "APO" Button

Pressing "APO >2S °C/°F" key to trigger on or off APO mode, and then APO annunciator will appear or disappear on the display. Power is automatically turn off, if no operation for a period of time, and "APO" annunciator is displayed at upper-left corner when APO function is enabled.

5. "MIN/MAX" Button

Press "MIN/MAX" once to begin recording MIN and MAX. Press "MIN/MAX" to select MIN or MAX or MAX-MIN or AVG. Hold down for 2 seconds to exit MIN/MAX function.

In the MIN/MAX record mode can not power off, must leave MIN/MAX record mode then power off.

It is the policy of OMEGA Engineering, Inc. to comply with all worldwide safety and EMC/EMI regulations that apply. OMEGA is constantly pursuing certification of its products to the European New Approach Directives. OMEGA will add the CE mark to every appropriate device upon certification. The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

WARNING: These products are not designed for use in, and should not be used for, human applications.

OFFSET ADJUSTMENT

The OFFSET control is set at the factory to allow for the variations found in standard thermocouples. By adjusting the OFFSET control, you can optimize measurement accuracy for a particular thermocouple at a particular temperature.

Adjusting for Accurate Measurements

- 1. Connect the thermocouple to the input connector and turn the thermometer on.
- 2. Place the thermocouple in a known, stable temperature environment at or near the temperature you wish to measure, and allow the readings to stabilize.
- Slowly adjust the OFFSET control so that the thermometer reading matches the temperature of the known environment. Leave sufficient time between adjustments to allow for measurement lag.

Resetting the OFFSET Control

To return the OFFSET control to the factory setting without having to recalibrate the thermometer, perform the following procedure:

- 1. Connect a thermocouple that is in good working order to the input that is to be adjusted.
- Place the thermocouple in an ice-water bath and allow the readings to stabilize.
- Slowly adjust the OFFSET control until the thermometer reads 0°C (32°F).

Probe Detector

The red LED will be ON when no K-type thermocouple probe is inserted into the TEMP input of the meter, and will be OFF after K-type thermocouple probe is inserted. If the red LED stays ON when thermocouple probe is attached, check the thermocouple probe which might be damaged.

OPERATOR MAINTENANCE

WARNING

To avoid possible electrical shock, disconnect the thermocouple connectors from the thermometer before removing the cover.

Battery Replacement

1. Power is supplied by 9V (NEDA 1604, IEC 6F22).

- 2. The "Diapears on the LCD display when replacement is needed.
- 3. Remove the battery from battery contacts.
- 4. When not use for long time remove battery.
- 5. Don't keep in place with high Temp, or high humidity.

Cleaning

Periodically wipe the case with a damp cloth and detergent, do not use abrasives or solvents.

WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use if its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s)

RETURN REQUESTS/INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

please have the following	FOR NON-WARRANTY REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA: 1. Purchase Order number to cover the COST of the repair or calibration, 2. Model and serial number of the product, and 3. Repair instructions and/or specific problems relative to the product.
OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering.	

OMEGA is a registered trademark of OMEGA ENGINEERING, INC. © Copyright 2017 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.

Where Do I Find Everything I Need for Process Measurement and Control? OMEGA...Of Course! Shop online at omega.com

TEMPERATURE

- Thermocouple, RTD & Thermistor Probes, Connectors, Panels & Assemblies
- ☑ Wire: Thermocouple, RTD & Thermistor
- Calibrators & Ice Point References
- Recorders, Controllers & Process Monitors
- Infrared Pyrometers

PRESSURE, STRAIN AND FORCE

- ☑ Transducers & Strain Gages
- Load Cells & Pressure Gages
- Displacement Transducers
- Instrumentation & Accessories

FLOW/LEVEL

- Rotameters, Gas Mass Flowmeters & Flow Computers
- Air Velocity Indicators
- ℤ Turbine/Paddlewheel Systems
- Totalizers & Batch Controllers

pH/CONDUCTIVITY

- 🖉 pH Electrodes, Testers & Accessories
- Benchtop/Laboratory Meters
- 🖉 Controllers, Calibrators, Simulators & Pumps
- Industrial pH & Conductivity Equipment

DATA ACQUISITION

- Data Acquisition & Engineering Software
- Communications-Based Acquisition Systems
- Plug-in Cards for Apple, IBM & Compatibles
- Datalogging Systems
- 🖉 Recorders, Printers & Plotters

HEATERS

- Heating Cable
- 🖉 Cartridge & Strip Heaters
- Immersion & Band Heaters
- Flexible Heaters
- Laboratory Heaters

ENVIRONMENTAL MONITORING AND CONTROL

Metering & Control Instrumentation

- Refractometers
- Pumps & Tubing
- Air, Soil & Water Monitors
- Industrial Water & Wastewater Treatment
- PH, Conductivity & Dissolved Oxygen Instruments