

DC Loop Powered Digital Pressure Gauge

DPG110

INSTRUCTION SHEET

Shop online at omega.com e-mail: info@omega.com For latest product manuals: omegamanual.info

Introduction

DPG110 is digital pressure gauge powered by a seperate loop power supply from 12 to 30VDC. It is made for easy on-site installation. The DPG110 uses a high-precision piezo-resistive pressure sensor. The output signal is amplified by a high-precision, low-temperature drift amplifier. The signal is then fed into a high accuracy A/D converter for the microprocessor to process and then show on the LED display.

This flexible, simple to operate digital pressure gauge is safe, reliable, and easy to debug. The DPG110 is widely used in hydropower, water, petroleum, chemical, mechanical, hydraulic, and other industries.

Features

- 4-20mA interface
- 4-digit 0.56" LED display
- Ceramic pressure sensor core
- Digital Calibration
- Anti-jamming design suitable for electromagnetic and harsh industrial environments.
- · IP65 rated outlet port connector

Specifications

- Measuring Range 0 - 20MPa
- Overload Pressure 150%~200%
- Pressure Type A/G
- Stability ≤0.2% FS per year
- Power Supply 12-30VDC

 Display 4 digits LED

Accuracy Range

±0.25% for gauge pressure >5psi ±0.5% FS for all others including absolute, compound gauge, and Vacuum ranges

- IP Rating IP65
- Output 4-20mA Signal
- Operating Temp -30°C ~ 80°C
- Relative Humidity ≤90%
- Thread Size 1/4 NPT
- Thread Material SS316

Dimensions


OE OMEGA 00

Operating Instructions


 Wiring RED: +24VDC Black: Ground

Calibration

Press ▼ for 5 seconds for zero callibration Press A for 5 seconds for full scale calibration



Control Method



1. Operation panel description:

• The transmitter board provides a three-button and Led display man-machine interface to operate all transmitter Settings and calibration parameters.

• Key functions are multiplexed. A down key is a shift key when the input data is shifted.

2. Clear the zero deviation:

• Given zero standard pressure, long press increase button for 10 seconds to calibrate full degree.

• Given full standard pressure, hold down the reduce button for 10 seconds to calibrate zero.

This operation is a shortcut provided to customers, generally not end users do not enter this function to prevent calibration data damage.

3. Menu operation, as shown below:

Calibration menu is the transmitter calibration way for factory calibration and general technical supervision department, general users do not enter the setting of any data, non-professionals modify any data may lead to the transmitter completely

unable to work.

Circuit board through the panel of the three keys to achieve all the parameters input and calibration data Settings, collection. The circuit board on the meter setting and input to take a variety of optimization measures to improve customer operation speed:

• The decrease key and increase key of the meter have variable speed function

• For the menu that needs to be modified by a large number, the menu that needs to continuously input data adopts the shift mode, and the menu that needs to continuously input data adopts the incremental mode

• The meter will stop analog output in the set state, so if the user does not operate the meter within 3 minutes, it will automatically exit to the measurement state

• The shift input has a flashing prompt function

• The full meter data will flash when it exceeds 120% of the normal setting display value. Less than 0.2% of the zero-setting value, the instrument displays the zero value, which can realize the zero-shielding function of the sensor

• When the meter enters the factory password menu in the state of zero clearance, the zero-clearance value will be automatically cleared when the menu exits

• The meter saves all settings only when it exits the menu normally



omega.com info@omega.com

Servicing North America:

U.S.A. Headquarters: Omega Engineering, Inc. Toll-Free: 1-800-826-6342 (USA & Canada only) Customer Service: 1-800-622-2378 (USA & Canada only) Engineering Service: 1-800-872-9436 (USA & Canada only) Tel: (203) 359-1660 e-mail: info@omega.com

For Other Locations Visit omega.com/worldwide

The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

WARNING: These products are not designed for use in, and should not be used for, human applications.

WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13** months from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal one (1) year product warranty to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages. CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

- 1. Purchase Order number under which the product was PURCHASED,
- 2. Model and serial number of the product under warranty, and
- 3. Repair instructions and/or specific problems relative to the product.
- FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:
- 1. Purchase Order number to cover the COST of the repair,
- Model and serial number of the product, and
 Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering. OMEGA is a trademark of OMEGA ENGINEERING, INC.

© Copyright 2018 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.