





# Shop online at omega.com®

e-mail: info@omega.com For latest product manuals: www.omegamanual.info

OM-CP-HITEMP140-M12 High Temperature Data Logger with an M12 Probe Connector

### **Product Overview**

The OM-CP-HITEMP140-M12 is a rugged and versatile high temperature data logger featuring an M12 probe connector. Compatible with a wide variety of M12 RTD probe styles, this data logger is capable of measuring up to 850°C (1562°F) (probe dependent).

All OM-CP-HITEMP140 data loggers have a water tight body enclosure made of food grade stainless steel and can be placed in environments with temperatures as high as 140°C (284°F). The operating range of the data logger body can be extended to higher temperatures when used with thermal barrier options and a suitable probe.

The OM-CP-HITEMP140-M12 records and stores up to 43,690 time stamped readings and is equipped with non-volatile solid state memory which retains data even if the battery becomes discharged.

A wide selection of compatible M12 probes are available from Omega to choose from, making the OM-CP-HITEMP140-M12 the most dynamic data logger of its kind. With the ability to change probes as needed, this device satisfies a multitude of application needs with one powerful data logger versus the need for multiple loggers.

Note: Specific M12 wiring configuration is required for compatibility. (see page 4)

### **Submergibility**

The OM-CP-HITEMP140-M12 logger itself is rated IP40 and not submersible. It will inherit the IP rating of the probe it is attached to, allowing for potential submergibility, depending upon the probe.

### **O-Rings**

O-ring maintenance is a key factor when properly caring for the OM-CP-HITEMP140-M12. The O-rings ensure a tight seal and prevent liquid from entering the inside of the device.

### **Trigger Settings**

The device can be programmed to only record based off user configured trigger settings.

- 1. In the **Connected devices** panel, select the intended device to change the settings.
- 2. On the **Device** tab, in the Information group, click **Properties**. Users can also right-click on the device and select **Properties** in the context menu.
- 3. Click **Trigger** and configure the **Trigger settings**. Trigger formats are available in Window and Two Point *(bi-level)* mode. Window mode allows for one range of temperature monitoring and two point mode allows for two ranges.

Note: This product is rated for use up to 140°C. Please heed the battery warning. The product will explode if exposed to temperatures above 140°C.

# **Troubleshooting Tips**

### Why is the data logger not appearing in the software?

If the OM-CP-HITEMP140-M12 doesn't appear in the Connected Devices panel, or an error message is received while using the OM-CP-HITEMP140-M12, try the following:

- Check that the OM-CP-IFC400 is properly connected. For more information, see Troubleshooting Interface Cable problems (below).
- Ensure that the battery is not discharged. For best voltage accuracy, use a voltage meter connected to the battery of the device. If possible, try switching the battery with a new OM-CP-BAT110.
- Ensure that no other Omega software is running in the background.
- Ensure that **Omega Software** is being used.
- Ensure that the **Connected Devices** panel is large enough to display devices. This can be verified by positioning the cursor on the edge of the Connected Devices panel until the resize cursor appears, then dragging the edge of the panel to resize it. The screen layout may also be reset in the options menu by selecting **File**, **Options**, and scrolling to the bottom.

### **Troubleshooting Interface Cable problems**

### Check that the software properly recognizes the connected OM-CP-IFC400.

If the data logger is not appearing in the **Connected Devices** list, it may be that the OM-CP-IFC400 is not properly connected.

- 1. In the software, click the **File** button, then click **Options**.
- 2. In the **Options** window, click **Communications**.
- **3.** The **Detected Interfaces** box will list all of the available communication interfaces. If the OM-CP-IFC400 is listed here, then the software has correctly recognized and is ready to use it.

### Check that Windows recognizes the connected OM-CP-IFC400.

If the software does not recognize the OM-CP-IFC400, there may be a problem with Windows or the USB drivers.


- 1. In Windows, click **Start**, right-click **Computer** and choose **Properties** or press **Windows+Break** as a keyboard shortcut.
- 2. Click **Device Manager** in the left hand column.
- 3. Double click Universal Serial Bus Controllers.
- 4. Look for an entry for **Data logger Interface**.
- 5. If the entry is present, and there are no warning messages or icons, then windows has correctly recognized the connected OM-CP-IFC400.
- 6. If the entry is not present, or has an exclamation point icon next to it, the USB drivers may need to be installed. These are available on the software flash drive included with the OM-CP-IFC400.

### Ensure that the USB end of the OM-CP-IFC400 is securely connected to the computer.

- 1. Locate the USB-A plug of the OM-CP-IFC400.
- 2. If the interface cable is connected to the PC, unplug it. Wait ten seconds.
- **3.** Reconnect the cable to the PC.
- 4. Check to make sure that the red LED is lit, indicating a successful connection.

## Wiring the Data Logger

OM-CP-HITEMP140-M12 connector is a 4 pin female M12 connection port which allows the user to change probes as desired. The OM-CP-HITEMP140-M12 will inherit the IP rating of the probe it is attached to, (up to, and including IP68/IP69K).



The OM-CP-HITEMP140-M12 is compatible with probes that have the wiring configuration as shown to the left.

### **Probe Connection**

### Connecting probes to the OM-CP-HITEMP140-M12

Materials: 15 mm wrench, Compatible Probe with M12 Connector

- 1. Connect the probe to the data logger, using the wiring diagram above.
- 2. Use a 15 mm hex wrench to tighten the threads and secure the probe to the data logger.



### Installation Guide

### Installing the Interface cable

- OM-CP-IFC400 or OM-CP-IFC406 Refer to the "Quick Start Guide" included in the package.

### Installing the software

Insert the Omega Software Flash Drive in an open USB port. If the autorun does not appear, locate the drive on the computer and double click on **Autorun.exe**. Follow the instructions provided in the Installation Wizard.

### **Device Operation**

### Connecting and Starting the data logger

- 1. Once the software is installed and running, plug the interface cable into the docking station.
- 2. Connect the USB end of the interface cable into an open USB port on the computer. Place the data logger into the docking station.
- 3. The data logger will automatically appear under **Connected Devices** within the software.
- 4. For most applications, select "**Custom Start**" from the menu bar and choose the desired start method, reading rate and other parameters appropriate for the data logging application and click "Start". ("**Quick Start**" applies the most recent custom start options, "**Batch Start**" is used for managing multiple loggers at once, "**Real Time Start**" stores the dataset as it records while connected to the logger.)
- 5. The status of the device will change to "Running", "Waiting to Start" or "Waiting to Manual Start", depending upon your start method.
- 6. Disconnect the data logger from the docking station and place it in the environment to measure. Note: The device will stop recording data when the end of memory is reached or the device is stopped. At this point the device cannot be restarted until it has been re-armed by the computer.

### Downloading data from a data logger

- 1. Connect the logger to the docking station.
- 2. Highlight the data logger in the **Connected Devices** list. Click "Stop" on the menu bar.
- 3. Once the data logger is stopped, with the logger highlighted, click "**Download**". You will be prompted to name your report.
- 4. Downloading will offload and save all the recorded data to the PC.

### **Product Maintenance**

### **Battery Replacement**

### Materials: OM-CP-BAT110

- 1. Unscrew the bottom of the logger and remove the battery.
- 2. Place the new battery into the logger. Note the polarity of the battery.
- 3. Screw the cover back onto the logger.

### Recalibration

The OM-CP-HITEMP140-M12 standard calibrations are two points at  $50\Omega$  and  $150\Omega$  and is verified at  $100\Omega$ .

Recalibration is recommended annually for any Omega data logger; a reminder is automatically displayed in the software when the device is due.

### **OM-CP-HITEMP140-M12 General Specifications**

Temperature Sensor	Various RTD Probes with M12 Connector (Sold Separately)
Measurement Range	18Ω to 400Ω -200°C to +850°C (-328°F to +1562°F) (Probe Dependent)
Temperature Resolution	0.0001Ω 0.01°C (0.018°F) (Probe Dependent)
Calibrated Accuracy	$\pm 0.015\Omega$ ±0.05°C (±0.09°F) (Probe Dependent)
*Calibrated Accuracy Range	18Ω to 200Ω -200°C to +265°C (-328°F to +509°F)
Connector Type	M12 Female, 4 Pin
Reading Rate	4 readings per second up to 1 reading every 24 hours
Memory	43,690 readings
Start Modes	<ul><li>Software programmable immediate start</li><li>Delay start up to 18 months in advance</li></ul>
Stop Modes	Manual or Timed (specific date and time)
Trigger Settings	High & Low limits may be set. Once data meets or exceed sets limits, the device will record to memory. Bi-level start and stop triggers can also be programmed. Users can specify the number of readings to take after the device triggers.
Readings in Trigger Settings Mode	18,724 readings
Real Time Recording	May be used with PC to monitor and record data in real time
Password Protection	An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password.
Memory Wrap Around	Yes
Battery Type	3.6V high-temperature lithium battery included; user replaceable
Battery Life	2 years typical (1 minute reading rate)
Calibration	Digital calibration through software
Calibration Date	Automatically recorded within device
Data Format	Date and time stamped °C, °F, °R, K
Time Accuracy	±1 minute/month at 25°C

\*Calibrated accuracies based on standard calibrations for 0 $\Omega$  to 200 $\Omega$  range.

### **OM-CP-HITEMP140-M12 General Specifications**

Computer Interface	OM-CP-IFC400 or OM-CP-IFC406 USB docking station required; 125,000 baud
Operating System Compatibility	XP SP3/Vista/Windows 7/Windows 8
	<ul> <li>OM-CP Standard Software version 4.2.5.0</li> <li>OM-CP Secure Software version 4.2.4.0 or later</li> </ul>
Operating Environment	-40°C to +140°C (-40°F to +284°F), 0%RH to 100%RH non-condensing, 0.002PSIA to 60PSIA
IP Rating	IP40 - logger alone (with no probe connected). The logger will inherit IP rating of the attached probe (up to, and including IP68/IP69K).
Dimensions (body)	2.15" x 0.97" x 0.97" (54.5mm x 24.6mm x 24.6mm)
Dimensions (probe)	Probe dependent
Weight	85 g (3.0 oz)
Materials	Body: 316 Stainless Steel
Approvals	CE

#### **Battery Warning**

WARNING: FIRE, EXPLOSION, AND SEVERE BURN HAZARD. DO NOT SHORT CIRCUIT, CHARGE, FORCE OVER DISCHARGE, CRUSH, PENETRATE OR INCINERATE. BATTERY MAY LEAK OR EXPLODE IF HEATED ABOVE 150°C (302°F).

Specifications subject to change. See Omega's terms and conditions at www.omega.com



omega.com info@omega.com

### **Servicing North America:**

U.S.A.:

Omega Engineering, Inc., One Omega Drive, P.O. Box 4047 Stamford, CT 06907-0047 USA Toll-Free: 1-800-826-6342 (USA & Canada only) Customer Service: 1-800-622-2378 (USA & Canada only) Engineering Service: 1-800-872-9436 (USA & Canada only) Tel: (203) 359-1660 Fax: (203) 359-7700 e-mail: info@omega.com

### For Other Locations Visit omega.com/worldwide

The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

WARNING: These products are not designed for use in, and should not be used for, human applications.

### 

### WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **61 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **five (5) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product. If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

#### **RETURN REQUESTS / INQUIRIES**

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

- 1. Purchase Order number under which the product was PURCHASED,
- 2. Model and serial number of the product under warranty, and
- 3. Repair instructions and/or specific problems relative to the product.

FOR **MON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

- 1. Purchase Order number to cover the COST of the repair,
- 2. Model and serial number of the product, and
- 3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering. OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2014 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.