

AHP Series



M2157/0517

Shop online at: omega.com e-mail: info@omega.com For latest product manuals: omegamanual.com



GENERAL DESCRIPTION

The AHP Series in-line air heaters are used to heat clean, dry air or gas for baking, drying, laminating, metal working, packaging, plastic welding, preheating, sealing, soldering, shrink fitting and synthetic fabric sewing. Outlet temperatures are varied by adjusting the voltage and/or the air flow. Closed loop control can also be achieved with temperature controllers and "T" fittings to mount thermocouples. Consult tables below to determine maximum and minimum recommended flow rates.

Calculate the flow rate, temperature rise, or power requirement as follows:

Watts = SCFM x Δ T/3

SCFM = Standard Cubic Feet per Minute

 ΔT = Temperature Rise in Degrees F from the Inlet to the Outlet

The cold air entry should always be at the termination end of the heater. Do not run without proper air flow. Controls should be used to prevent operation of the heater without air flow, i.e. and air flow switch. Incoming air should be filtered prior to passing through the heater and be free of moisture, condensation or other contaminants.

Model Number	Volts	Watts	Heated Length mm (inch)	Watts/ Inch [†]	Maximum CFM	Diameter mm (inch)	NPT Fitting	Weight g (lb)	
120 Vac Models									
AHP-3741	120	200	889 (3½)	57	8	10 (¾)	1/4"	82 (0.18)	
AHP-5051	120	400	114 (4½)	88	10	13 (½)	3⁄8"	113 (0.25)	
AHP-7561	120	750	140 (5½)	136	20	19 (¾)	3/4"	308 (0.68)	
20/240 Vac Models**									
AHP-3742	120 240	50 200	889 (3½) 889 (3½)	14 57	8 8	10 (%)	1⁄4"	82 (0.18)	
AHP-5052	120 240	100 400	114.3 (4½) 114.3 (4½)	22 80	10 10	13 (½)	3⁄8"	113 (0.25)	
AHP-7562	120 240	190 750	139.7 (5½) 139.7 (5½)	34 136	20 20	19 (¾)	3⁄4"	308 (0.68)	

* Indicates watts per inch of heated length. The watts per inch of heated length can be changed by reducing the operating voltage or by ordering a custom made heater.


** These air heaters can be operated on either 120 or 240V. Specifications are shown for operation on both 120 and 240V.

Specifications

Pressure Rating:80PSIGWattage Tolerance:+5,-10% or better at the voltage specifiedMaximum Outlet Temperature:1000°FMaximum Inlet Temperature:250°F

Construction

- Optional stainless steel bushing
- 2. Ceramic coil support
- Resistance element
- 4. Stainless steel sheath
- 5. Silver solder
- 6. Fiberglass insulated leads
- 7. Epoxy seal
- 8. Copper tee
- 9. Heliarc weld
- 10. Optional brass bushing



Pressure Drop vs. Air Flow

3/8

1/2

10

Air Flow (SCFM)

15

Purchase Order number to cover the COST of the repair, Model and serial number of the product and

3. Repair instructions and/or specific problems relative to the product.

20

5

Maximum Watts Per Linear Inch of Heated Length

Minimum CFM Required	½" Diameter	½" Diameter	¾" Diameter	
1	60	80	120	
2	60	80	120	
4	100	100	120	
6	150	150	150	
8	200	200	200	
10	-	250	250	
15	-	-	375	
20	-	-	500	

MEGA

omega.com info@omega.com

Servicing North America:

U.S.A.

Headquarters: Omega Engineering, Inc. Toll-Free: 1-800-826-6342 (USA & Canada only) Customer Service: 1-800-622-2378 (USA & Canada only) Engineering Service: 1-800-872-9436 (USA & Canada only)

Tel: (203) 359-1660 Fax: (203) 359-7700

e-mail: info @omega.com

For Other Locations Visit

omega.com/worldwide

The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

WARRANTY/DISCLAIMER

10.0

2.5

0

(psig) 7.5

Pressure Drop 5.0

OMEGA ENGINEERING, INC., warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product. If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of everseive corresion, or current heat moisture or ybiration improper

improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs. OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MARKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY. The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

damages. CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity; medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS/INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence. The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **NON-WARRANTY RETURNS**, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA. FOR WARRANTY RETURNS, please have the following

information available BEFORE contacting OMEGA 1. Purchase order number which the product was

- PURCHASED.
- 2. Model and serial number of the product under warranty, and
- 3. Repair instructions and/or specific problems relative to the product. OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords customers

the latest technology and engineering. OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© COPYRIGHT 2017 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, translated, or reduced to any electronic medium-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.