

PHH-127

Multi-Parameter Water Quality Monitor

INSTRUCTION
SHEET

M4930/0511

Shop online at: omega.com e-mail: info@omega.com
For latest product manuals: omegamanual.info

MADE IN TAIWAN

Specifications

Range

EC: 0.00 to 19.99 mS	pH: 0.00 to 14.00
CF: 0.0 to 199.9	mV: 0 to ±1999
TDS: 10 to 19990 ppm	
°C: -50 to 70°C	°F: -58 to 158°F


Resolution

EC: 0.01 mS	pH: 0.01
CF: 0.1	mV: 1
TDS: 10 ppm	°C: 0.1 °F: 0.2°

Accuracy

pH: ±0.1
°C: ±1.0
mV: ±0.1% F. S ±1 digit
EC, CF, TDS: ±2% F S
Operating Temperature Compensation: 0 to 50°C
Power: Rechargeable battery (included) with 120Vac power adaptor (included)
Dimensions: 155 x 86 x 22 mm
Weight: 230 g

Front Panel Description



- | | |
|------------------------------|-------------------------------------|
| ① Display | ⑦ °C/°F action function switch |
| ② Power adaptor receptacle | ⑧ EC/CF/ppm action function switch |
| ③ pH action function switch | ⑨ EC/CF/TDS calibration inset |
| ④ ORP action function switch | ⑩ pH or ORP probe inset |
| ⑤ pH 4.0 calibration inset | ⑪ EC/CF/TDS/Temperature probe inset |
| ⑥ pH 7.0 calibration inset | ⑫ ON/OFF switch |

Operating Information

1. Connect the power adaptor to the power supply outlet.
2. Connect the pH or ORP electrode to the BNC on the instrument. Remove the protective cap.
3. Turn on the meter.
4. Immerse the electrode in the solution to be tested. Stir gently and wait for the reading to stabilize.
5. Press the °C/°F key, choose the °C/°F for measuring. Press the “EC/CF/ppm” key, choose EC, CF, or TDS for measuring.
6. When you connect the ORP electrode, press the “MV” key. It will show the ORP value.
7. After use, turn off the meter. Rinse the electrode with tap water to minimize contamination. Replace the protective cap with pH4 buffer to keep the pH/ORP sensor wet.

Calibration

1. pH Calibration

- Pour a small quantity of pH7.0, and pH4.0 solution into clean beakers.
- For a particularly accurate calibration, it is advised to use two beakers for each buffer solution; the first is to be used for rinsing the electrode, the second is to be used for the calibration. In this way, the risks of contaminating the buffer solution are reduced to a minimum.
- Connect the power adaptor. Turn on the meter.
- Immerse the pH electrode in pH7.0 buffer solution, and gently stir it.
- Allow the reading to stabilize and with the supplied screwdriver, adjust the “pH7.0” calibration trimmer to read “7.0” pH or 10.0. Rinse the electrode with distilled water, and wipe it with filter-paper.
- Immerse the pH electrode in pH4.0 or 10.0 buffer solution, and gently stir it.
- Allow the reading to stabilize and with the supplied screwdriver, adjust the “pH4.0” calibration trimmer to read “4.0” pH. Rinse the electrode with distilled water, and wipe it with filter-paper.

2. EC, CF, ppm Calibration

- Press the “EC/CF/ppm” key. Choose the “EC” for operating. Immerse the meter in 1413µs/cm (1.413mS) calibrated solution.
- Allow the reading to stabilize and with a small screwdriver turn the CAL calibration trimmer until the display shows “1.41EC”. Rinse the electrode with distilled water, and wipe it with filter-paper.

Important

The instrument’s pH range must be re-calibrated whenever:

- The electrode has been used (laid) for a long time from the last calibration.
- The electrode has been used in particularly taxing conditions.
- The utmost accuracy is required.

Notice

- Stir the sensor gently when using.
- In case of abnormal phenomena such as high measured deviation, blinking measured value, no zero resetting, etc., please immerse the electrode in alcohol for cleaning (5 minutes maximum) or replace as needed.
- If the protective cap has been without electrolyte, or if the electrode has not been used for a short time, the electrode may be reactivated by leaving it for several hours in a beaker containing normal tap water or buffer 4.
- If reactivation cannot be done, the electrode must be replaced.
- Without using power adaptor, if the meter can not be switched on or the display fades, connect the power adaptor to the power supply outlet. It will charge the rechargeable battery and it is operational while charging.



OMEGAnet® Online Service omega.com	Internet e-mail info@omega.com
---------------------------------------	-----------------------------------

Servicing North America:

U.S.A.: Omega Engineering, Inc., One Omega Drive, P.O. Box 4047
ISO 9001 Certified Stamford, CT 06907-0047
 Toll-Free: 1-800-826-6342 Tel: (203) 359-1660
 FAX: (203) 359-7700 E-mail: info@omega.com

Canada: 976 Bergar
 Laval (Quebec), H7L 5A1 Canada
 Toll-Free: 1-800-826-6342 TEL: (514) 856-6928
 FAX: (514) 856-6886 e-mail: info@omega.com

Servicing Europe:

Benelux: Managed by the United Kingdom Office
 Toll-Free: 0800 099 3344 TEL: +31 20 347 21 21
 FAX: +31 20 643 46 43 e-mail: sales@omegaeng.nl

Czech Republic: Frystatska 184
 733 01 Karviná, Czech Republic
 Toll-Free: 0800-1-66342 TEL: +420-59-6311899
 FAX: +420-59-6311114 e-mail: info@omegashop.cz

France: Managed by the United Kingdom Office
 Toll-Free: 0800 466 342 TEL: +33 (0) 161 37 29 00
 FAX: +33 (0) 130 57 54 27 e-mail: sales@omega.fr

Germany/Austria: Daimlerstrasse 26, D-75392 Deckenpfronn, Germany
 Toll-Free: 0800 6397678 TEL: +49 (0) 7056 9398-0
 FAX: +49 (0) 7056 9398-29 e-mail: info@omega.de

For immediate technical or application assistance:

U.S.A. and Canada: Sales Service: 1-800-826-6342/1-800-TC-OMEGA®
 Customer Service: 1-800-622-2378/1-800-622-BEST™
 Engineering Service: 1-800-872-9436/1-800-USA-WHEN®

Mexico/Latin America: En Español: 001 (203) 359-7803 FAX: 001 (203) 359-7807
 info@omega.com.mx e-mail:espanol@omega.com

United Kingdom: OMEGA Engineering Ltd.
 One Omega Drive, River Bend Technology Centre, Northbank
ISO 9001 Irlam, Manchester M44 5BD United Kingdom
 Toll-Free: 0800-488-488 TEL: +44 (0) 161 777-6611
 FAX: +44 (0) 161 777-6622 e-mail: sales@omega.co.uk

It is the policy of OMEGA Engineering, Inc. to comply with all worldwide safety and EMC/EMI regulations that apply. OMEGA is constantly pursuing certification of its products to the European New Approach Directives. OMEGA will add the CE mark to every appropriate device upon certification. The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.

WARNING: These products are not designed for use in, and should not be used for, human applications.

WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

1. Purchase Order number under which the product was PURCHASED,
2. Model and serial number of the product under warranty, and
3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

1. Purchase Order number to cover the COST of the repair,
2. Model and serial number of the product, and
3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering.

OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2011 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced in any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.