


HHLM1337

Digital Light Meter

INSTRUCTION SHEET

M5306/0813





- Data-hold function for holding measuring values.
- Unit and sign display for easy reading.
- Automatic zeroing.
- Meter corrected for spectral relative efficiency.
- Correction factor need not be manually calculated for nonstandard light sources.
- Short rise and fall times.
- · Capable of selecting measuring mode in lux or fc scale, alternatively.
- Maximum and minimum measurements.

III SPECIFICATIONS

- Display : 3-1/2 digit LCD.
- Measuring Range : 20.00 lux, 200.0 lux, 2000 lux, 20.00 Klux / 20.00 fc, 200.0 fc, 2000 fc, 20.00 Kfc.
 Note : 1fc =10.76 lux , 1Klux ≈1000 lux , 1Kfc = 1000fc
- Note : 11C = 10.76 ux , 1000 ux , 1000 ux , 1000
- Overrange Display : LCD will show "OL" symbol.
- Spectral Response : CIE Photopic. (CIE human eye response curve).
- Spectral Accuracy : CIE V λ function f '1 \leq 6%
- Cosine Response : f'₂ ≦2%
- Accuracy : \pm 3% rdg $\pm\,$ 0.5% f.s. (\pm 4% rdg $\pm\,$ 10 dgls as > 10,000 lux/fc range) .

(calibrated to standard incandescent lamp at color temperature 2856 K $\rangle\,$.

- Repeatability : ± 2% .
- Temperature Characteristics : ± 0.1%/°C.
- Sampling Rate : 2.5 times/sec.
- Photo Detector : One silicon photo diode and spectral response filter.
- Operating Temperature & Humidity : 0°C to 40°C (32°F to 104°F) & 0% to 80% RH.

INSTRUCTION

- The digital illuminance meter is a precision instrument used to measure illuminance (lux, footcandle) in the field.
- It is meet CIE photopic spectral response, $f_1^* \leq 6\%$.
- It is fully cosine corrected for the angular incidence of light.
- The illuminance meter is compact, tough and easy to handle owing to its construction.
- The light sensitive component used in the meter is a very stable, long-life silicon phote diode and spectrel response filter.
- U.S. Pat. No. Des. 446,135
- U.S. Pat. No. Des. 469,025

II FEATURES

 Light-measuring levels ranging from 0.01 lux - 20.00 klux / 0.01 fc - 20.00 kfc, repeatedly.


1

· High accuracy and rapid response.

Storage Temperature and Humidity : -10°C to 50°C (14°F to 140°F) & 0% to 70% RH.

- Power Source : 6 pcs size AAA battery.
- Battery life (typical) : 400 hours (carbon zine).
- Photo detector Lead Length : 150 cm (approx.).
- Photo detector Dimensions : 92Lx 60Wx 29H (mm);
- Meter Dimensions : 150Lx 72Wx 35H (mm);
- Weight : 320g .
- Accessories : Carry case, instruction manual, battery.

IV NAME OF PARTS AND POSITIONS



- 2. Power Control key : The power switch key turns the illuminance meter ON or OFF.
- Range Selector key : It indicates 20.00 lux, 2000 lux, 2000 lux, 2000 lux, 20.00 Klux / 20.00 fc, 200.0 fc, 2000 fc, 20.00 Kfc, total 4 range for lux and 4 range for fc.
- 4. Data-Hold key : Data Hold control key.
- 5. Lux/fc key : Illuminance scale selects. 1 footcandle = 10.76 lux.
- 6. MX/MN key : Maximum and Minimum reading recorder control key.
- 7. Photo Detector.

V OPERATING INSTRUCTIONS

- 1. Power-up : Press the power key to turn the meter ON or OFF.
- 2. Selecting the lux or fc scale : Set the range selection switch to desired lux or fc range.
- 3. Remove the photo detector cap and face to light sourse in a horizontal position
- 4. Read the illuminance nominal from the LCD display.
- 5. Overange : If the instrument only display "OL", the input signal is too strong, and a higher range should be selected.
- Data-Hold mode : Press the HOLD key to select Data-Hold mode. When HOLD mode is selected, the illuminance meter will stop all further measurements.

Press the HOLD key again to exit DATA-HOLD mode. Then it resumes normal operation.

4

VIII MAINTENANCE

- 1. The white plastic disc on the top of the detector should be cleaned with a damp cloth when necessary.
- 2. Do not store the instrument where temperature or humidity is excessively high.
- 3. The reference level, as marker on the face plate, is the tip of the photo detector globe.
- 4. The calibration interval for the photo detector will vary according to operational conditions, but generally the sensitivity decreases in direct proportion to the product of luminous intensity by the operational time. In order to maintain the basic accuracy of the instrument, periodic calibration is recommended.

IX RECOMMENDED ILLUMINATION						
1fc = 10.76 łux						
LOCATIONS	lux	fc				
 OFFICE Conference, Reception room. Clerical work Typing drafting 	200 ~ 750 700 ~ 1,500 1000 ~ 2,000	18 ~ 70 65 ~ 140 93 ~ 186				
• FACTORY Visual work at production line Inspection work Electronic parts assembly line Packing work, Entrance passage	300 ~ 750 750 ~ 1,500 1500 ~ 3,000 150 ~ 300	28 ~ 70 70 ~ 140 140 ~ 279 14 ~ 28				

to exit this mode.


8. When the measurement is completed, replace the photo detector cap and turn the meter off.

VI BATTERY CHECK-UP & REPLACEMENT

- As the battery power is not sufficient, LCD will display "BT": and, replacement of one new batterie type 6×1.5V is required.
- 2. After turning off the meter, press the battery cover and push in the direction of the arrow to open.
- Disconnect the battery from the instrument and replace it with a standard 6×1.5V battery and go for the cover.

VII SPECTRAL SENSITIVITY CHARACTERISTIC

 To the detector, the applied photo diode with filters makes the spectral sensitivity characteristic almost meet C.I.E. (INTERNATIONAL COMMISSION ON ILLUMINATION) photopic curve V(λ) as the following chart described.



•	HOTEL Public room, Cloakroom Reception Cashier	100 ~ 200 200 ~ 500 750 ~ 1000	9 ~ 18 18 ~ 47 70 ~ 93
•	STORE Indoors Stairs Corridor Show window, Packing table Forefront of show window	150 ~ 200 750 ~ 1,500 1500 ~ 3,000	14 ~ 18 70~140 140 ~279
•	HOSPITAL Sickroom, Warehouse Medical Examination room Operating room Emergency Treatmet	100 ~ 200 300 ~ 750 750 ~ 1,500	9 ~ 18 28 ~ 70 70 ~ 140
•	SCHOOL Auditorium, Indoor Gymnasium Class room Laboratory, Library, Drafting, room	100 ~ 300 200 ~ 750 500 ~ 1,500	9 ~ 28 18 ~ 70 47 ~ 140



omega.com info@omega.com

U.S.A.:	Servicing North America:	• • • • • • • • • •		1 \
0.5.A.:	Omega Engineering, Inc., One Omega Drive, P.O. Box 4047, Stamford, CT 06907-0047 U.S.A. Toll-Free: 1-800-826-6342 (USA & Canada only)	France:	Freephone: 0805 541 038 (Fra Tel: 01 57 32 48 17 e-mail: esales@omega.fr	ance only) Fax: 01 57 32 48 18 Web: www.omega.fr
	Customer Service: 1-800-622-2378 (USA & Canada only) Engineering Service: 1-800-872-9436 (USA & Canada only) Tel: (203) 359-1660 Fax: (203) 359-7700 e-mail: info@omega.com	Germany/Austria	: Freephone: 0800 826 6342 (G Tel: +49 (0)7056-9398-0 e-mail: info@omega.de	Germany only) Fax: +49 (0)7056-9398-29 Web: www.omega.de
Canada:	Toll-Free: 1-800-826-6342 (USA & Canada only) Tel: (514) 856-6928 Fax: (514) 856-6886 e-mail: generalinfo@omega.ca Web: www.omega.ca	Italy:	Freephone: 800 906 907 (Ital) Tel: +39 022 333 1521 e-mail: commerciale@it.omeg Web: it.omega.com	Fax: +39 022 333 1522
Mexico/ Latin America:	Servicing Mexico and Latin America: Tel: 001-800-099-0420 (Mexico Only) Tel: 001-203-359-7577 (Outside Mexico) Fax: 001-203-968-7290 e-mail: ventas@mx.omega.com Web: mx.omega.com	Netherlands: Benelux	Freephone: 0800 099 3344 (N Tel: +31 070 770 3815 e-mail: esales@omega.nl	Vetherlands only) Fax: +31 070 770 3816 Web: www.omega.nl
		Spain:	Freephone: 800 900 532 (Spa Tel: +34 911 776 121 e-mail: ventas@es.omega.com Web: es.omega.com	Fax: +34 911 776 122
China:	Servicing Asia: Hotline: (+86) 800 819 0559, (+86)400 819 0559 e-mail: info@cn.omega.com Web: cn.omega.com	United Kingdom:	Freephone: 0800 488 488 (Ur Tel: +44 (0)161 777 6611 e-mail: sales@omega.co.uk	Fax: +44 (0)161 777 6622

WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of 13 months from date of purchase. OMEGA'S WARRANTY adds an additional one (1) month grace period to the normal one (1) year product warranty to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence. The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

- 1. Purchase Order number under which the product was PURCHASED,
- 2. Model and serial number of the product under warranty, and
- 3. Repair instructions and/or specific problems relative to the product.
- FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:
- 1. Purchase Order number to cover the COST of the repair,
- 2. Model and serial number of the product, and
- 3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering. OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2013 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.

Where Do I Find Everything I Need for Process Measurement **OMEGA...Of** Course! and Control? Shop online at omega.com™

TEMPERATURE

- MPERALORE Thermocouple, RTD & Thermistor Probes, Connectors, Panels & Assemblies Wire: Thermocouple, RTD & Thermistor Calibrators & Lee Point References Recorders, Controllers & Process Monitors
- Wire: Thermocouple,
 Calibrators & Ice Poir
 Recorders, Controllers
 Infrared Pyrometers

PRESSURE, STRAIN AND FORCE

- Transducers & Strain Gages
 Load Cells & Pressure Gages
 Displacement Transducers
 Instrumentation & Accessories

FLOW/LEVEL Rotameters, Gas Mass Flowmeters &

- Flow Computers
- Air Velocity Indicators Turbine/Paddlewheel Systems Totalizers & Batch Controllers

PH/CONDUCTIVITY

- pH Electrodes, Testers & Accessories Benchtop/Laboratory Meters Controllers, Calibrators, Simulators & Pumps Industrial pH & Conductivity Equipment

DATA ACQUISITION

- Data Acquisition & Engineering Software
 Communications-Based Acquisition Systems
 Plug-in Cards for Apple, IBM & Compatibles
 Data Logging Systems
 Recorders, Printers & Plotters

- HEATERS

- Heating Cable
 Cartridge & Strip Heaters
 Immersion & Band Heaters
 Flexible Heaters
- Flexible Heaters
 Laboratory Heaters

ENVIRONMENTAL MONITORING AND CONTROL

- Hotering & Control Instrumentation
 Refractometers
 Pumps & Tubing
 Air, Soil & Water Monitors
 Industrial Water & Wastewater Treat
 pH, Conductivity & Dissolved Overset Pumps & Tubing Air, Soil & Water Monitors Industrial Water & Wastewater Treatment pH, Conductivity & Dissolved Oxygen Înstruments