


ELECTRIC MOTOR HEATER

MH Series
Starts at
\$67



MH Series, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)					
Model No.	Size	Watts	Volts	Amps	Price
MH-105-120	1.00 x 5.00"	25	120	0.21	\$67
MH-105-240	1.00 x 5.00"	25	240	0.10	67
MH-110-120	1.00 x 10.00"	50	120	0.42	78
MH-110-240	1.00 x 10.00"	50	240	0.21	78
MH-115-120	1.00 x 15.00"	75	120	0.63	86
MH-115-240	1.00 x 15.00"	75	240	0.31	86
MH-120-120	1.00 x 20.00"	100	120	0.83	95
MH-120-240	1.00 x 20.00"	100	240	0.42	95
MH-125-120	1.00 x 25.00"	125	120	1.04	105
MH-125-240	1.00 x 25.00"	125	240	0.52	105
MH-215-120	2.00 x 15.00"	150	120	1.25	110
MH-215-240	2.00 x 15.00"	150	240	0.63	110
MH-220-120	2.00 x 20.00"	200	120	1.67	118
MH-220-240	2.00 x 20.00"	200	240	0.83	118
MH-225-120	2.00 x 25.00"	250	120	2.08	127
MH-225-240	2.00 x 25.00"	250	240	1.05	127

Motor Heaters (MH series heaters) are designed to control moisture build-up on the electric motor windings. Condensation build-up in the motor can result in premature failure of the electric motor. Moisture condensation occurs when moist air comes in contact with the cold metal surface. Over a period of time the moisture deteriorates the electric windings in the motor. Flexible motor heaters provide heat to the electrical windings preventing moisture to collect in the motor.

MH series heater also benefits electrical motors by ensuring warm start-ups, extended bearing life and adds freeze protection to electrical motors.

Comes complete with termination 24" PTFE lead wires.

Ordering Example: MH-105-120, motor heater, 25 W, 120V, \$67.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters