

OVER-THE-SIDE IMMERSION HEATERS FOR MILDLY CORROSIVE FLUIDS



TLS and KTLS Series
Starts at

\$1100

- ✓ 2 to 18 kW
- ✓ 120, 240, 480V, 1 and 3 Phase
- ✓ Stainless Steel Sheath and Riser Elements
- ✓ Optional Thermostat Kits are Available to Fit into Terminal Box

FEATURES

These over-the-side immersion heaters are designed for installing in the top of a tank with the heated portion directly immersed along the side or at the bottom. This provides easy removal of the heater and ample working space inside the tank.

APPLICATIONS

Alkaline cleaners (electrified), alkaline soaking cleaners, copper sulfate, electroless copper, electro cleaners, mild acid baths, wash tanks dip tanks containing alkali, oakite, caustic soda, detergent and other aqueous solutions

SPECIFICATIONS

Wattage: 2 to 18 kW
Power: 120, 240, 480V, 1 & 3
Watt Density: 40 W/in²

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.



TLS-220A-036/120V, \$1100, shown smaller than actual size.

KTLS-220A-036/120V, \$1200, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| kW | Riser (A) cm (in) | Straight Elements | | | Curved Elements | | | Wt. lb (kg) |
|---|----------------------|------------------------------------|---------------------|--------|------------------------------------|----------------------|--------|----------------|
| | | Min. Tank Clearance (B)—cm (in) | Model No. | Price | Min. Tank Clearance (B)—cm (in) | Model No. | Price | |
| Two Elements—Stainless Steel, 40 W/in.² | | | | | | | | |
| 2 | 91 (36) | 31 (12¼) | TLS-220A-036/120 | \$1100 | 27 (10%) | KTLS-220A-036/120 | \$1200 | 8 (4) |
| 2 | 91 (36) | 31 (12¼) | TLS-220A-036/* | 1100 | 27 (10%) | KTLS-220A-036/* | 1200 | 8 (4) |
| 4 | 91 (36) | 57 (22¼) | TLS-240A-036/120 | 1200 | 35 (13%) | KTLS-240A-036/120 | 1300 | 8 (4) |
| 4 | 91 (36) | 57 (22¼) | TLS-240A-036/* | 1200 | 35 (13%) | KTLS-240A-036/* | 1300 | 8 (4) |
| 6 | 91 (36) | 75 (29½) | TLS-260A-036/120 | 1300 | 41 (16%) | KTLS-260A-036/120 | 1400 | 10 (5) |
| 6 | 91 (36) | 75 (29½) | TLS-260A-036/* | 1300 | 41 (16%) | KTLS-260A-036/* | 1400 | 10 (5) |
| 8 | 91 (36) | 95 (37%) | TLS-280A-036/* | 1450 | 47 (18%) | KTLS-280A-036/* | 1450 | 12 (5) |
| 10 | 121 (48) | 103 (45) | TLS-210A-048/* | 1500 | 54 (21¼) | KTLS-210A-048/* | 1550 | 14 (6) |
| 12 | 121 (48) | 133 (52½) | TLS-212A-048/* | 1600 | 59 (23%) | KTLS-212A-048/* | 1650 | 16 (7) |
| Three Elements—Stainless Steel, 40 W/in.² | | | | | | | | |
| 3 | 91 (36) | 31 (12¼) | TLS-330A-036/120 | \$1250 | 27 (10%) | KTLS-330A-036/120 | \$1350 | 9 (4) |
| 3 | 91 (36) | 31 (12¼) | TLS-330A-036/240/** | 1250 | 27 (10%) | KTLS-330A-036/240/** | 1350 | 9 (4) |
| 3 | 91 (36) | 31 (12¼) | TLS-330A-036/480/** | 1250 | 27 (10%) | KTLS-330A-036/480/** | 1350 | 9 (4) |
| 6 | 91 (36) | 57 (22¼) | TLS-360A-036/120 | 1400 | 35 (13%) | KTLS-360A-036/120 | 1500 | 10 (5) |
| 6 | 91 (36) | 57 (22¼) | TLS-360A-036/240/** | 1400 | 35 (13%) | KTLS-360A-036/240/** | 1500 | 10 (5) |
| 6 | 91 (36) | 57 (22¼) | TLS-360A-036/480/** | 1400 | 35 (13%) | KTLS-360A-036/480/** | 1500 | 10 (5) |
| 9 | 91 (36) | 75 (29½) | TLS-390A-036/240/** | 1450 | 41 (16%) | KTLS-390A-036/240/** | 1600 | 12 (5) |
| 9 | 91 (36) | 75 (29½) | TLS-390A-036/480/** | 1450 | 41 (16%) | KTLS-390A-036/480/** | 1600 | 12 (5) |
| 12 | 121 (48) | 95 (37%) | TLS-312A-048/240/** | 1550 | 47 (18%) | KTLS-312A-048/240/** | 1700 | 14 (6) |
| 12 | 121 (48) | 95 (37%) | TLS-312A-048/480/** | 1550 | 47 (18%) | KTLS-312A-048/480/** | 1700 | 14 (6) |
| 15 | 121 (48) | 103 (45) | TLS-315A-048/240/** | 1650 | 54 (21¼) | KTLS-315A-048/240/** | 1850 | 16 (7) |
| 15 | 121 (48) | 103 (45) | TLS-315A-048/480/** | 1650 | 54 (21¼) | KTLS-315A-048/480/** | 1850 | 16 (7) |
| 18 | 121 (48) | 133 (52½) | TLS-318A-048/240/** | 1750 | 60 (23½) | KTLS-318A-048/240/** | 1950 | 18 (8) |
| 18 | 121 (48) | 133 (52½) | TLS-318A-048/480/** | 1750 | 60 (23½) | KTLS-318A-048/480/** | 1950 | 18 (8) |

* Designate voltage, i.e. insert "240" for 240V for "480V" for 480V. ** Add the suffix "3P" to the model number for 3 phase power.

Optional thermostat kits are available to fit into heater terminal box.

Ordering Examples: TLS-220A-036/240, 2 kW heater powered by 1 phase 240 Vac, \$1100.

TLS-330A-036/240/3P, 3 kW heater powered by 3 phase 240 Vac, \$1250.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters