

CORROSION RESISTANT OVER-THE-SIDE IMMERSION HEATERS

TPR Series Starts at
\$550



TPR—Round Cross Section Elements

- ✓ Fluoropolymer Coated Stainless Steel Elements
- ✓ 20 W/in²
- ✓ 1 to 8 kW
- ✓ 120, 240 and 480V, 1 Phase
- ✓ Moisture Resistant Terminal Enclosure

FEATURES



- ✓ Moisture Resistant Terminal Enclosure
- ✓ Standard Polypropylene Guard
- ✓ Side Mounted Construction with PVC Mounting Flange
- ✓ Overtemperature Protection Integral Manual Reset Cutout [116°C (240°F)]
- ✓ Low Profile, Light Weight

1. Corrosion Resistant:

Thermoplastic fluoropolymer coated stainless steel sheath for long life in almost all types of corrosive solutions for operating temperatures up to 212°F. Pin hole free, durable coating, 100% tested at factory.

2. Overtemperature Shutoff:

Standard on all units. A manual reset cutout will deactivate the heater in the event of an overtemperature condition (rated 25 amps up to 277 volts). A visual minimum level indication is also provided on the heater guard.




3. **Low Profile:** Single and three phase heaters have flat profiles which permit maximum work area and minimum interference with plating process. Heater projects less than 2" away from the side of the tank.

Continued on page 114

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.



MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)

Watts	Volts	Dimensions: cm (in)		Model No.	Price	Weight kg (lb)
		A	B			
1000	120	33 (13)	15 (6)	TPR-101	\$550	2 (4)
1000	240	33 (13)	15 (6)	TPR-102	550	2 (4)
2000	240	53 (21)	30 (12)	TPR-202	650	2 (5)
2000	480	53 (21)	30 (12)	TPR-204	650	2 (5)
3000	240	66 (26)	43 (17)	TPR-302	800	3 (6)
3000	480	66 (26)	43 (17)	TPR-304	800	3 (6)
4000	240	79 (31)	56 (22)	TPR-402	1050	3 (7)
4000	480	79 (31)	56 (22)	TPR-404	1050	3 (7)
6000	240	107 (42)	84 (33)	TPR-602	1300	5 (10)
6000	480	107 (42)	84 (33)	TPR-604	1350	5 (10)
8000	240	135 (53)	112 (44)	TPR-802	1750	5 (12)
8000	480	135 (53)	112 (44)	TPR-804	1750	5 (12)

Ordering Example: TPR-202 single phase, round cross section element immersion heater, 2000 W, 240V, \$650.

CORROSION RESISTANT OVER-THE-SIDE IMMERSION HEATERS

TPF Series
Starts at
\$915



TPF—Flat Elements

- ✓ Fluoropolymer Coated Stainless Steel Thinblade Elements
- ✓ 20 W/in²
- ✓ 3 to 10 kW
- ✓ 240 and 480V, 3 Phase
- ✓ Moisture Resistant Terminal Enclosure

FEATURES

- ✓ Moisture Resistant Terminal Enclosure
- ✓ Standard Polypropylene Guard
- ✓ Side Mounted Construction with PVC Mounting Flange
- ✓ Overtemperature Protection Integral Manual Reset Cutout (240°F)
- ✓ Low Profile, Light Weight

4. Vapor Tight Terminal:

Enclosure of PVC material with left or right hand conduit entry.

5. Mounting Bracket:



Made of PVC material with conveniently located mounting slots.

6. Polypropylene Guard:

Standard on all units. It protects the heater from work in process in heating tank. Guard easily disassembles for ease of cleaning heating elements.

7. Grounded Construction:

With metal sheath heating elements to allow for proper grounding safety.




TPF-Flat Element, Three Phase Models

8. **Low Watt Density:** 20 watts per square inch heat output suitable for almost all corrosive solutions.
9. **Light Weight:** Simple design permits easy installation and removal for cleaning.

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Watts	Volts	Dimensions: cm (in)		Model No.	Price	Weight kg (lb)
		A	B			
3000	240	51 (20)	28 (11)	TPF-302	\$1000	4 (8)
3000	480	51 (20)	28 (11)	TPF-304¹	795	4 (8)
4000	240	58 (23)	36 (14)	TPF-402	1100	4 (9)
4000	480	58 (23)	36 (14)	TPF-404¹	1100	4 (9)
6000	240	76 (30)	53 (21)	TPF-602	1450	5 (11)
6000	480	76 (30)	53 (21)	TPF-604¹	1450	5 (11)
8000	240	94 (37)	71 (28)	TPF-802	1750	5 (12)
8000	480	94 (37)	71 (28)	TPF-804¹	1750	5 (12)
10000	240	112 (44)	89 (35)	TPF-1002	2150	6 (14)
10000	480	112 (44)	89 (35)	TPF-1004¹	2150	6 (14)

¹ Not UL Listed or CSA Certified.

Ordering Example: TPF-404, three phase, flat element immersion heater, 4000 W, 480V, \$1100. It is not UL Listed or CSA Certified.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters