


FLANGED IMMERSION HEATERS FOR BOILERS AND WATER HEATERS

TTSF Series
Starts at
\$310




- ✓ 2½" (6 cm) Square Steel Flange
- ✓ Premium Quality
- ✓ Rugged Construction
- ✓ U.L. Component Recognized

Type TTSF heaters are used in industrial water boilers and storage tanks. They feature high watt density for rapid heat transfer. The steam boiler heaters feature the highest quality, high nickel Incoloy® sheath that provides the highest practical protection available against hard water containing minerals, scale and salts while resisting stress, corrosion, cracking, and sulphur attack. The water heater has a copper sheath and copper face plate. These heaters are not supplied with enclosures since they are normally mounted in boilers or tanks which have a surrounding enclosure for terminal protection.



TTSF-009, \$370, shown smaller than actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)								
kW	Volts	Circ.	Phase	W/in. ²	Dim. B in.(cm)	Model No.	Price	Wt. lb (kg)
Steam Boiler Heater Specifications—Incoloy Sheath								
5	208	1	3	94	12 (30)	TTSF-009	\$370	2 (0.9)
5	240	1	3	94	12 (30)	TTSF-010	370	2 (0.9)
10	208	1	3	79	24 ⁷ / ₁₆ (61)	TTSF-005	415	3 (1)
10	240	1	3	79	24 ⁷ / ₁₆ (61)	TTSF-006	415	3 (1)
10	480	1	3	79	24 ⁷ / ₁₆ (61)	TTSF-007	415	3 (1)
15	208	1	3	82	34 (84)	TTSF-002	450	4 (2)
15	240	1	3	82	34 (84)	TTSF-003	450	4 (2)
15	480	1	3	82	34 (84)	TTSF-001	465	4 (2)
Water Heater Specifications—Copper Sheath/Copper Face Plate								
13.5	208	1	3	184	13 ⁷ / ₁₆ (34)	TTSF-3135	\$310	2 (0.9)
13.5	480	1	3	184	13 ⁷ / ₁₆ (34)	TTSF-3135	310	2 (0.9)
15	480	1	3	153	17 ⁷ / ₁₆ (44)	TTSF-3150	395	3 (1)
18	480	1	3	153	21 ¹ / ₁₆ (53)	TTSF-3180	420	4 (2)

Ordering Examples: TTSF-009, 5 kW, 208V, flanged immersion heater Incoloy sheath, \$370. TTSF-3135, 13.5 kW 480V, immersion heater, copper sheath/copper face plate, \$310.

SPECIFICATIONS

Wattage: 5 to 18 kW
Power: 208 and 240 or 480 Vac, 3 Phase
Watt Density: 79 to 184 W/in.²
Sheath: 0.315" (0.8 cm) dia. Incoloy (steam boiler heater) or copper (water heater).

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters