

POCKET TEST GAUGES

76 mm (3") DIAL AND STAINLESS STEEL CASE

PGT Series

All Models
\$170



- ✓ 0.5% FS Accuracy
- ✓ Ideal "Tool Box" Test Gauge
- ✓ All Stainless Steel Construction

SPECIFICATIONS

Accuracy: 0.5% FS
Case: Polished stainless steel
Dial: White background with mirrored band
Pointer: Adjustable with knife-edge tip
Movement: Stainless steel
Element: 316 SS
Connection: ¼ NPT



PGT-30L-300, cover included, \$170, shown actual size.

Recommended Reference Book:
 OSHA Inspections, Preparation and Response,
GE-2064, \$64.95.
 See Section Y
 For Additional Books

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| MODEL NO. | PRICE | DIAL DIA. mm (in) | RANGE | GRADUATIONS FIGURE | |
|--------------|-------|----------------------|-----------|-----------------------|-------|
| | | | | MAJOR | MINOR |
| PGT-30L-15 | \$170 | 76 (3) | 0 to 15 | 1 | 0.1 |
| PGT-30L-30 | 170 | 76 (3) | 0 to 30 | 2 | 0.2 |
| PGT-30L-60 | 170 | 76 (3) | 0 to 60 | 5 | 0.5 |
| PGT-30L-100 | 170 | 76 (3) | 0 to 100 | 10 | 1 |
| PGT-30L-150 | 170 | 76 (3) | 0 to 150 | 10 | 1 |
| PGT-30L-200 | 170 | 76 (3) | 0 to 200 | 20 | 2 |
| PGT-30L-300 | 170 | 76 (3) | 0 to 300 | 20 | 2 |
| PGT-30L-400 | 170 | 76 (3) | 0 to 400 | 50 | 2 |
| PGT-30L-600 | 170 | 76 (3) | 0 to 600 | 50 | 5 |
| PGT-30L-1000 | 170 | 76 (3) | 0 to 1000 | 100 | 10 |

Ordering Examples: PGT-30L-100, pocket test gauge with 0 to 100 psi range, and stainless steel cover, \$170.
 PGT-30L-300, pocket test gauge with 0 to 300 psi range, and stainless steel cover, \$170.

LOW-PRESSURE DIAPHRAGM GAUGES

PGL Series


All Models
\$39



- ✓ Corrosion-Resistant Bronze Diaphragm
- ✓ 150% Overpressure Protection
- ✓ Recalibration Screw on Dial
- ✓ 2-1-2 ANSI Grade A Accuracy*

SPECIFICATIONS

Dial: 64 mm (2.5") Dia.
Pointer: Black aluminum
Movement: Brass
Element: Bronze diaphragm
Connection: ¼ NPT
Window: Polycarbonate
Media: Clean, dry, non-corrosive gas only



PGL-25L-100, \$39, shown larger than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| MODEL NO. | PRICE | RANGE/GRADUATIONS | | | | | |
|-------------|-------|--------------------------|-------------------------|----------------|-------------|---------------|-------------|
| | | OUTER SCALE | INNER SCALE | INNER SCALE | | OUTER SCALE | |
| | | | | FIG. INTERVALS | MINOR GRAD. | FIG INTERVALS | MINOR GRAD. |
| PGL-25L-10 | \$39 | 0/10 inH ₂ O | — | 1 | 0.1 | — | — |
| PGL-25L-15 | 39 | 0/15 inH ₂ O | 0/9 oz/in ² | 1 | 0.2 | 5 | 0.2 |
| PGL-25L-35 | 39 | 0/35 inH ₂ O | 0/20 oz/in ² | 5 | 0.5 | 5 | 0.5 |
| PGL-25L-60 | 39 | 0/60 inH ₂ O | 0/35 oz/in ² | 5 | 0.5 | 5 | 0.5 |
| PGL-25L-100 | 39 | 0/100 inH ₂ O | 0/60 oz/in ² | 10 | 1 | 10 | 1 |
| PGL-25L-160 | 39 | 0/160 inH ₂ O | — | 20 | 2 | — | — |
| PGL-25L-200 | 39 | 0/200 inH ₂ O | — | 20 | 2 | — | — |
| PGL-25L-300 | 39 | 0/300 inH ₂ O | — | 50 | 5 | — | — |

* 2% first 10%, 1% middle 80%, 2% last 10%.

Note: Cannot be oxygen cleaned.

Ordering Example: PGL-25L-100, low-pressure gauge with 0 to 100 inH₂O range, \$39.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters