


# 483 mm (19") Jack Panels

## Standard Connectors with Anodized Panels

### 19SJP Series



I.D. Labels supply loose for customer to identify in the field. Photo shown with labels for illustration purpose only.

OSW3, visit [omega.com](http://omega.com)

Switches and meter sold separately.

OSW3, visit [omega.com](http://omega.com)

DPI8C 1/8 DIN ultra compact meter, visit [omega.com](http://omega.com)

**Custom Panels Available! Contact Sales**

Shown smaller than actual size.

### 483 mm (19") Plain Panel Jacks

No. of Rows	Panel Height	Max No. of Jacks
1	89 mm (3 1/2")	22
2	133 mm (5 1/4")	44
3	178 mm (7")	66
4	222 mm (8 3/4")	88

### 483 mm (19") Jack Panels with Switch Cutout

No. of Rows	Panel Height	Switch Size	Max No. of Jacks
1	133 mm (5 1/4")	76 mm (3")	15
2	133 mm (5 1/4")	76 mm (3")	30
2	178 mm (7")	127 mm (5")	30
3	178 mm (7")	127 mm (5")	45
4	222 mm (8 3/4")	127 mm (5")	60

**Note:** When a switch is ordered with a panel, installation is included at no extra charge, add suffix "-MTG" to model number of switch or meter.

**Note:** Panels with switches and/or meters are not supplied wired.

Model No. ANSI Color Code	Total No. of Jacks	Switch Cutout	Meter Cutout
19SJP1-10-(*)	10	—	—
19SJP1-20-(*)	20	—	—
19SJP2-20-(*)	20	—	—
19SJP2-28-(*)	28	—	—
19SJP2-30-(*)	30	—	—
19SJP3-30-(*)	30	—	—
19SJP4-40-(*)	40	—	—
19SJP1-10-(*)-OSW	10	76 mm (3")	—
19SJP3-30-(*)-OSW	30	127 mm (5")	—
19SJP4-40-(*)-OSW	40	127 mm (5")	—
19SJP1-10-(*)-OSW-MTR	10	76 mm (3")	Yes
19SJP3-30-(*)-OSW-MTR	30	127 mm (5")	Yes
19SJP4-40-(*)-OSW-MTR	40	127 mm (5")	Yes

\*Insert calibration code J, K, T, E, R, S, U or N calibrations; for Types G, C or D, consult Sales for pricing information.

**Ordering Example:** 19SJP1-10-K, 483 L x 89 mm H (19 L x 3.5" H) jack panel with 1-row of 10 Type K calibration snap-in jack panels with the universal "fits all" female connector design.

Consult Custom Engineering Department for information on custom color-coded anodized panels or wired panels. Non-standard Panels: \$1,000 minimum order. Contact [custom@omega.com](mailto:custom@omega.com) for pricing and availability.

### 483 mm (19") Jack Panels with Switch and Meter Cutouts

No. of Rows	Panel Height (mm/in)	Switch Size (mm/in)	Max No. of Jacks
1	133 (5 1/4")	76 (3")	10
2	133 (5 1/4")	76 (3")	20
2	178 (7")	127 (5")	20
3	222 (8 3/4")	127 (5")	40
4	222 (8 3/4")	127 (5")	40

**Note:** A 1/8 DIN (45 x 92 mm) meter cutout is supplied unless otherwise specified.