

Introduction to DIN Rail Terminal Blocks



Visit us online for our complete line of terminal blocks

Stainless steel screws and serrated current bars provide a strong, corrosion-resistant grip.



Cone shaped guide allows easy wire insertion.

OMEGA's OMTBV7-W terminals are designed to meet the three most important criteria when selecting a terminal block line – ease of wiring, secure connections and durability. The line is also comprehensive, offering a wide array of terminal types for most circuits and functions, from control to low level power.

The Size You Need

OMTBV7-W feed-through terminals come in ten sizes and are rated to 600 Vac (800V-IEC). They accommodate a full range of wire sizes from 30 AWG to 3/0 AWG (0.5 mm² to 70 mm² wire cross section). Many "specialty" feed-through terminals are also available that provide multiple terminations or increase the density of connections. This reduces panel space and saves money.

Comprehensive Selection of Special Terminals

Aside from the broad selection of standard feed-through terminals, many special terminals are also part of the OMTBV7-W line, including:

- ✓ Two level terminals
- ✓ High Current terminals
- ✓ Ground terminals
- ✓ Dual connection terminals
- ✓ Diode and resistor terminals
- ✓ Plug-in style terminals
- ✓ Various isolating terminals
- ✓ Fuse terminals
- ✓ Sensor terminals
- ✓ Thermocouple terminals
- ✓ Proximity switch terminals

Even the most varied circuit requirements can be supported by the broad selection offered with this line.

Super Reliable Connections

The most important aspect of a terminal block is to join wires in a reliable connection. With OMTBV7-W terminals, a cone shaped guide allows easy insertion of the wire into a nickel plated barrel. As tightening torque is applied to strong stainless steel screws, the wire is secured between a recessed contact

pad and serrated current bar. This corrosion-resistant clamping mechanism provides excellent performance in the most demanding industrial conditions.


Superior Insulation and Protection Features

All metal parts are recessed, providing a touch-safe, dead front design for optimum safety. Terminal bodies are manufactured from Polyamide 6.6, known for its excellent thermal stability, impact resistance and resistance to electrical creepage. The insulating cases are rated up to 90°C (195°F) for continuous operation. They also stay elastic down to -40°C (-40°F) without fracturing.

International Approvals

OMEGA's OMTBV7-W terminal block line is UL recognized and CSA Certified. Many terminals have also been certified for use in hazardous locations. The line also carries the CE Mark for use in most international markets.

DIN Rail Fuse Terminal Blocks



Standard Fuse Blocks

To Order			
Terminal	Model No.	Model No.	Model No.
Black (Pkg of 10)	OMTBV7-WFB4-10	OMTBV7-WFB424-10	OMTBV7-WFB4250-10
Accessories			
End Barrier	Not Required	Not Required	Not Required
End Anchors -50 (pkg of 50) -10 (pkg of 10) Screw Type—Normal Duty Screw Type—Heavy Duty	OMTBV7-EA35-50 OMTBV7-EAH35-10	OMTBV7-EA35-50 OMTBV7-EAH35-10	OMTBV7-EA35-50 OMTBV7-EAH35-10
Jumpers (Pkg of 10) Side Jumper (10-pole Insulated)	OMTBV7-SJFB8-10-10	OMTBV7-SJFB8-10-10	OMTBV7-SJFB8-10-10
DIN rail, 35 x 7.5 mm x 2 m, slotted	XBANS3575P	—	—
DIN rail, 35 x 7.5 mm x 2 m, solid	XBANS3575U	—	—
DIN rail, 35 x 15 mm x 2 m, slotted	XBANS3515P	—	—
DIN rail, 35 x 15 mm x 2 m, solid	XBANS3515U	—	—
Blank marking tags, 8 x 12 mm, cards of 100	OMTBV7-SM8X12	OMTBV7-SM8X1	OMTBV7-SM8X12
Blank marking tags, 6 x 9 mm, cards of 100, for fuse handle	OMTBV7-SM6X9	OMTBV7-SM6X9	OMTBV7-SM6X9
Pre-printed marking tabs, single digit (0...9), sticks of 10	OMTBV7-MP	OMTBV7-MP	OMTBV7-MP

SPECIFICATIONS	OMTBV7-WFB4-10			OMTBV7-WFB424-10			OMTBV7-WFB4250-10		
Approvals									
Voltage Rating (AC/DC)	300V	300 VC	500V	300V	300V	500V	300V	300V	500V
Maximum Current	15 A	15 A	15 A	15 A	15 A	15 A	15 A	15 A	15 A
Wire Range (Rated Cross Section)	#22 to #12 AWG	#22 to #12 AWG	0.05 to 4 mm ²	#22 to #12 AWG	#22 to #12 AWG	0.05 to 4 mm ²	#22 to #12 AWG	#22 to #12 AWG	0.05 to 4 mm ²
Indicator Type	Non-Indicating			LED			Neon		
Leakage Current	—			2 mA @ 24V			1 mA @ 264 Vac		
Working Voltage	Per Fuse Rating			10 to 57 Vac/Vdc			85 to 264 Vac		
Fuse Size (not supplied)	5 x 20 mm			5 x 20 mm			5 x 20 mm		
Wire Strip Length	8 mm (0.31")			8 mm (0.31")			8 mm (0.31")		
Recommended Tightening Torque	0.6 Nm (5.0 to 5.6 lb-in.)			0.6 Nm (5.0 to 5.6 lb-in.)			0.6 Nm (5.0 to 5.6 lb-in.)		
Density	125/m (38 pcs./ft)			125/m (38 pcs./ft)			125/m (38 pcs./ft)		
Insulation Temperature Range	-40 to 90°C (-40 to 195°F)			-40 to 90°C (-40 to 195°F)			-40 to 90°C (-40 to 195°F)		

Fuses not included.

Ordering Examples: OMTBV7-WFB4-10, single circuit fuse block, pkg of 10, OMTBV7-EAH35-10, end anchors, and OMTBV7-SJFB8-10-10, jumpers. OMTBV7-WFB4250-10, single circuit fuse block with neon blown fuse indicator, 10 pack.