
## RTD Probes with Transitions



For 1/6" Diameter Sensor Visit



## **Standard Dimensions**

| To Order             |                  |               |  |
|----------------------|------------------|---------------|--|
| Model Number         | Lead Wire Style* | Sheath Length |  |
| PR-11-2-100-(*)-6-E  | 3 Wire           | 6"            |  |
| PR-11-2-100-(*)-9-E  | 3 Wire           | 9"            |  |
| PR-11-2-100-(*)-12-E | 3 Wire           | 12"           |  |
| PR-11-2-100-(*)-18-E | 3 Wire           | 18"           |  |
| PR-11-2-100-(*)-24-E | 3 Wire           | 24"           |  |

<sup>\*</sup> Specify "-1/8", "-3/16", or "-1/4" for probe diameter in inches. To order probes in intermediate lengths, change model number, using next longer probe. Over 24", add an additional cost per inch of probe length. Stainless steel overbraid or BX cable available. For 4-wire configuration, change "2" in model number to "3" for additional cost.

For longer leads, add the length in inches to the model number for additional cost, (Styles 2 & 3) or (Style 1).

**Ordering Example: PR-11-2-100-1/4-12-E-TA3F**, 100  $\Omega$ , class "A" RTD with a  $\frac{1}{4}$ " diameter by 12" long probe, 40" of 3-wire cable and TA3F connector.

## **Metric Dimensions**


| moule Dimensions      |                  |               |
|-----------------------|------------------|---------------|
| Model Number          | Lead Wire Style* | Sheath Length |
| PR-11-2-100-(*)-150-E | 3 Wire           | 150 mm        |
| PR-11-2-100-(*)-225-E | 3 Wire           | 225 mm        |
| PR-11-2-100-(*)-300-E | 3 Wire           | 300 mm        |
| PR-11-2-100-(*)-450-E | 3 Wire           | 450 mm        |
| PR-11-2-100-(*)-600-E | 3 Wire           | 600 mm        |


<sup>\*</sup> Specify "-M30" for 3 mm, "-M45" for 4.5 mm or "-M60" for 6 mm for probe diameter in millimeters. To order probes in intermediate lengths, change model number, using next longer probe price. Over 600 mm, add an additional cost per 25 mm of probe length. For 4-wire configuration, change "2" in model number to "3" for additional cost.

For longer leads, add the lead length in meters to the model number for an additional cost per meter (Styles 2 & 3) or (Style 1).


**Ordering Example: PR-11-2-100-M45-150-E-MTP,** 100  $\Omega$ , class "A" RTD with a 4.5 mm diameter by 150 mm long probe, 1 m of 3-wire cable and MTP connector.

These general purpose sensors can be used in most liquid and air applications. When used in liquid environments, the epoxy-sealed end should not be immersed directly into the liquid. These probes can be used as stand-alone sensors, or they can be configured with a variety of termination options, and combined with controllers, indicators, or precision thermometers to create complete measurement systems.





**Need a different resistance, temperature coefficient, cable length, cable type?** Use the Model Number Builder below to go beyond our stock product offering to construct the sensor that meets your specific needs. You can also visit our online store and select "Order by Model Number," and simply enter the model number and length modifications to automatically obtain price and availability.



<sup>\*</sup> Contact Sales for pricing.

Ordering Example: PR-10-2-100-3/16-12-E, 100  $\Omega$  class A RTD with  $\frac{3}{16}$  Dia. x 12" long probe, 1 m of 3-conductor cable.