


High Temperature Probes OMEGA™

Foundry Probe

SP-HF-K-6 Series

- ✔ Type K, CHROMEGA™-ALOMEGA™ Thermocouple Elements
- ✔ Measures Hot Metal Surfaces
- ✔ Rated up to 1260°C (2300°F)
- ✔ Extra Heavy-Duty Design
- ✔ 6 mm (¼") Diameter Contact Elements
- ✔ Works with High Temperature Impedance Type K Temperature Readouts
- ✔ Rugged, Heavy-Duty Aluminum Handle

CUSTOM ASSEMBLIES AVAILABLE!
Please Contact Custom Engineering and Send Sketch for Quotation.




Specifically designed for use where surface temperatures reach up to 1260°C (2300°F) and rough handling is routine, Omega's foundry probe uses large, heavy-duty tips that can penetrate surface slag to measure the true temperature of the casting. The surface to be measured must be electrically conductive. The lead wires are 16-gauge stranded wire with high temperature insulation and stainless steel overbraiding for added protection.

Will not work with analog display systems requiring 10 or 15 input impedance.

Specifications

- Calibration:** Type K, CHROMEGA™-ALOMEGA™
- Maximum Temperature:** 1260°C (2300°F)
- Contacts:** 6 mm (¼") pointed
- Lead Wire:** 1.8 m (6'), stainless steel overbraiding
- Probe Length:** 762 mm (30")
- Handle:** Rugged Aluminum, type HDX



To Order	
Model No.	Description
SP-HF-K-6.0	Spade lugs termination
SP-HF-K-6.0-OST-M	OSTW male connector termination
SP-HF-K-6.0-OGP-M	OGP male connector termination

Note: Probe tips must contact measurement surface for accurate readings.

Note: Probe Tips Must Contact Measurement Surface for Accurate Readings

Ordering Example: SP-HF-K-6.0-OST-M, high-temperature foundry probe, Type K, 6" long with an OSTW male standard size connector.

Surface Probes

with Retractable Cable and Miniature Connector Termination



Probe shown with model HH-26K Handheld Thermometer. For complete details on this meter, and hundreds of others, visit Omega.

Tried and True System Show!

HPS-HT Series

- ✓ Measures Temperature up to 1100°C (2000°F)
- ✓ K, E, or J Calibrations
- ✓ SMPW Miniature Male Connector Termination

Specifications

Maximum Short-term Temperature Rating:
Type K: 1100°C (2000°F)
Type E: 870°C (1600°F)
Type J: 760°C (1400°F)
Maximum Handle Temperature: 70°C (160°F)
Length: 300 mm (12") (custom lengths available)
Cable: 300 mm (1') Retractable, stretches to 1.5 m (5'); miniature thermocouple (SMPW) connector

Omega's high temperature surface probe features a thermocouple alloy spring-loaded sensing element to ensure consistent readings. The 300 mm (12") probe comes with an SMPW male Connector termination and a 0.3 mm (1') retractable sensor cable (stretches to 1.5 m (5')). Available in thermocouple Types J, K, or E, the HPS-HT probe can measure temperatures up to 1100°C (2000°F), Type K only.



To Order	
Model No.	Description
HPS-HT-K-12-SMPW-M	High temperature surface probe, Type K
HPS-HT-E-12-SMPW-M	High temperature surface probe, Type E
HPS-HT-J-12-SMPW-M	High temperature surface probe, Type J

Ordering Example: HPS-HT-K-12-SMPW-M, high temperature surface probe, Type K, 300 mm (12") long with an SMPW miniature connector.