

CHROME-PLATED QUICK COUPLINGS

High Temperature Brass Couplings

For durability and heat resistance

High Temperature brass couplings have a chrome-plated brass valve and Viton seals to operate effectively in temperatures up to 204°C (400°F). Made for high-heat environments or to carry fluids up to 204°C (400°F) without leaking. They offer all of the same quick connect-quick disconnect capabilities of other OMEGA® couplings.

Chrome-plated brass shutoff valves can be ordered as either the insert, the body, or both sides. For maximum flow, use couplings without valves.

All metal high temperature couplings have chrome-plated brass bodies and valves, stainless steel springs and latch, and Viton® fluoroelastomer O-Ring seals. They are an economical alternative to stainless steel quick couplings.

High Temperature Coupling Selection

All OMEGA® chrome-plated brass couplings are available in high temperature versions.

To Order Specify Model Number for FT-MC or FT-LC

HOW TO ORDER:

Simply add "HT" after the part number shown for the chrome-plated brass couplings to order with the chrome-plated brass valve and Viton® seals. Add **\$4.05** to the price of each coupling or insert, a 25 piece minimum order required.

Ordering Example:

High temperature panel mount body, 1/8" flow with shutoff valve, 1/4" ID tubing. Model Number, **FT-MCD16-04HT**.



Specifications

Working Pressure: Vacuum to 250 psi, 17.3 Bar

Operating Temperature: -40 to 204°C
-40 to 400°F

Materials:

Bodies: Chrome-Plated Brass
Valves: Chrome-Plated Brass
Valve Spring: 316 Stainless Steel
External Springs, Pin, Latch: Stainless Steel
Steel Seals: Viton

Tubing sizes:

1/8" thru 3/8" ID
5/32" OD x .10" ID thru 3/8" OD x .250" ID
4 OD x 2.5 mm ID thru 10 OD x 6.5 mm ID

Applications:

- Photo Chemicals for Film Processing
- Inks and Dyes
- Process Monitoring Instruments
- Boiling Water
- Autoclave Drains



With a combination of powerful features, the new portable and rugged OS520 Series infrared pyrometers offer solutions for many non-contact temperature measurement applications. The standard 1 mV per degree analog output allows interfacing with data acquisition equipment, including chart recorders, dataloggers and computers.

OS522 Unit with Standard Laser Sight, \$1295

CHROME-PLATED QUICK COUPLINGS

Keyed, Color-Coded Brass Quick Couplings

1/8" Flow, FT-MC Series

Keyed OMEGA® quick couplings are specifically designed for small flexible hose and plastic tubing applications which require positive mechanical connections and non-interchangeable lines. They provide economical, keyed, high reliability, fool proof connections that are compatible with lower pressure and size requirements for instrumentation applications.

Features:

- Available in Chrome-Plated Brass
- Three Keyed, Non-Interchangeable Combinations
- Keyed Combinations Have Same Color-Code
- Available in Panel Mount and Pipe Thread Bodies
- Straight Through or Single End Shutoff, 1/8" Flow Size

Warning: Standard thermoplastic and chrome-plated brass quick disconnects cannot be interchanged with keyed quick disconnect couplings because they will leak.

***Color Coding:** K1= Orange
K2= Yellow
K3= Blue

1/8" Flow

COUPLING BODIES



Pipe Thread

MALE THREAD	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE
1/8" NPT	FT-MC10-02-K*	\$12.69	FT-MCD10-02-K*	\$14.99
1/4" NPT	FT-MC10-04-K*	12.69	FT-MCD10-04-K*	14.99

Panel Mount with Hose Barb

TUBING	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE
1/8" ID	FT-MC16-02-K*	\$18.59	FT-MCD16-02-K*	\$20.26
1/4" ID	FT-MC16-04-K*	19.14	FT-MCD16-04-K*	20.83

Panel Mount Ferruleless Polytube Fitting†, PTF

TUBING	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE
1/4" OD x .170" ID	FT-MC12-04-K*	\$20.10	FT-MCD12-04-K*	\$22.26

INSERTS



For body and insert dimensions, refer to MC Series listings.

† PTF fittings are designed for semi-rigid tubing i.e. polyethylene, nylon, etc., and polyurethane tubing.

Pipe Thread

MALE THREAD	STRAIGHT THRU MODEL NUMBER	PRICE
1/8" NPT	FT-MC24-02-K*	\$7.51

Hose Barb

TUBING	STRAIGHT THRU MODEL NUMBER	PRICE
1/8" ID	FT-MC22-02-K*	\$6.83
1/4" ID	FT-MC22-04-K*	6.83

Ferruleless Polytube Fitting†, PTF

TUBING	STRAIGHT THRU MODEL NUMBER	PRICE
1/4" OD x .170" ID	FT-MC20-04-K*	\$9.56



Specifications

Working Pressure: Vacuum to 250 psi, 17.3 Bar

Operating Temperature: -40 to 82°C continuous
-40 to 180°F continuous

Materials: Bodies: Chrome-Plated Brass
Valves: Delrin Acetal
Valve Spring: 316 Stainless Steel
External Springs, Pin, Latch: Stainless Steel
Seals: Buna-N

Ordering: All couplings have consistent color coding (i.e., K1-Orange, K2-Yellow, K3-Blue). Order body and insert separately to make tubing connection. For example, MC10-02K1 and MC22-02K1.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters