

# Economical, High Performance Handheld Thermometers


## °C/°F and 0.1°/1° Resolution Models

HH-25/HH-26 Series



Standard No Points

- ✓ Certificate Included Stating NIST-Traceability (No Points)
- ✓ Up to 0.4% of Reading Accuracy
- ✓ HH-25 Models for 0.1° and 1° Display with Type K or T Thermocouples
- ✓ HH-26 Models for °C/°F Display, 1° Resolution with Type J or K Thermocouples
- ✓ Rugged, High-Impact ABS Plastic Case
- ✓ Large 3½ Digit LCD Display



**Free Thermocouple Included!**  
 These models include a free 1 m (40") insulated beaded wire thermocouple with subminiature connector and wire spool caddy (1 per channel). **Order a Spare! Model No. SC-GG-(\*)-30-36**  
 \* Insert thermocouple Type, J, K, T, E.



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

HH-26K.



### Specifications


**Input Current:** 120 nA typical  
**Repeatability:** 0.2°C (0.3°F) typical for 1 week at constant ambient temperature  
**Temperature Coefficient:** -10 to 18°C and 28 to 50°C; less than ±(0.025% of rdg + 0.1°C)/°C  
**Operating Temperature:** -10 to 50°C (14 to 122°F) and less than 80% RH up to 35°C (95°F)  
**Display:** 3½ digit LCD, 13 mm H (0.5"), polarity, overrange, oversensor and decimal indication  
**Conversion Rate:** 1.5 readings per second  
**Maximum Common Mode Voltage:** 42V peak to earth  
**Thermocouple Input:** Miniature thermocouple connector  
**Power:** 9V alkaline battery (included)  
**Battery Life, Continuous:** 300 hour, alkaline  
**Battery Indicator:** Display indicates "LO BAT" when less than 10% of the life remains  
**Dimensions:** 69 W x 31 D x 160 mm L (2.7 x 1.2 x 6.3")  
**Weight:** 210 g (7.5 oz)

### To Order

Model No.	Resolution	Range	Accuracy
HH-25KF	0.1°F 1°F	-40 to 199.9°F -120 to 1999°F	±(0.5% rdg + 1.0°F) ±(1.0% rdg + 2.0°F)
HH-25KC	0.1°C 1°C	-40 to 199.9°C -120 to 1999°C	±(0.5% rdg + 0.5°C) ±(1.0% rdg + 1.0°C)
HH-26K	1°F 1°C	-120 to 1999°F -85 to 1100°C	±(1.0% rdg + 2.0°F) ±(1.0% rdg + 1.0°C)
HH-25TF	0.1°F 1°F	-112 to 199.9°F 200 to 752°F	±(0.4% rdg + 1.1°F) ±(1.0% rdg + 2.0°F)
HH-25TC	0.1°C 1°C	-80 to 199.9°C 200 to 400°C	±(0.4% rdg + 0.6°C) ±(1.0% rdg + 1.0°C)
HH-26J	1°F 1°C	-112 to 1400°F -80 to 760°C	±(1.0% rdg + 2.0°F) ±(1.0% rdg + 1.0°C)

Comes complete with 9V battery, operator's manual, beaded wire thermocouple, and NIST certificate (no data points).  
**Ordering Example:** HH-26K, handheld thermometer, Type K, resolution 1°F, and JTSS-HH, Type K general purpose meter probe (shown below).  
 OCW-3, OMEGACARE<sup>SM</sup> extends standard 2-year warranty to a total of 5 years.

Model No.	Description
SC-800	Carrying case
CAL-3-HH	NIST-traceable calibration, with points



L-45