

Dual M12 Cables for Sensors and Transmitters

Straight or Right Angle Terminations



DM12CAB Series




- ✓ 8-Pin M12 Connectors with Gold Plated Contacts
- ✓ Straight or Right Angle Connections
- ✓ 28 Gauge Stranded Tinned Copper Conductors
- ✓ PVC Insulation: -25 to 105°C (-13 to 221°F)
Static: -40 to 105°C (-40 to 221°F)
- ✓ Shielded Conductors with 300V Insulation Rating

These extension cables can be used for connecting transmitters or sensors such as OMEGA™ ZW Series and Smart Sensors to process instrumentation. Each extension cable has 7 conductors plus a drain with an 8-pin M12 connector on each end. They are available with straight or right angle connectors in 3 standard lengths of 1, 3, or 5 m (3.3, 9.8, or 16.4').

DM12CAB-8-1-RA shown smaller than actual size.

Specification

- Insulation: PVC
- Temperature Range:
 - Dynamic: -25 to 105°C (-13 to 221°F)
 - Static: -40 to 105°C (-40 to 221°F)
- Voltage Rating: 300V
- Insulation Resistance: 10 MΩ/KM20°C
- Cable Color: Black
- Assembly: Braided shielding with drain wire
- Jacket Diameter: 4.8 mm (0.20")
- Nut: M12 Nickel plated zinc alloy



Conductors Position/Colors: 1/Black, 2/Brown, 3/Red, 4/Orange, 5/Drain, 6/Green, 7/Blue, 8/Violet

To Order	
Model No.	Description
DM12CAB-8-1	Dual M12 8-pin connectors, 1 m (3.3') cable
DM12CAB-8-1-RA	Dual M12 right angle 8-pin connectors, 1 m (3.3') cable
DM12CAB-8-3	Dual M12 8-pin connectors, 3 m (9.8') cable
DM12CAB-8-3-RA	Dual M12 right angle 8-pin connectors, 3 m (9.8') cable
DM12CAB-8-5	Dual M12 8-pin connectors, 5 m (16.4') cable
DM12CAB-8-5-RA	Dual M12 right angle 8-pin connectors, 5 m (16.4') cable

Ordering Example: DM12CAB-8-3-RA dual M12 right angle 8-pin connectors with 3 m (9.8') extension cable.