1% **DIN HIGH-PERFORMANCE METERS** ALARM/CONTROL CAPABILITIES STRAIN GAGE, PROCESS VOLTAGE AND CURRENT, TEMPERATURE





All Units Feature:

- ✓ 5-Year Warranty
- 6-Digit Display
- Min/Max Storage
- 4 Isolated Open-Collector Outputs
- NEMA 4 (IP65) Front Panel
- 12 Readings per Second
- Alarm/Control Capabilities
- Smart Filtering Detects the Difference Between a Spike or Process Change (Patent Applied for)
- Peak and Valley Detection
- Digital Tare
- Easy Front-Panel Programming
- Optional BCD Output
- Optional Analog Output
- Optional RS232/RS485 Communications
- Optional Mechanical Relays
- Thermocouple Input:
- 0.01° Resolution
- 0.2°C Accuracy
- ✓ 9 Thermocouple Types
- ✓ °C/°F/K Units
- Uses Complete NIST Calibration Tables
- RTD Input:
- 0.01° Resolution
- 0.2°C Accuracy
- 2-, 3-, or 4-Wire
- ✓ 385 and 392 Pt Curves

Voltage/Current Inputs:

- ✓ ±0.005% Rdg Accuracy
- ✓ 10 User-Selectable
- Voltage or 4 to 20/
- 0 to 20 mA Input Ranges Fully Scalable Display Up
- to 500,000 Counts
- 1.5 to 11 Vdc or 24 Vdc Sensor Excitation
- Adjustable Decimal Point

The OMEGA® DP41 Series of digital panel meter/controllers has set the world standard for accuracy and quality in industrial instrumentation. These meters can measure a broad spectrum of DC voltage and current ranges as well as inputs from 9 thermocouple types and from most RTDs, pressure transducers, load cells, strain gages, and potentiometers. Models include the DP41-W, a legal-for-trade, NTEPcertified strain meter with enhanced features, and the DP41-U, which covers all the input types. Standard features include 6-digit display; 5 front-panel pushbutton keys; 4 open-collector outputs; and alarm/control, BCD, and analog outputs. Configurable analog output ranges are 0 to 20 mA, 4 to 20 mA, 0 to 5 Vdc, and 0 to 10 Vdc.

On-board excitation allows these meters to power virtually any sensor or transmitter, and 4 setpoints give the user numerous control/alarm possibilities. Setpoint configurations include active above or below; latching or non-latching; and high deviation, low deviation, or band deviation.

With the RS232/485 serial communications option, the user can set the display parameters and read the current, max, and min values remotely. The DP40-R board option provides dual 7 A mechanical relays, activated by the selected setpoint.

The DP41 displays feature 14-segment LED characters, which greatly improves alphanumeric representations. The 7-segment LED characters found on most instruments are adequate for presenting

numbers, but not letters. Words are easier to read with the 14-segment LED characters on the DP41, which, in turn, simplifies operating and programming.



HIGH-PERFORMANCE METERS

SPECIFICATIONS

Accuracy: ±0.005% rdg Span Temperature Coefficient: ±20 ppm Step Response: 1 s to 99.9%

Warm-Up to Rated Accuracy: 50 minutes Operating Environment: 0 to 50°C (32 to 122°F); 95% RH, non-condensing

Storage Temperature:

-40 to 85°C (-40 to 185°F) **Power:** 115 or 230 Vac, 49 to 400 Hz; 10 to 32 Vdc

Power Consumption: 6 W nom., 10 W max

Normal-Mode Rejection: 60 dB Common-Mode Rejection: 120 dB Common-Mode Voltage:

1500 Vp per HV test

Resolution: 15-bit

Conversion: Dual-slope technique **Reading Rate:** 3/s or 13/s, 60 Hz; 3/s or 12/s, 50 Hz

Display: Red or green 6-digit, 14-segment, 13.7 mm (0.54") high; 4 alarm indicators **Dimensions:** 48 H x 96 W x 165 mm D (1.89 x 3.78 x 6.5")

Panel Cutout: 45 H x 92 mm W (1.772 x 3.622"); % DIN

Weight: 574 g (1.27 lb) Setpoint Outputs: 4 isolated open

collector; rated 150 mA at 1V sink, 30V open

BCD Output: Isolated, tri-state, TTL/CMOS compatible; external 5V supply required for isolated; internal 5V supply for non-isolated

Dual Relays: Form "C", 7 A @ 30 Vdc or 230 Vac

4-Relay Option: Dual 7 A relays and dual 1 A relays

Analog Output: 0 to 5V/1 to 5V/ 0 to 10V/0 to 20 mA/4 to 20 mA, user selectable; 354 Vp isolation; 15-bit resolution; 0.1% accuracy; 50 ms step response

RS232 Communications: 300/600/1200/2400/4800/9600/ 19.2K baud; RJ11 4-wire connection; programmable to transmit current display, alarm status, min/max, actual measured input value and status

RS485 Communications: 300/600/1200/2400/4800/9600/ 19.2K baud; RJ12 6-wire connection; addressable from 0 to 199

Voltage Input Ranges: 0 to 100 mV, 0 to 1V, 0 to 5V, 1 to 5V, 0 to 10V, 0 to 100V, ±50 mV, ±500 mV, ±5V, ±50V Current Input Ranges: 0 to 20 mA,

4 to 20 mA Input Configuration: Single-ended

Polarity: Unipolar/bipolar, programmable **Span Adjustment:** 0.00001 to 500,000, programmable

Offset Adjustment: 0 to 999,999 or 0 to -99,999, programmable Thermocouple Input Types: J, K, T, E, R, S, B, N, J DIN RTD Input: Any 6 Ω to 6 k Ω NIST or DIN platinum and any linear RTD RTD Connection: 2-, 3- or 4-wire Sensor Break Protection: Up-scale or down-scale, programmable Sensor Excitation: 10 V at 30 mA; 24V at 25 mA

The DP41 thermocouple meter offers very high accuracy ensured by an advanced (patent applied for) thermocouple linearizing system. Accuracy for most thermocouple types is 0.2° C (3.6° F). The meter is front-panel programmable for any of 9 thermocouple types. The DP41 RTD input meter is programmable for any 6 to 6000 Ω DIN or NIST platinum RTD. It provides a precision ultra-low constant current excitation to minimize self-heating errors and maximize stability.

	INPUT TYPE	RANGE, °C	RANGE, °F	ACCURACY
J	Iron-constantan	-210 to 760	-346 to 1400	0.2°C/0.3°F
K	CHROMEGA®-ALOMEGA®	-270 to 1372	-454 to 2500	0.2°C/0.3°F
Т	Copper-constantan	-270 to 400	-454 to 752	0.2°C/0.3°F
Е	CHROMEGA®-constantan	-270 to 1000	-454 to 1832	0.2°C/0.3°F
R/S	Pt/Rh	-50 to 1768	-58 to 3214	0.2°C/0.3F
В	Pt/30% Rh-Pt/6° Rh	100 to 1820	212 to 3300	0.3°C/0.5F
N	OMEGALLOY®	-270 to 1300	-454 to 2372	0.2°C/0.3F
J DIN	Iron-constantan	-200 to 900	-328 to 1652	0.6°C/1.0F
RTD	All curves	-200 to 850	-328 to 1562	0.2°C/0.3F

	INPUT TYPE	RANGE, °C	RANGE, °F	RANGE, K	ACCURACY
RTD 1	10 Ω copper	-200 to 200	-328 to 392	73.2 to 473.2	1.0°C/2.0°F/1.0 K
RTD 2	100 Ω Pt 0.00385	200 to 900	-328 to 1652	73.2 to 1173.2	0.2°C/0.3°F/0.2 K
RTD 3	100 Ω Pt 0.00392	-200 to 850	-328 to 1562	73.2 to 1123.2	0.2°C/0.3°F/0.2 K



D-30



DP41Z-E split meter with remote display, panel mount or surface mount with bracket shown smaller than actual size.

METERS



ANALOG OUTPUT/COMPUTER COMMUNICATIONS

MODEL NO.	DESCRIPTION
DP40-A3	Analog output
DP40-S24	Isolated RS232/485 communications

DP40-S24 option comes with communications cable with phone plug termination. For proper termination to a computer, 9-pin and 25-pin connectors are offered below.

CONTROL/BCD OUTPUTS

MODEL NO.	DESCRIPTION
DP40-B	Isolated BCD output board*
DP40-R	Dual 7 A mechanical relays*
DP40-R4	Dual 7 A and Dual 1 A relays*

*Note: Order DP40-B, DP40-R or DP40-R4; only 1 option can be used per unit. DC power option not available on models with DP40-R or DP40-R4.

Ordering Example: DP41-TC-DC-S2A and DP40-9SC2, DP41 unit for thermocouple inputs, with 10 to 32 Vdc power, RS232 communications, analog output and 9-pin serial connector.

To Order		
MODEL NO.	DESCRIPTION	
DP41-E	Process voltage/current indicator	
DP41-S	Strain gage indicator	
DP41-W	Weight NTEP strain indicator	
DP41-TC	Thermocouple indicator	
DP41-RTD	RTD indicator	
DP41-U	Universal input indicator	
DP41Z-E	Split-display voltage/current indicator	
DP41Z-S	Split-display strain gage indicator	
DP41Z-W	Split-display weight NTEP strain indicator	
DP41Z-TC	Split-display thermocouple indicator	
DP41Z-RTD	Split-display RTD indicator	
DP41Z-U	Split-display universal input indicator	
POWER AND DISPLAY OPTIONS		
SUFFIX	DESCRIPTION	
-230	230 Vac power	
-DC	10 to 32 Vdc isolated power	
-GN	Green LED display	
ACCESSORIES	FOR COMPUTER COMMUNICATIONS	
MODEL NO.	DESCRIPTION	
DP40-9SC2	9-pin serial connector for RS232	
DP40-9SC4	9-pin serial connector for RS485	
DP40-25SC2	25-pin serial connector for RS232	
DP40-25SC4	25-pin serial connector for RS485	
ACCESSORIES FOR DP41 METERS		
MODEL NO.	DESCRIPTION	
0004		

MODEL NO.	DESCRIPTION
SPC4	NEMA 4 (IP65) heavy-duty splashproof lens, screw clamp
SPC18	NEMA 4 (IP65) splashproof lens, spring clip
DP41-TBS	Economical bench stand
DPP-5	½ DIN panel punch

1% DIN HIGH-PERFORMANCE PROCESS INDICATORS DP41 SERIES

