



BENEFITS/FEATURES

- Reduced installation time through zero and span controls that provides quick and easy calibration
- · Fast and easy setup and calibration with push-button zero and span controls
- Immediate corrective action can be taken by local alerts via the easy-to-read LCD display
- Reduces upgrade installation costs and simplifies field upgrade from a Magnehelic[®] gage, as both use the same diameter cutout

APPLICATIONS


- Differential pressure across filters
- Fan control
- Static pressures in ducts or buildings
- Room pressurization monitoring


DESCRIPTION

The **Series DM DigiMag® Differential Pressure Transmitter** senses the pressure of air and compatible gases and sends a standard 4-20 mA output signal. The DM housing is specifically designed to mount in the same diameter cutout as a standard Magnehelic® gage. A wide range of models are available factory calibrated to specific ranges. The polycarbonate molded housing features integral pressure connections, which reduces installation time. Digital push-button zero and span simplify calibration over typical turn-potentiometers. A single push-button allows field selection of 4 to 6 engineering units, depending on the range.

SPECIFICATIONS


LOI IOATIONO	
Service	Air and non-combustible, compatible gases.
Wetted Materials	Consult factory.
Housing Material	Polycarbonate.
Accuracy	±1% FSO for all ranges except 0.25 in w.c. @ ±2% FSO, and ranges at or below ±0.1 in w.c. @ ±4% FSO.
Stability	< ±1%/year FSO.
Pressure Limits	Ranges > 1 in w.c.: 6 psi max operation, 6 psi burst; Ranges ≤ 1 in w.c.: 3.6 psi max operation, 6 psi burst.
Temperature Limits	-4 to 158°F (-20 to 70°C).
Thermal Effect	0.036% FS/°C (0.02% FS/°F).
Power Requirements	10-35 VDC (2-wire).
Output Signal	4-20 mA (2-wire).
Zero and Span Adjustments	Push-button.
Loop Resistance	0 to 1250 Ω max.
Current Consumption	21 mA max.
Electrical Connections	Screw-type terminals.
Process Connections	Male ports on side for 1/8", 3/16", 1/4", 5 mm, 6 mm ID flexible tubing.
Enclosure Rating	NEMA 4X (IP66).
Mounting Orientation	Not sensitive to position.
Size	5" OD (127 mm) x 1.9" (48 mm) deep.
Weight	7.04 oz (200 g).
Compliance	CE.
Compliance	





HOW TO ORDER

Use the **bold** characters from the chart below to construct a product code.



ORDER ONLINE TODAY! dwyer-inst.com



DWYER INSTRUMENTS, LLC

©Copyright 2022 Dwyer Instruments, LLC Printed in U.S.A. 1/23

DS-DM Rev. 1

Important Notice: Dwyer Instruments, LLC reserves the right to make changes to or discontinue any product or service identified in this publication without notice. Dwyer advises its customers to obtain the latest version of the relevant information to verify, before placing any orders, that the information being relied upon is current.