

HIGH PERFORMANCE FAN HEATER FOR PANEL, DIN RAIL OR FOOT-MOUNT

CR030/CR130 Series



- ✓ Compact DIN Rail, Panel Mount or Foot-Mounted Fan Heater
- ✓ Maintains Minimum Operating Temperatures in Enclosures
- ✓ Helps to Prevent Failure of Electronic Components Caused by Condensation and Corrosion
- ✓ Built-In Overheat Protection
- ✓ Integrated Adjustable Thermostat
- ✓ Double Insulated Plastic Housing



CR030599 shown smaller than actual size.



CR130599 shown smaller than actual size.

Specifications

Heating Element: High performance cartridge heater

Heat Sink: Extruded aluminum profile

Overheat Protection: Built-in temperature limiter

Axial Fan (Ball Bearing): Service life 50,000h @ 25°C (77°F)

Air Flow, Free Blowing: 160 m³/h (94 cfm)

Connection: 2-pole terminal AWG 16 max (1.5 mm²) with strain relief, clamping torque 0.8 Nm max

Mounting:

CR030: M5 screws (not included)

CR130: Clip for 35 mm DIN rail, EN 60 715 or M6 screws (not included)

Position: Preferably horizontal

Wiring Compartment: Plastic, UL94V-0, black

Dimensions:

CR030: 168 x 145 x 99 mm (6.6 x 5.7 x 3.9")

CR130: 182 x 160 x 99 mm (7.2 x 6.3 x 3.9")



Weight: 1.4 kg (3.1 lb)

Operating Temperature: 0 to 60°C (32 to 140°F)

Storage Temperature: -45 to 70°C (-49 to 158°F)

Protection Class: II (double isolated)

Protection Type: NEMA 2 (IP20)



To Order

Model No.	Description
CR030599	Fan heaters, 950 W, 120 Vac with adjustable thermostat 0 to 60°C (32 to 140°F), foot mount
CR130599	Fan heaters, 950 W, 120 Vac with adjustable thermostat 0 to 60°C (32 to 140°F), DIN or panel mount
XBANS3575P	DIN rail 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6') slotted

Comes complete with operator's manual.

Ordering Examples: CR030599, foot-mounted fan heater.

CR130599, DIN or panel mounted fan heater.