

# INSERTION ELECTROMAGNETIC FLOW TRANSMITTER

Field Configurable, High Accuracy, BACnet or Modbus® Protocol

CALIBRATION SERVICES AVAILABLE





Shown with  
A-IEF-VLV-BR\*\*  
accessory valve kit



-LCD option shown



A-IEF-KIT



The **Series IEF Insertion Electromagnetic Flow Transmitter** is an adjustable insertion flowmeter featuring electromagnetic technology that accurately and reliably measures fluid velocity in addition to providing several continuous signal outputs. This series is specifically designed to offer superior performance paired with simple installation and use. One unit is adjustable to fit pipe sizes from 4 to 36" (102 to 914 mm), and offers several output options including selectable BACnet MS/TP or Modbus® RTU communications protocol over 2-wire RS-485 in addition to the standard analog, frequency and alarm outputs.

## BENEFITS/FEATURES

- Meet application requirements with field configurable setup displays (-LCD integral option or remote accessory A-IEF-DSP), which accommodate a variety of application configurations with one model through multiple display configurations i.e. pipe size, pipe material, liquid type, analog output, pulse/frequency output, alarm outputs, communication outputs, damping, and calibration factor
- Maintain system efficiency with high performance accuracy that is maintained through changes in temperature, density or viscosity
- Quick and easy ordering and set up with Setup Wizard and installation tool that are simple to use and allow for precise installation
- Save time with accessory setup kit A-IEF-KIT that ensures exact installation application depth with included thickness gage and measuring tape
- Reduced costs, long product life, and minimal maintenance requirements with no moving parts to wear or break and electrodes that discourage fouling
- Minimize installation costs with isolation valve accessory options to allow for installation in operational systems via hot-tap kit or easy removal without system downtime
- Required documents included with NIST traceable pass/fail verification certificate included standard for Carbon Steel Schedule 40 pipes sized 4" (102 mm), 6" (150 mm), 8" (200 mm)

## APPLICATIONS

- Boiler feed water
- Chilled water
- Open and closed loop condenser water
- Irrigation system
- Municipal water distribution
- Process and coolant flow
- Ground water remediation
- Chemical processing
- Pump protection
- Wastewater
- Mining

## SPECIFICATIONS

**Service:** Compatible clean or dirty non coating, conductive liquids.

**Range:** 0 to 20 ft/s (0 to 6 m/s).\*

**Wetted Materials:** Body shaft/fitting: 316 SS; Electrodes: 316 SS; Electrode cap: Polymer/Polystyrene; O-ring: Silicon.

**Accuracy:** High accuracy units: ±0.5% of reading at calibrated velocity; ±1% of reading from 2 to 20 ft/s (0.6 to 6 m/s); ±0.02 ft/s (±0.006 m/s) at < 2 ft/s (0.6 m/s); Standard accuracy units: ±1% FS.

**Temperature Limits:** Ambient: -20 to 160°F (-29 to 71°C); Process: 15 to 250°F (-9 to 121°C); Storage: -40 to 185°F (-40 to 85°C).

**Process Connection:** 1" NPT or BSPT with accessory full port ball valve options.

**Pressure Limits:** 400 psi (27.6 bar) @ 100° F (37.8°C).

**Pressure Drop:** < 0.1 psi at 12 ft/s in 4" (101.6 mm) and larger pipe.

### Outputs:

(1) Analog: 4-20 mA, 0-5 V, 0-10 V or 2-10 V (display selectable);

(1) Pulse/Frequency: 0-15 V peak pulse, 0 to 500 Hz or scalable pulse output (display selectable);

(2) Alarm: (1) Empty pipe detection or minimum/maximum velocity, (display selectable); (1) Reverse flow output indication.

**Power Requirements:** 12-42.4 VDC, .25 A @ 24 VDC, 12-36 VAC.

**Electrical Connection:** Removable terminal blocks, model selectable 1/2" female NPT conduit connection, PG 16 gland or PG 16 gland with (2) 10 ft (3 m) 9 conductor 22 AWG plenum rated cables, accessory cable lengths up to 200 ft (61 m) optional.

**Display (-LCD option):** 2" (5.08 cm) x 2" (5.08 cm) graphic LCD with backlight.

**Conductivity:** >20 microsiemens.

**Enclosure Material:** Powder coated die cast aluminum.

**Enclosure Ratings:** NEMA 6P (IP68) (Non display models); NEMA 4X (IP66) (-LCD option).

**Compliance:** BTL, CE, NSF/ANSI 61 and 372.

**COMMUNICATIONS (-COM OPTION)**

**Type:** BACnet MS/TP or Modbus® RTU communication protocol (default disabled, display selectable).

**Supported Baud Rates:** 9600, 19200, 38400, 57600, 76800, or 115200 bps (display selectable).

**Device Load:** 1/8 unit load.

**ADDITIONAL SPECIFICATIONS**

**Applicable Pipe Material:** Most popular plastic and metal pipes; i.e. Carbon steel, SS, copper, UPVC/PVDF, galvanized steel, mild steel, and brass.†

**Applicable Pipe Size:** 4-36" (101 to 914 mm), model dependent. See model chart.

**Diameter Length Requirements:** >10 upstream; >5 downstream.

**Glycol:** 0 to 100% display selectable.

\*For max flowrates >10 ft/s (3 m/s) order option -CC.

†Brass fittings and pipe are not to be used with NSF Certified models.

MODEL CHART						
Example	IEF	-H	N	-CND	-LCD	IEF-HN-CND-LCD
<b>Series</b>	IEF					Insertion electromagnetic flow transmitter
<b>Accuracy</b>		L G S F I E T H				Standard accuracy 4 to 10" (200 to 250 mm) pipe; 1% FS Standard accuracy > 10 to 36" (250 to 900 mm) pipe; 1% FS Standard accuracy 4 to 36" (100 to 900 mm) pipe; 1% FS High accuracy 4" (100 mm) pipe; 1% of reading High accuracy 6" (150 mm) pipe; 1% of reading High accuracy 8" (200 mm) pipe; 1% of reading High accuracy 10" (250 mm) pipe; 1% of reading High accuracy 4 to 10" (100 to 250 mm) pipe; 1% of reading
<b>Process Connection</b>			N B			1" male NPT 1" male BSPT
<b>Housing</b>				CND		1/2" female NPT conduit connection without cable
<b>Electrical Connection</b>				PG		PG gland without cable
<b>Options</b>				10		PG gland with 10' (3 m) cable
				CC		Custom configured for specific installation
				COM		BACnet or Modbus® communication protocol (display selectable)
				FC		Factory calibration certificate for 0.5% of reading at single point
				LCD		Integral LCD display
				NIST		Six point NIST traceable calibration certificate
				NW		NSF certified

**Note:** For CC option, must provide completed configuration paperwork.

**Note:** For maximum performance select -LCD option or setup display accessory.

ACCESSORIES	
Model	Description
A-IEF-CBL-50	Plenum rated cable 50 ft (15.2 m)
A-IEF-DSP	Setup display
A-IEF-KIT	Setup kit (includes setup display, thickness gage and measuring tape), and universal power adaptor
A-IEF-PA	AC wall adaptor
A-IEF-VLV-BR	1-1/4" full port isolation valve brass kit**
A-IEF-VLV-SS	1-1/4" full port isolation valve 316 SS kit

\*\*Brass fittings and pipe are not to be used with NSF Certified models. Brass valves are non-RoHS compliant.

Modbus® is a registered trademark of Schneider Electric USA, Inc.

A-IEF Remote Display now available: See page 293