

## 4-Channel Current Data Logger Part of the NOMAD® Family

### OM-CP-QUADPROCESS



- ✓ 16-Bit Resolution
- ✓ Programmable Engineering Units, Scale Factor, and Offset Value
- ✓ Memory Wraparound
- ✓ Miniature Size
- ✓ User Calibration Through Software
- ✓ Real-Time Operation

The OM-CP-QUADPROCESS is a 4-channel, battery-powered, standalone current data logger. The OM-CP-QUADPROCESS lets the user store predefined units in the device, as well as scale factors and offset values. This allows easy, automatic linearization and scaling of any process meter that provides an analog output to process units. This portable, easy-to-use device will read and record up to 32,767 current measurements per channel.

The OM-CP-QUADPROCESS represents a major leap in both size and performance. Its small size allows it to fit almost anywhere. Its real-time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security, even if the battery becomes discharged.

Data retrieval is simple. Plug the logger into an available COM port and our easy-to-use software does the rest.

The software converts a PC into a real-time strip chart recorder. Data can be printed in graphical or tabular format. It can also be exported to a text or Microsoft Excel file.



OM-CP-QUADPROCESS-100MA shown actual size.

### Specifications

#### Input Channels:

4 non-isolated inputs

**Memory:** 32,767 readings/channel

**Input Connection:** Screw terminal

**Analog Conversion Time:** 133 ms

**Frequency Rejection:** 60 Hz

**ADC Resolution:** 16 bits

**Current Calibration:** Digital calibration available in software

**Calibration Date:** Automatically recorded within device to alert user when calibration is required

**Recording Interval:** 1 second to 12 hours selectable with software

**Start Time:** Start time and date are programmable through software

**Memory Wraparound:** Selectable in software

**Real-Time Recording:** Device can be used with PC to monitor and record data in real time

**Time Accuracy:** ±1 minute per month at 20°C

**Power:** 9V alkaline battery (included); 120 Vac power optional

**Battery Life:** 1 year typical

**Time Accuracy:** ±1 minute per month at 20°C

**Data Format:** Date and time stamped in µA, mA, A and other engineering units programmable through software

**Weight:** 370 g (13 oz)


**Computer Interface:** PC serial, RS-232C COM or USB (interface cable required); 2400 baud

**Software:** XP SP3/Vista 7 and 8 (32-bit and 64-bit)

**Operating Environment:** -40 to 60°C (-40 to 140°F) 0 to 95% RH non-condensing

**Dimensions:** 26 D x 112 L x 89 mm W (1.0 x 4.4 x 3.5")

**Material:** Black anodized aluminum



**OM-CP-IFC200**  
Windows software displays data in graphical or tabular format



**OM-CP-QUADPROCESS-100MA** shown smaller than actual size.

INPUT RANGES	OM-CP-QUADPROCESS-1MA	OM-CP-QUADPROCESS-25MA	OM-CP-QUADPROCESS-100MA
Nominal Range	±1 mA	±25 mA	±100 mA
Measurement Range	±1.5 mA	±30 mA	±120 mA
Resolution	0.05 µA	1 µA	5 µA
Calibrated Accuracy	±0.5% FSR	±0.1% FSR	±0.1% FSR
Input Impedance	50 Ω	10 Ω	2 Ω
Overload Protection	±20 mA	±100 mA	±125 mA

Specified accuracy range: nominal range @ 25°C.

To Order	
Model No.	Description
OM-CP-QUADPROCESS-1MA	4-channel current data logger, ±1 mA range
OM-CP-QUADPROCESS-1MA-CERT	4-channel current data logger, ±1 mA range with NIST calibration certificate
OM-CP-QUADPROCESS-25MA	4-channel current data logger, ±25 mA range
OM-CP-QUADPROCESS-25MA-CERT	4-channel current data logger, ±25 mA range with NIST calibration certificate
OM-CP-QUADPROCESS-100MA	4-channel current data logger, ±100 mA range
OM-CP-QUADPROCESS-100MA-CERT	4-channel current data logger, ±100 mA range with NIST calibration certificate
OM-CP-IFC200	Windows software and 1.8 m (6') USB interface cable
OM-CP-BAT103	Replacement 9V alkaline battery
OM-CP-CONNECTOR-3	Replacement 3 position terminal block connector

Operator's manual and USB interface cable are included with the OM-CP-IFC200 Windows software (required to operate the data logger and sold separately).

To order data loggers with optional 120 Vac power, add suffix "-AC" to model number for additional cost.

Ordering Example: OM-CP-QUADPROCESS-25MA-CERT 4-channel current data logger with NIST calibration certificate and OM-CP-IFC200 Windows software with USB interface cable.