
INSERTION MAGNETIC FLOWMETER

FMG900 Series



- Durable
- ✓ Adjustable Depth
- ✓ Brass or Stainless Steel
- ✓ Immersibility Available
- Reverse Flow Output Available
- ✓ 3 to 48" Diameter Pipes

The complete lack of moving parts of this insertion flow sensor is the source of its reliability. There is no rotor to stop turning in dirty water and there are no bearings to wear out. Brass and stainless steel models withstand a variety of temperature, pressure, and chemical conditions. Reverse flow output and immersibility are optional. A rapidly reversing magnetic field is produced in the lower housing. As the fluid moves through this field, a voltage is generated that is measured and translated into a frequency signal proportional to flow rate. This square wave signal can be sent directly to a PLC, control or converted to 4 to 20 mA with the FTB700-T shown below (optional). A modular system of electronics can be attached directly to the flow sensor or remotely mounted. The FMG900 series can provide full indication of rate and total with the (optional) FTB700-D or just a 4 to 20 mA output with the (optional) FTB700-T blind transmitter. The adaptor fitting of the standard unit is a male NPT, and can be directly threaded into ordinary saddles or threaded weld fittings. The hot tap versions include an isolation valve, allowing hot-tap installation, or installation and removal under pressure. Hot tap units include the appropriate installation valve.



Standard Units: 1½ NPT male, hot tap models, 2 NPT male

Ambient Temperature: -17 to 72°C

(0 to 160°F)

Fluid Temperature: 0 to 93°C

(32 to 200°F)

Maximum Pressure: 13.8 bar (200 psi)

Minimum Conductivity: 20 microSiemens/cm

Shaft and Fitting: 316 SS or brass

(depending on model) **Electrodes:** Hastelloy®

Electrode Cap: PVDF

Housing: Cast powder-coated

aluminum

Valve: Bronze or SS (depending on model)
O-Ring: EPDM

Accuracy: ±1% of full scale

Output: Square wave pulse, opto
isolated, 550 Hz @ 20 ft/second 6 mA
maximum, 30 Vdc forward flow standard

(reverse flow optional)

Empty Pipe: Defaults to zero flow

RATE AND TOTAL DISPLAY

FOR THE FMG900 SERIES

FTB700-D Series


- ✓ Simple Setup
- Loop Powered
- Remote or Flow Sensor Mounted Indicator
- Rugged Metallic Housing
- ✓ Non-volatile Memory

The FTB700-D Series flow displays are microcontroller-based indicator/ transmitters that display flow rate and total and provide output signals. The FTB700-D is powered by external DC voltage and has both pulse and 4 to 20 mA analog outputs. When the FTB700-D is being used in the 4 to 20 mA mode, it is a "two-wire" or "loop-powered" device, meaning that the 4 to 20 mA output signal doubles as its power supply.

The addition of a dual-relay output board (-R2) allows for certain applications requiring contact output isolation (e.g., certain metering pumps and water treatment controls). Dual solid state relays provide exactly the same pulse output as the standard unit, and each can signal one external device.

The FTB700-D can be mounted on the meter (-M) or remotely wall mounted with the brackets provided (FTB700D-W). Housings for the "-W" and "-M" models are rugged cast aluminum, potted and gasketed for maximum environmental protection. A membrane keypad allows settings to be changed without removing the cover. (Password protection, a standard feature, can be used to prevent settings from being changed.)





SPECIFICATIONS

Power: 12 to 30 Vdc, (4 to 20 mA) Display Rate: 6-digit autorange,

1/2" character height

Total: 8-digit, 5/16" character height Outputs Current Sinking Pulse: Scaled pulse output (0.1 second duration 6.1 Hz maximum) (or high alarm output or low alarm output). Sensor pass-through pulse output (unscaled)

Analog: 4 to 20 mA

Pulse Output Range:

0.1 - 9999999.9 units/pulse

Input: 5V pulse or contact closure **Input Range:** 1.0 - 1,500 pulses/second

K-Factor Range: 0.001 - 99999.999

Flow Alarm Output Range:


0.01 - 999999.99


Operating Temperature: -30 to 65°C

(-22 to 148°F)

Environmental: NEMA 4X, (IP66)


Regulatory: CE





Dimensions: mm (inch)

Flow Range LPM (GPM)		
Pipe Size	Min Flow	Max Flow
3	23 (6)	1666 (440)
4	42 (11)	2964 (783)
6	95 (25)	6670 (1762)
8	167 (44)	11,860 (3133)
10	261 (69)	18,530 (4895)
12	375 (99)	26,687 (7050)
14	507 (134)	36,325 (9596)
16	662 (175)	47,443 (12,533)
18	840 (222)	60,050 (15,863)
20	1037 (274)	74,134 (19,584)
24	1495 (395)	160,749 (28,200)
30	2336 (617)	166,800 (44,064)
36	3361 (888)	240,192 (63,452)



To Order		
Model No.	Description	
FMG901	Brass insertion style magmeter, 76 to 254 mm (3 to 10") pipe	
FMG902	Brass insertion style magmeter, 254 to 1219 mm (10 to 48") pipe	
FMG903	SS insertion style magmeter, 76 to 254 mm (3 to 10") pipe	
FMG904	SS insertion style magmeter, 254 to 1219 mm (10 to 48") pipe	
FMG905	Brass insertion style magmeter, hot tap, 76 to 254 mm (3 to 10") pipe	
FMG906	Brass insertion style magmeter, hot tap, 254 to 1219 mm (10 to 48") pipe	
FMG907	SS insertion style magmeter, hot tap, 76 to 254 mm (3 to 10") pipe	
FMG908	SS insertion style magmeter, hot tap, 254 to 1219 mm (10 to 48") pipe	

Accessories

Model No.	Description	
FTB700-T	Blind 4 to 20 mA transmitter	
FTB700D-WMB	Wall mount bracket for FTB700-D	
FTB700-D	Remote rate and total display with 4 to 20 mA output	
PSU-93	24 Vdc power supply, 200 mA	
TX4-100	4 conductor hook-up wire, 30 m (100')	

Comes complete with operator's manual.

For reverse flow option add a "-RF" to the model number for additional cost.

Ordering Examples: FMG901, brass insertion style magmeter, PSU-93, power supply and TX4-100, multi conductor wire.

FMG903, 316SS insertion style magmeter, PSU-93, power supply and TX4-100, multi conductor wire.