RTD Utility Handle Probe

The PR-16 series, Omega's RTD handle probe, features an easygrip molded handle. It has a 3-conductor retractable cable that is 1 foot long, expandable to 5 feet. This is available in standard lengths of 12, 18 and 24". The 12" length probe can be stored in toolboxes or other locations for easy access. Standard termination is stripped-end lead wires. This comes with either PT100 Ω or PT1000 Ω element.

Features

Specifications

- Class A accuracy, conforming to IEC 60751
- Low temperature range: -50 to 250°C (-58 to 482°F)
- High temperature range: -50 to 450°C (-58 to 842°F)
- Extreme temperature range: -200 to 600°C (-328 to 1112°F)
- Standard probe lengths of 12, 18 and 24 inches
- Resistance value: PT100 Ω or PT1000 Ω
- Stripped-end standard; other terminations offered
- Choice of PT100 and PT1000 Ω element

	/	
	Z	

Model	PR-16L (Low)	PR-16H (High)	PR-16E (Extreme)			
Process Temperature	-58 to 250°C	-50 to 450°C	-200 to 600°C			
Range	(-58 to 482°F)	(-58 to 842°F)	(-328 to 1112°F)			
Accuracy	Class A	Class A from -50 to 300°C	Class A from -100 to 450°C			
		(-58 to 572°F); or else Class B	(-148 to 842°F); or else Class B			
Nominal Resistance and	100 Ω and 1000 Ω at 0°C standard;					
Curve	TCR = $0.00385 \Omega/\Omega/^{\circ}C$ standard					
Wire Length	1 foot (expandable to 5 feet)					
Wire Material	TPE (coiled)	TPE (coiled)	TPE (coiled)			
Lead Wire Termination	Stripped ends. Other terminations may be configured.					
Dimensions	Diameters: 1/8, 3/16 and 1/4 inch.					
	Standard probe length of 2, 3, 4, 6, 12, 18 and 24 inch.					
	Other lengths may be built using our configurator.					
Ingress Protection	IP67	None	IP67			
Response time T90 (s)	1/8" 2.4 sec	1/8" 2.8 sec	1/8" 9 sec			
	3/16" 2.8 sec	3/16" 4.11 sec	3/16" 9.8 sec			
	1/4" 3.25 sec	1/4" 5.41 sec	1/4" 10.6 sec			
Vibration	IEC 60068-2-6; 5 to 2000 Hz sweep rate, one active per minute;					
	number of sweep cycles 10 and acceleration 5g (15 probes tested together)					
	Duration: 1 day					
Shock	IEC 60068-2-27; 50g/11ms (15 probes tested together) Duration: 1 day					