

# SERIES DM-1000 | DIGIMAG® DIGITAL DIFFERENTIAL PRESSURE AND FLOW GAGE



# **BENEFITS/FEATURES**

- Field programmed reduces installation time
- · User selectable parameters for pressure, air velocity or flow permits same device for multiple applications
- Specialized filter set point for alerts when maintenance is due
- · Security levels permit matches the correct access to right skill
- Power versatility works with 9-24 VDC or 9 V battery allows deployment in a variety of spaces wired or not

#### **APPLICATIONS**

- Differential pressure across filters
- Fan control
- · Static pressures in ducts or buildings
- · Room pressurization monitoring

#### **DESCRIPTION**


The Series DM-1000 DigiMag® Digital Differential Pressure and Flow Gage monitors the pressure of air and compatible gases just as its famous analog predecessor the Magnehelic® differential pressure gage. All models are factory calibrated to specific ranges. The 4-digit LCD can display readings in common English and metric units so conversions are not necessary. The simplified four button operation reduces set up time and simplifies calibration with its digital push-button zero and span.


#### **SPECIFICATIONS**


Service	Service: Air and non-combustible, compatible gases.
Wetted Materials	Wetted Materials: Consult factory.
Accuracy	±1% FS including linearity, hysteresis and repeatability; ±2% FS for ranges 1 in w.c. and below.
Temperature Limits	0 to 140°F (-18 to 60°C).
<b>Compensated Temperature Limits</b>	32 to 122°F (0 to 50°C).
Long Term Stability	±1% FS per year.
Thermal Effect	±0.05% FS/°F typ.; ±0.10% FS/°F for ranges 1 in w.c. and below.
Display	4-digit LCD (digits: 0.60H x 0.33W).
Display Update	Selectable for 1 s to 10 minutes or update only from button push.
Pressure Limits	Normal and bi-directional ranges 5 in w.c. and lower = 2 psi (13.7 kPa); Normal and bi-directional ranges 10 ir
	w.c. and higher = 11 psi (75 KPa).
Selectable Engineering Units	in w.c., psi, kPa, Pa, mm w.c., mBar, in Hg, mm Hg, FS (0-100%).
Power Requirements	9 V alkaline battery, included, user replaceable or external power supply 9-24 VDC.
Battery Service Life	Battery life depending on the display update setting: 150 hours (typical) if display update = 1 s; 9 month (typical) if display update = 10 minutes; 1.5 years (typical) if display update is disabled. Battery may last up to four times longer when using lithium-based battery ULTRALIFE U9VL-J.
Current Consumption	5 mA max.
Electrical Connections	Removable terminal block for 16 to 26 AWG.
Electrical Entry	Cable gland for 0.114 to 0.250" (2.9 to 6.4 mm) diameter cable.
Process Connections	1/8" (3 mm) ID tubing.
Enclosure Rating	NEMA 4X (IP66).
Size	5" (127 mm) OD front face.
Weight	1.18 lb (535 g).
Compliance	CE.

# **DIMENSIONS**

# **WIRING DIAGRAM**








# **HOW TO ORDER**

Use the **bold** characters from the chart below to construct a product code.



#### **ACCESSORIES**

Model	Description
A-286	4-1/2" gage panel mounting flange
A-300	Flat flush mounting bracket
A-480	Plastic static pressure tip
A-489	4" straight static pressure tip with flange

# **ORDER ONLINE TODAY!**

dwyer-inst.com/Product/SeriesDM-1000



**DWYER INSTRUMENTS, LLC** 

©Copyright 2022 Dwyer Instruments, LLC Printed in U.S.A. 1/22

DS-DM-1000 Rev. 2