

ECONOMICAL DIGITAL HANDHELD MANOMETER

0 to 20 inH₂O RANGE

HHP680



- ✓ Max and Reading Hold
- ✓ Portable and Easy-to-Use
- ✓ Auto-Zero Power
- ✓ Switchable High Resolution: 0.01/0.1" Water Column
- ✓ Comes with Tubing [60 cm (24")] and 1/8" NPT Fitting
- ✓ 4 "AAA" Alkaline Batteries Included
- ✓ Soft Carrying Case

The HHP680 is a low-cost, versatile handheld manometer. It comes with tubing, fitting, soft carrying case, and batteries. Typical applications include commercial and automotive HVAC.

SPECIFICATIONS

Display: 3½ digit LCD with a maximum reading of 1999

Range: 0 to 20 inH₂O

Resolution: 0.01/0.1"

Low-Battery Indicator:

The "⚡" displays

Storage Temperature:

-20 to 60°C (-4 to 140°F)

Operating Temperature:

0 to 40°C (32 to 104°F)

Operating Relative Humidity:

15 to 90% RH, non-condensing

Accuracy: ±2% at 23°C (73°F)

[±5°C (9°F), <75% RH]

Dimensions: 190 H x 44 W x 40 mm D

(7.5 x 1.7 x 1.6")

Weight: Approx. 150 g (5.3 oz) with batteries

Batteries: 4 "AAA" (included)

Sensor: Solid state

Battery Life: 150 hrs, typical usage; no measurable current when in off position

Compatible Media: Dry, non-corrosive gases



HHP680, shown actual size.

60 cm (24") of tubing and 1/8" NPT adaptor included.

A

PRESSURE INSTRUMENTS

To Order Visit omega.com/hhp680 for Pricing and Details

MODEL NO.	DESCRIPTION
HHP680	Portable manometer with 0 to 20 inH ₂ O range

Comes complete with 60 cm (24") of tubing, fitting, 4 "AAA" alkaline batteries, soft carrying case and operator's manual.

Ordering Example: HHP680, handheld manometer.