Room Series | Thermistor Wall Mount Enclosures, Thermistor

The ACI Thermistor Room Series combines option flexibility with attractive styling in our "-R2" or "-R" style enclosures which include four-way air flow design to minimize selfheating to the sensor. These enclosures are offered in a White "-R2" or Beige "-R" color depending on the enclosure style. These units are designed to be mounted over a single gang junction box or hole in the wall using drywall anchors. Screw terminal blocks are available for making all connections to your building management system (network). An optional 3.175 mm (1/8 in) Black foam pad with pressure sensitive adhesive is available to insulate the sensor from thermal drafts within the wall or wall surface. A 1/16 in Hex driver is needed to secure the cover from being easily removed. The "LCD" option uses two temperature sensors to monitor the ambient air temperature in the space and is factory calibrated at a single point.

Applications

Space Temperature Sensing, Decorative Wall Sensor Applications, Office Buildings, Schools, Colleges, Commercial Buildings, OEM Opportunities

Warranty

The ACI Thermistor Room is covered by ACI's Five (5) Year Limited Warranty. The warranty can be found in the front of ACI's Sensors & Transmitters catalog, as well as on ACI's website, <u>workaci.com</u>.

Specifications

Sensor Type: Thermistor Sensor Curve: Non-Linear, NTC (Negative Temperature

Coefficient)

Number Temperature Sensing Points: One

Sensor Output at 25 °C (77 °F) A/1.8K Series: 1.8 kΩ nominal A/CSI Series: 10 kΩ nominal

> A/3K Series: $3 k\Omega$ nominal A/10KS Series: $10 k\Omega$ nominal

A/AN Series (Type III): $10 \text{ k}\Omega$ nominal A/10K-E1 Series: $10 \text{ k}\Omega$ nominal

A/AN-BC Series: 5.238 kΩ nominal A/50K Series: 50 kΩ nominal | Brown/Yellow)

A/20K Series: 20 kΩ nominal **A/100KS Series:** 100 kΩ nominal

A/CP Series (Type II): 10 kΩ nominal

Accuracy 0 °C to 70 °C (32 °F to 158 °F): ±0.2 °C (±0.36 °F) except:

A/10K-E1 Series: ±0.3 °C (±0.54 °F)

A/1.8K Series: ±0.5 °C at 25 °C (77 °F) and ±1.0 °C (±1.8 °F)

Stability: Sensor Dependent; Contact ACI for more information on specific sensor

Response Time (63% Step Change): 10 seconds nominal

Power Dissipation Constant: 3 mW / °C except: A/1.8K Series: 1 mW / °C

A/10K-E1 Series: 2 mW / °C





LCD Display Supply Voltage: 9 V dc to 35 V dc / 24 V ac (50 Hz to 60 Hz)

LCD Display Supply Current/VA: < 4 mA / 0.12 V A LCD Display Accuracy: ±2 °F or ±2 °C at 21.5 °C (71 °F) typical

LCD Display Descriptor: °F (Fahrenheit) or °C (Celsius) Number of Digits: 3 1/2 Segment Display

LCD Display Life Expectancy: 50,000 hours minimum Set Point Specifications I Set Point Indication: See Ordering Grid options on back of Product Data Sheet

Set Point Tolerance: ±10 % of range

Override Options: Short Thermistor (Default); Field (Jumper) Selectable "Dry Contact" Closure (Separate Input); Short Set Point available upon request

Operating Range: 1.5 °C to 50 °C (35 °F to 122 °F)

Storage Temperature Range

Non-LCD: -40 °C to 65 °C (-40 °F to 149 °F) **LCD Display:** -10 °C to 65 °C (14 °F to 149 °F)

Operating Humidity Range: 10 % to 95 % RH, noncondensing

Connections: Screw Terminal Blocks

Wire Size: 1.31 mm² (16 AWG) to 0.129 mm² (26 AWG)

Terminal Block Torque Rating: 0.5 Nm minimum; 0.6 Nm maximum

Enclosure Material I Color:

"-R2" Enclosure: ABS Plastic, White, UL94-HB

"-R" Enclosure: ABS Plastic, Beige UL94-HB

Product Dimensions: See dimension drawing on this product data sheet

Product Weight:

A/XX-R/RS/RO Series: 63.5g (0.14 lb) A/XX-RSO Series: 81.6g (0.18 lb)

A/XX-R2/R2S/R2O Series: 72.6g (0.16 lb) A/XX-R2SO Series: 90.7g (0.20 lb)


All LCD Display Units: 81.6g (0.18 lb)

Agency Approvals: CE**, UKCA, RoHS2, WEEE

Note¹: All LCD Display Units are not CE Compliant, but they are RoHS2 Compliant



Dimensions



Standard Ordering

Model #	Item #	Description	
A/CP-R	144212 10 kΩ (Type II), "R" Version, Beige, No Options		
A/CP-R2	A/CP-R2 144213 10 kΩ (Type II), "R2" Version, White, No Options		
A/AN-R	A/AN-R 144208 10 kΩ (Type III), "R" Version, Beige, No Options		
A/AN-R2	'AN-R2 144209 10 kΩ (Type III), "R2" Version, White, No Options		
A/20K-R	A/20K-R 144160 20 kΩ, "R" Version, Beige, No Options		
A/20K-R2	A/20K-R2 144170 20 kΩ, "R2" Version, White, No Options		

Custom Ordering

		Options and Descriptions	Model #					
Α.	Sensor Series ¹ No Selection Required	A/	A/					
В.	Model Series Select One (1)	1.8K 3K AN AN-BC CP CSI 10KS 10K-E1 20K 50K 100KS						
C.	Configuration Select One (1)	R = Room RO = Room with Override RS = Room with Set Point						
		RSO = Room with Setpoint and Override R2 = Room R2O = Room with Override						
		R2S = Room with Set Point R2SO = Room with Set Point and Override						
D.	Communication Jack Select One (1)	= No Jack						
		RJ4 = 4 Pin 4 Conductor RJ9, RJ10, or RJ22 Style Head Set Modular Connector						
		RJ6 = 6 Pin 6 Conductor RJ12 Modular Phone Connector						
		232 = 3.5 mm (1/8 in) Stereo Jack						
_	LCD Display² Select One (1)	= No LCD Display						
E.		LCD ² = With LCD Display (Only Available with "R" Style Enclosure)						
F.	LCD Display Descriptor Select One (1)	F = °F (Fahrenheit) C = °C (Celsius)						
~	NIST ³ Select One (1)	= No NIST Certificate						
G.		NIST = NIST Certificate (3-Points)						



	Direct Acting	A01 = 0 Ω to 100 kΩ	A02 = 0 Ω to 20 kΩ	A03 = 0 Ω to 10 kΩ	A06 = 4.75 kΩ to 24.75 kΩ A10 = 0 Ω to 1 kΩ A18 = 10 kΩ to 15 kΩ
		A07 = 10 kΩ to 30 kΩ	Α08 = 1 kΩ to 11 kΩ	A09 = 0 Ω to 2 kΩ	
Slidepots⁴ Select One (1)		A11 = 2.05 kΩ to 3.05 kΩ	A12 = 0 Ω to 400 Ω	A16 = 0 Ω to 5 kΩ	
		A20 = 6.19 kΩ to 26.19 kΩ	A26 = 866 to 1,266	A29 = 7.87 kΩ to 27.8	kΩ
	Reverse Acting	A04 = 1051.1 Ω to 51.1 Ω	A14 = 10 kΩ to 0 Ω	A24 = 9.5 kΩ to 1 kΩ	2
Setpoint Indication Select One (1)	A3 = 18 °	C to 28 °C A4 = 20 °C	to 30 °C B4	= 55 °F to 85 °F	B7 = 60 °F to 90 °F
	C5 = CO	OL/WARM C6 = COO WARMER	LER/ D3	= WARM/COOL	G5 = BLUE/RED (R2 Enclosure)

Note¹: A/ part numbers come without logo. For custom logo, replace A/ with Company abbreviation. Please contact ACI | Note²: LCD Display is not compatible with NIST | Note³: NIST is available in "R" and "R2" only configurations | Note⁴: Other Setpoint configurations are available. Please contact ACI | Note^{*}: Short Sensor is factory default, but the Dry Contact option is field selectable with jumper shunts included.

Accessories Ordering

Model #	Item #	Description
A/MOUNTING PLATE BEIGE R	106821	Wall Mounting Back Plate, Plastic, Beige ("R")
A/MOUNTING PLATE WHITE R	126386	Wall Mounting Back Plate, Plastic, White ("R")
A/MOUNTING PLATE WHITE R2	143369	Wall Mounting Back Plate, Plastic, White ("R2")
LOCKING COVER	107370	Clear Thermostat Guard, Locking Cover, Low Profile
A/ROOM-FOAM-PAD	125690	3.175 mm (1/8 in) Foam Insulation Pad with Adhesive, 76.2 mm (3 in) x 50.8 mm (2 in), Black









WEISS



